

1206 Fast Acting SMD Fuses

DOC.NO.: ISS:F12F12

INDIVIDUAL SPECIFICATION SHEET

Product Name: 1206 Fast Acting SMD Fuses

Part Number: F12F12

Revision: A









Dongguan TLC Electronic Technology Co., LTD

No.18,5th GaoLi Road,TangXia Town,DongGuan,GuangDong,P.R China 523710

TEL: 86-0769-3892 0511
FAX: 86-0769-8793 2077
Http: www.tlcet.com.cn

Rev.	Effective Date	Changed Contents
Α	2020-11-02	New Release

The individual specification sheet are the property of Dongguan TLC electronic technology Co.,Ltd and shall not be copied or used as commercial purposes without permission.

PREPEARED BY	APPROVED BY
杨崎	AVBA



Description

F12F Series are the fuses set the industry standard for performance, reliability and quality. The solder-free design provides excellent on-off and temperature cycling characteristics during use and also makes our SMD fuses more heat and shock tolerant than typical subminiature fuses.

Electrical Characteristics				
Rated Current	1.0ln	2.5In	3.5In	
250mA~5A	4 hour min	5 sec max.	-	
6A~40A	4 hour min.	-	5 sec max.	

Features

- > AEC-Q200 Automotive Grade Certified
- Rapid interruption of excessive current
- Compatible with reflow and wave solder
- > Ceramic and glass construction
- > One time positive disconnect
- Lead Free and Halogen free material

Specifications

Specification							
Part No.	Rated Voltage DC	Rated Curren t (A)	Breaking Capacity(A) ¹	Typical Cold. Resistance (mOhms) ²	Typical Voltage Drop (mV)	Typical Pre- Arcing I ² t (A ² Sec) ³	Alpha Marking
F12F12	32V	12A	150A@32Vdc	5	85	11.5	12


- 1. DC Interrupting Rating (Measured at rated voltage, time constant of less than 50 microseconds, battery source)
- 2. DC Cold Resistance are measured at <10% of rated current in ambient temperature of 25°C
- 3. Typical Pre-arcing I²t are measured at 10In Current

Specifications are subject to change without notice. Application testing is strongly recommended.

Dimension


Drawing not to scale (Unit: mm) Top


view



Side view: 1A~15A










Recommended land pattern



Unit: mm(inch)

Soldering method

Wave solder

■ Reservoir temperature: 260°C


■ Time in reservoir: 10 seconds maximum

> Infrared reflow

■ Temperature: 260°C

■ Time: 30 seconds maximum

Solder reflow profile



Profile Feature		Lead(Pb) free solder
Preheat and soak	Temperature min.(T _{smin})	150°C
	Temperature max. (T _{smax})	200℃
	 Time (T_{smin} to T_{smax}) (t_S) 	60 - 120 Seconds




Average ramp up rate T _{smax} to T _p	3°C / Second Max.	
Liquidous temperature (T _L)	217°C	
Time at liquidous (t∟)	60 - 150 Seconds	
Peak package body temperature (T _P)	260°C	
Time (t _P) within 5°C of the specified classification temperature (T _C)	30 Seconds	
Average ramp-down rate (T _P to T _{smax})	6°C / Second Max.	
Time (25°C to Peak Temperature)	8 Minutes Max.	

Temperature Derating Curve

Normal ambient temperature: 23+/-3°C

Operating temperature: -55 ~ 125°C, with proper correction factor applied



Package

3000 fuses on 8mm tape-and-reel on a 7 inch (178mm) reel per EIA Standard 481.

--- End of Document ---