

1206 Slow Blow SMD Fuses

DOC.No. ISS:F12T 0.75

INDIVIDUAL SPECIFICATION SHEET

Product Name: 1206 Slow Blow SMD Fuses

Part Number: :F12T0.75

Revision: A



Dongguan TLC Electronic Technology Co., LTD

No.18,5th GaoLi Road,TangXia Town,DongGuan,GuangDong,P.R China 523710

TEL: 86-0769-3892 0511
FAX: 86-0769-8793 2077
Http: www.tlcet.com.cn

Rev.	Effective Date	Changed Contents		
Α	2021-11-23	New Release		

The individual specification sheet are the property of Dongguan TLC electronic technology Co.,Ltd and shall not be copied or used as commercial purposes without permission.

PREPEARED BY	APPROVED BY
杨崎	ABB



ndustry standard for performance, reliability and quality. The solder-free design provides excellent on-off and temperature cycling characteristics during use and also makes our SMD fuses more heat and shock tolerant than typical subminiature fuses.

Electrical Characteristics						
Rated Current 1.0In		2.5In	3.0ln	3.5In	10.0ln	
0.75A	4 hour min.	5 sec max.	0.1sec – 3sec	-	0.2ms – 20ms	

Features

- > High inrush current withstanding capability
- AEC-Q200 Automotive Grade Certified
- Compatible with reflow and wave solder
- Ceramic and glass construction
- > Excellent environmental integrity
- One time positive disconnect
- Lead Free and Halogen free material

Specifications

Specification							
Part No.	Rated	Rated Current	Breaking Capacity (A) ¹	Typical Cold. Resistance (mOhms) ²	Typical Voltage Drop (mV)	Typical Pre- Arcing I ² t (A ² Sec) ³	Alpha Mark
	Voltage	(A)					
	DC						
F12T0.75	72V 63V	0.75	50A	850	900	0.01	0.75

- 1. DC Interrupting Rating (Measured at rated voltage, time constant of less than 50 microseconds, battery source)
- 2. DC Cold Resistance are measured at <10% of rated current in ambient temperature of 25°C
- 3. Typical Pre-arcing I²t are measured at 10In Current


Choice fuse for surge application (USB charger etc.), make sure the l²t of fuse is 4 times than surge. Specifications are subject to change without notice. Application testing is strongly recommended.




Dimension

Drawing not to scale (Unit: mm)


Top view



Side view




Recommended land pattern



Unit: mm(inch)







Soldering method

Wave solder

■ Reservoir temperature: 260°C


■ Time in reservoir: 10 seconds maximum

> Infrared reflow

■ Temperature: 260°C

■ Time: 30 seconds maximum

Solder reflow profile




the state of the s					
Profile Feature	Lead(Pb) free solder				
Preheat and soak	Temperature min.(T _{smin})	150°C			
	• Temperature max. (T _{smax})	200℃			
	• Time (T _{smin} to T _{smax}) (t _S)	60 - 120 Seconds			
Average ramp up rate T _{smax} to T _p	3°C / Second Max.				
Liquidous temperature (T _L)	217℃				
Time at liquidous (t _L)	60 - 150 Seconds				
Peak package body temperature	260°C				
Time (t _P) within 5°C of the specifi	30 Seconds				
Average ramp-down rate (TP to T	6°C / Second Max.				
Time (25°C to Peak Temperature	8 Minutes Max.				



Temperature Derating Curve

Normal ambient temperature: 23+/-3°C

Operating temperature: -55 ~ 125°C, with proper correction factor applied



Package

3000 fuses on 8mm tape-and-reel on a 7 inch (178mm) reel per EIA Standard 481.

--- End of Document ---