

HSF

NOTES:

Current Rating: 2.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 500V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C

Contact Material: Phosphor Bronze
 Contact plating: Au Or Sn over Ni
 Insulator Material: PA9T+30%GF UL94V-0


Ordering Information

2243 - 2 XX S XX CUN T

No. of Pins per Row: 02-40PIN
 Contact Plating:
 G0=Gold Flash
 G3=10μ"Gold
 G4=15μ"Gold
 G5=30μ"Gold
 S0=Gold Flash/Tin
 S3=10μ"Gold/Tin
 S4=15μ"Gold/Tin
 S5=30μ"Gold/Tin
 SN=Tin
 SM=Matte Tin

Packing:
 T=Tube

| | | |
|-----------|-------|-----------|
| Item | Pitch | Mating |
| Standard | 2.00 | 1215/1220 |
| Alternate | | |



Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)

| | | | | | | | | | |
|---|------------|--------------------------|---------|------------|-------|--------------------------|--|--------------|--|
| OPERATION | | DRAW | | DATE | | SCALE | | PART NO. | |
| XX | ±0.40 | JYHuang | CHECK | 2012/07/19 | mm | 2243-2XXSXXCUN T1 | | TITLE: | |
| XX XX | ±0.25 | | CHECK | DATE | A4 | FH2.00 DUAL ROW 180° DIP | | H=4.3 W=4.5 | |
| XX XXX | ±0.15 | | | DATE | SHEET | 1/1 | | Customer NO. | |
| Angle | ± 3° | | APPROVE | DATE | PROJ. | | | | |
| DIM | TOL | | | | | | | | |
| REV | DATE | MODIFICATION DESCRIPTION | | CHANGE | | | | | |
| A0 | 2012/07/19 | NEW | | | | | | | |
| <p>WCON-Dongguan Htt: www.wcon.com WCON-Kunshan</p> <p>Tel: +86 769 85358920 Tel: +86 512 57468408</p> <p>Fax: +86 769 85358915 Fax: +86 512 57468468</p> <p>E-mail: sales@wcon.com E-mail: sales@wcon.com</p> | | | | | | | | | |