



NOTES:
 Rated Current: 9.0AMP
 Contact Resistance: 30mΩ max
 Withstand Voltage: 1500V AC/minute
 Insulation Resistance: 1000MΩ min
 Operation Temperature: -25℃ to +85℃

Contact Material: Brass
 Contact plating: Au Or Sn Over Ni
 Insulator Material: PA66(White Transparent
 UL94-V2 std)Or PA46(Natutal UL94-V0)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE ±0.05)



PART NO.	PIN	A	B	Material
WF4202-2WRHXXX1	2*5P 及以下	+0.30 -0.10	+0.40 -0.20	PA46
	2*5P 以上	+0.50 -0.00	+0.60 -0.00	
WF4202-2WRXXX1	2*1P-2*12P	±0.20	±0.30	PA66

Ordering Information

WF4202 -2WR XX W A 1

No. of Row
Dual Row


No. of pins
01-12P

Insulation Material
H=PA46
Blank=PA66

Contact Plating
S0=Gold Flash/Tin
S3=10u"Gold/Tin
S4=15u"Gold/Tin
S5=30u"Gold/Tin
G0=Gold Flash
G3=10u"Gold
G4=15u"Gold
G5=30u"Gold
Blank=Tin

Color
B=Black
T=Natural
W=White Transparent

Packing
0=PE Bag
A=Tray



Specification & Ordering Information:

Circuit	Part No.	Dimension		Pcs /Tray
		A	B	
2x01	WF4202-2WR01WA1	---	5.40	410
2x02	WF4202-2WR02WA1	4.20	9.60	230
2x03	WF4202-2WR03WA1	8.40	13.80	160
2x04	WF4202-2WR04WA1	12.60	18.00	130
2x05	WF4202-2WR05WA1	16.80	22.20	100
2x06	WF4202-2WR06WA1	21.00	26.40	80
2x07	WF4202-2WR07WA1	25.20	30.60	70
2x08	WF4202-2WR08WA1	29.40	34.80	60
2x09	WF4202-2WR09WA1	33.60	39.00	60
2x10	WF4202-2WR10WA1	37.80	43.20	50
2x11	WF4202-2WR11WA1	42.00	47.40	50
2x12	WF4202-2WR12WA1	46.20	51.60	40


REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
A2	2019/05/15	MODIFY	---	X.X ±0.40	Ding	2019/05/15	UNIT	mm	SEE TAB
A1	2013/05/22	MODIFY THE DRAWING	---	X.XX ±0.25	CHECK	DATE	SIZE	A4	TITLE: 4.20 MINI FIT DUAL ROW 90° WITHOUT POST
AO	2012/09/19	NEW	---	X.XXX ±0.15	APPROVE	DATE	SHEET	1/2	Customer NO.
				Angle ± 3°			PROJ.		
				DIM TOL					

WCON


Http: www.wcon.com

WCON-Dongguan
 Tel: +86 769 85358920
 Fax: +86 769 85358915
 E-mail: sales@wcon.com


WCON-Kunshan
 Tel: +86 512 57468408
 Fax: +86 512 57468468
 E-mail: salesks@wcon.com




2x01P




2x02P




2x03P




2x04P




2x05P




2x06P




2x07P




2x08P




2x09P



2x10P



2x11P



2x12P

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
A2	2019/05/15	MODIFY	—	x.x ±0.40	Ding	2019/05/15	UNIT	mm	WF4202-2WRXXWX1
A1	2013/05/22	MODIFY THE DRAWING	—	x.xx ±0.25	CHECK	DATE	SIZE	A4	
AO	2012/09/19	NEW	—	x.xxx ±0.15	APPROVE	DATE	SHEET	2/2	TITLE: 4.20 MINI FIT DUAL ROW 90° WITHOUT POST
				Angle ± 3°			PROJ.	⊕	Customer NO.
				DIM TOL					



Http: www.wcon.com

WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com	WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com
---	--