

1206 Slow Blow SMD Fuses

DOC.No. ISS:F12T2

INDIVIDUAL SPECIFICATION SHEET

Product Name: 1206 Slow Blow SMD Fuses

Part Number: :F12T2

Revision: B



Dongguan TLC Electronic Technology Co., LTD

No.18,5th GaoLi Road, TangXia Town, DongGuan, GuangDong, P.R China 523710

TEL: 86-0769-3892 0511 FAX: 86-0769-8793 2077

Http: www.tlcet.com.cn

| Rev. | Effective Date | Changed Contents | | |
|------|----------------|----------------------|--|--|
| Α | 2020-9-25 | New Release | | |
| В | 2021-3-10 | Update Spedfications | | |
| | | | | |

The individual specification sheet are the property of Dongguan TLC electronic technology Co.,Ltd and shall not be copied or used as commercial purposes without permission.

| PREPEARED BY | APPROVED BY |
|--------------|-------------|
| 杨娟 | ABA |



Description

F12T Series are the fuses set the industry standard for performance, reliability and quality. The solder-free design provides excellent on-off and temperature cycling characteristics during use and also makes our SMD fuses more heat and shock tolerant than typical subminiature fuses.

| Electrical Characteristics | | | | | |
|----------------------------|-------------|------------|---------------|-------|--------------|
| Rated Current | 1.0In | 2.5In | 3.0In | 3.5ln | 10.0ln |
| 2A | 4 hour min. | 5 sec max. | 0.1sec – 3sec | - | 0.2ms – 20ms |

Features

- ➤ High inrush current withstanding capability
- > AEC-Q200 Automotive Grade Certified
- > Compatible with reflow and wave solder
- Ceramic and glass construction
- > Excellent environmental integrity
- One time positive disconnect
- > Lead Free and Halogen free material

Specifications

| Part No. | Rated Voltage DC | Rated Current (A) | Breaking Capacity (A) | Typical Cold. Resistance (mOhms) ² | Typical Voltage Drop (mV) | Typical Pre- Arcing I ² t (A ² Sec) | Alpha Mark |
|----------|------------------------|-------------------------|--------------------------|-----------------------------------------------------|---------------------------------|--------------------------------------------------------------|---------------|
| F12T2 | 72V | 2A | 50A | 135 | 316 | 0.41 | N |

- 1. DC Interrupting Rating (Measured at rated voltage, time constant of less than 50 microseconds, battery source)
- 2. DC Cold Resistance are measured at <10% of rated current in ambient temperature of 25°C
- 3. Typical Pre-arcing I²t are measured at 10In Current


Choice fuse for surge application (USB charger etc.), make sure the l²t of fuse is 4 times than surge. Specifications are subject to change without notice. Application testing is strongly recommended.



Dimension

Drawing not to scale (Unit: mm)


Top view




Side view



Recommended land pattern









Soldering method

Wave solder

■ Reservoir temperature: 260°C


■ Time in reservoir: 10 seconds maximum

> Infrared reflow

■ Temperature: 260°C

■ Time: 30 seconds maximum

Solder reflow profile




| Profile Feature | Lead(Pb) free solder | |
|----------------------------------------------------------|------------------------------------------------------------------|------------------|
| Preheat and soak | reheat and soak • Temperature min.(T _{smin}) | |
| | Temperature max. (T _{smax}) | 200°C |
| | Time (T _{smin} to T _{smax}) (t _S) | 60 - 120 Seconds |
| Average ramp up rate T _{smax} to T _p | 3°C / Second Max. | |
| Liquidous temperature (T _L) | 217°C | |
| Time at liquidous (t∟) | 60 - 150 Seconds | |
| Peak package body temperature | 260°C | |
| Time (t _P) within 5°C of the specific | 30 Seconds | |
| Average ramp-down rate (TP to T | 6°C / Second Max. | |
| Time (25°C to Peak Temperature | 8 Minutes Max. | |



Temperature Derating Curve

Normal ambient temperature: 23+/-3°C

Operating temperature: -55 ~ 125°C, with proper correction factor applied



Package

3000 fuses on 8mm tape-and-reel on a 7 inch (178mm) reel per EIA Standard 481.

--- End of Document ---