

PolySwitch®

PTC Devices Overcurrent Protection Device

PRODUCT: BD280-1130-20/16

DOCUMENT: SCD26435

REV LETTER: I

REV DATE: JANUARY 21, 2019

PAGE: 1 OF 2

Д

lacksquare

Specification Status: Released

Electrical Rating

Voltage: 14 Vdc MAX Current: 100 A MAX **Terminal Material:**

Brass H65

Thickness: 0.8mm

Tin plating thickness: 5µm

Insulating Material:

Black& Yellow color PBT, Meets UL94V-0

Requirements

Marking:

- Manufacturer's Mark 14VDC - Voltage

Rating

BD280-1130-10 - Part ID

□□□□ - Lot Number

TABLE I. DIMENSIONS:

mm: in*:

| Α | | l B | | C | | l D | | E(x2) | | F | |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|------|------|-------|
| MIN | MAX | MIN | MAX | MIN | MAX | MIN | MAX | MIN | MAX | MIN | MAX |
| 30.0 | 30.6 | 8.7 | 9.3 | 10.75 | 11.25 | 6.05 | 6.65 | 2.55 | 3.05 | 3.3 | 3.9 |
| 1.181 | 1.205 | 0.343 | 0.366 | 0.423 | 0.443 | 0.238 | 0.262 | 0.1 | 0.12 | 0.13 | 0.154 |

| G | | Н | | I | | J | | K | |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| MIN | MAX |
| 3.4 | 4 | 1.7 | 2.3 | 10.9 | 11.5 | 0.8 | 1.2 | 0.6 | 1.0 |
| 0.134 | 0.157 | 0.067 | 0.091 | 0.429 | 0.453 | 0.031 | 0.047 | 0.024 | 0.039 |

^{*}Rounded off approximation

TABLE II: PERFORMANCE RATINGS:

| | INITIAL | | TIME TO TRIP | TRIP CURRENT | R1max | ONE- | HOLD CURRENT | TRIPPED-STATE |
|----|------------------------|----|--------------|--------------|------------|------|--------------|---------------|
| RI | RESISTANCE AT 80AMPS | | AT 80AMPS | AT Rmin | HOUR | | AT R1max | POWER |
| | VALUES | | | | POST-TRIP | | | DISSIPATION |
| | | | | | RESISTANCE | | | |
| | OHMS | | SECONDS AT | AMPS OHMS | | /IS | AMPS | WATTS AT |
| / | AT 25°C | | 25°C | AT 25°C | AT 25°C | | AT 25°C | 20°C, 14V |
| | MIN MAX | | MAX | MAX | MA | X | MIN | TYP |
| 0. | 0028 0.00 | 45 | 10.0 | 26.0 | 0.00 | 64 | 16 | 5.2 |

Reference Documents: PS300, PS400 & SAE-J2685

Precedence: This specification takes precedence over documents referenced herein. Effectivity: Reference documents shall be the issue in effect on the date of invitation orbid. CAUTION:

Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame When using a test probe to probe either of the two test points on the top of the device, care should be taken to avoid puncturing through the insulating material of the device, as this can

result in shorting out the terminals which can cause electrical arcing orflame.

Materials Information

ROHS Compliant

ELV Compliant

Pb-Free

Directive 2002/95/EC

Directive 2000/53/EC Compliant





PolySwitch® PTC Devices Overcurrent Protection Device

PRODUCT: BD280-1130-20/16

DOCUMENT: SCD26435 REV LETTER: I

REV DATE: JULY 26, 2016

PAGE: 2 OF 2

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their Own applications. Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, military, aerospace, medical, lifesaving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set for thin applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set for thin applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set for thin applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.