

PolySwitch® PTC Devices

Overcurrent Protection Device

PRODUCT: VLP175UAF

DOCUMENT: SCD25835

PCN: D55286 REV LETTER: E

REV DATE: JULY 26, 2016

PAGE NO.: 1 OF 2

Specification Status: Released

Maximum Electrical

Rating

Operating Voltage: 16Vdc Interrupt Current: 60A

Chip Size: 2.8 X 9.6 mm Leads: Nickel 1/2H

0.125mm nominal


thickness Solder: Lead-free

Tape: None

Marking: None

mm:

in*:



*Dimension values on the drawing are for reference only.

TABLE I. DIMENSIONS:

MIN MAX MIN MAX MAX MIN MAX MIN MIN MIN MAX MIN 23.6 25.6 2.7 2.9 0.7 7.0 8.0 7.0 8.0 2.3 2.5 (0.93)(1.01)(0.11)(0.11)(0.03)(0.28)(0.31)(0.28)(0.31)(0.09)(0.98)

*Rounded off approximation

TABLE II. PERFORMANCE RATINGS: As measured in Mueller Kelvin Clips model BU-75K.

I HOLD	CURRENT TRIP LIMITS									_	REFERENCE ONE-H				TRIPPED-
										.IP	RESIS	STANC			STATE
											F	E	RESIS	STANC	POWER
													E		DISSIPATIO
															N
AMPS	AMPS		AMPS		AMPS		AMPS		SECONDS		OHMS		OHMS		WATTS AT
25°C	AT 0°C		AT 25°C		AT 60°C		AT°C		AT 25°C,		AT 25°C		AT 25°C		25°C, 16V
									8.75A		/ 20 0		, 20 0		20 0, 101
HOLD	HOLD	TRIP	HOLD	TRIP	HOLD	TRIP	HOLD	TRIP	MIN	MAX	MIN	MAX	MIN	MAX	MAX
1.75	2.3	5.3	1.75	3.9	0.9	2.2				5.0	0.023	0.041	0.023	0.082	1.8

Agency Recognitions: UL, CSA, TUV Reference Documents: PS300

Precedence: This specification takes precedence over documents referenced herein.

Effectivity: Reference documents shall be the issue in effect on the date of invitation for bid.

CAUTION: Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

Materials Information: ROHS Compliant

ELV Compliant

Pb-Free

Directive 2002/95/EC Compliant

Directive 2000/53/EC Compliant





PolySwitch® PTC Devices

Overcurrent Protection Device

PRODUCT: VLP175UAF

DOCUMENT: SCD25835 PCN: D55286

REV LETTER: E REV DATE: JULY 26, 2016

PAGE NO.: 2 OF 2

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, military, aerospace, medical, lifesaving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.