

General

- Chip size from 1206 to 2512
- Resistance value from 1mΩ to 500mΩ
- Low thermal EMF
- Low inductance 0.5nH to 5nH
- Low TCR
- Lead free, RoHS compliant for global
- Applications and halogen free

Application

- Switching model power supply
- Battery pack
- Notebook, personal computer
- Test Instrument
- Power Amplifier

Electrical Specifications

| Type | Power Rating at 70°C(W) | Resistance Range (mΩ) | TCR (ppm/°C) | Resistance tolerance | Operation Temp. Range |
|------|-------------------------|-----------------------|--------------|----------------------|-----------------------|
| 2512 | 2 | 1~500 | ±50 | ±0.5%(D) | -55°C~+170°C |
| | 3 | 1~10 | | ±1%(F) | |
| 1206 | 1 | 2~30 | | ±5%(J) | |
| | | | | ±0.5%(D) | |
| | | | | ±1%(F) | |

Part Number information

SMR 25 M 2 F R010 I

【1】 【2】 【3】 【4】 【5】 【6】 【7】

【1】 Series Name: SART Metal Current Sensing Chip Resistors

【2】 Chip size: 12:1206 25:2512

【3】 Material Code: M:MnCu N:NiCu S:CuMnSn


【4】 Power Code: 1:1W 2:2W 3:3W

【5】 Resistance Tolerance: F:±1% D:±0.5% J:±5%


【6】 Resistance Code: R002=2mΩ、R010=10mΩ、2L50=2.5mΩ

【7】 Packaging Code: T: Tape & Reel、B: Bulk Pack

Dimensions




2512 (1~2mΩ)




2512 (3~500mΩ)

| Type | Resistance Range (mΩ) | L (mm) | W (mm) | T (mm) | E (mm) |
|------|-----------------------|-----------|-----------|-----------|-----------|
| 2512 | 1~2 | 6.40±0.20 | 3.20±0.20 | 0.80±0.20 | 2.00±0.20 |
| | 3~500 | | | | 0.90±0.20 |




| Type | Resistance Range (mΩ) | L (mm) | W (mm) | T (mm) | E (mm) |
|------|-----------------------|-----------|-----------|-----------|----------|
| 1206 | 2~30 | 3.20±0.20 | 1.60±0.20 | 0.70±0.20 | 0.5±0.30 |

Recommended Land Patterns




| Type | Resistance Range (mΩ) | a (mm) | b (mm) | L (mm) |
|------|-----------------------|--------|--------|--------|
| 2512 | 1~2 | 4.00 | 3.10 | 1.80 |
| | 3~500 | 4.00 | 2.10 | 4.10 |
| 1206 | 2~30 | 1.80 | 1.70 | 1.60 |

Materials



| No. | Materials |
|-----|-------------|
| 1 | Metal Alloy |
| 2 | Epoxy |
| 3 | Epoxy |
| 4 | Cu |
| 5 | Ni |
| 6 | Sn |


Power Derating Curve



Recommended Solder Curve

1. Infrared Reflow

- Temperature: 260°C.
- Time: 10 sec Max.
- Recommend Reflow profile:



| Profile Feature | Pb-Free Assembly |
|--|--------------------------------|
| Average Ramp-up Rate (T _{Smax} to T _p) | 3°C/sec Max. |
| Preheat Temperature Min.(T _{Smin}) Temperature Max.(T _{Smax}) Time(ts)(T _{Smin} to T _{Smax}) | 150°C 200°C 60sec~120sec |
| Peak Temperature(T _p) | 260°C |
| Time (t _p) within 5°C of actual Peak Temperature(T _p) | 10sec Max |
| Liquidous temperature (T _L) | 217°C |
| Time at liquidous (T _L) | 60sec~150sec |
| Ramp-down Rate | 6°C/sec Max. |
| Time 25°C to peak Temperature | 8 min Max. |

2. Wave soldering

- Reservoir Temperature: 260°C
- Time in Reservoir: 10sec Max.

3. Hand Soldering


- Temperature: 350°C
- Time: 3sec Max.

Product Characteristics


| Item | Test condition/ Methods | Performance | Standard |
|---------------------------------------|--|------------------------------------|---------------------------|
| Resistance | Measuring resistance value at room temperature 25°C ±5°C | Refer to SART Spec | IEC60115-1 4.5 |
| Temperature coefficient of resistance | $TCR = (R-R_0)/R_0(T_2-T_1) \times 10^{-6}$ T1 T2 Test temperature: +25°C~+125°C | Refer to SART Spec | MIL-STD-202 Method 304 |
| Short time Overload | 5 times the rated power for 5 sec | $ \Delta R \leq 1.0\%R$ | IEC 60115-1 4.13 |
| Resistance to Soldering Heat | 260°C±5°C, time: 10 sec±1 sec | $ \Delta R \leq 1.0\%R$ | MIL-STD-202 Method 210 |
| Thermal shock | -55°C(15min)/+125°C(15min), 300 cycles | $ \Delta R \leq 1.0\%R$ | MIL-STD-202 Method107G |
| Low temperature storage | -55°C for 45 min, No power | $ \Delta R \leq 1.0\%R$ | IEC60115-1 4.23.4 |
| High Temperature storage | 125°C for 1000 hours, No power | $ \Delta R \leq 1.0\%R$ | MIL-STD-202 Method 108 |
| Temperature Humidity Bias Test | +85°C, 85% RH, 10%bias, 1000hours | $ \Delta R \leq 1.0\%R$ | MIL-STD-202 Method103 |
| Mechanical shock | 100 g's ,6 ms, 5pulses | $ \Delta R \leq 1.0\%R$ | MIL-STD-202 Method 213 |
| Vibration | The frequency varies from 10Hz to 2000Hz, 1 min, 3 directions, and 12 hours | $ \Delta R \leq 1.0\%R$ | MIL-STD-202 Method 204 |
| Load life | 70°C±2°C, 1000 hours, at rated power 1.5 hours "ON", 0.5 hours "OFF" | 2512 3W: $ \Delta R \leq 2\%R$ | MIL-STD-202 Method 108 |
| | | Other: $ \Delta R \leq 1.0\%R$ | |
| Solderability | Dip the terminal in a flux and then dip into a soldering bath at 245°C±5°C for 2sec~3sec | Min 95% coverage | J-STD-002B Test B |
| Board Flex | Min 2 mm deflection,60sec | $ \Delta R \leq 1.0\%R$ | AEC-Q200-005 |
| ESD test | Other: 2KV, 2 times /1sec | $ \Delta R \leq 1.0\%R$ | AEC-Q200-002 |

Packaging

1. Embossed Tape Dimensions



| Type | A (mm) | B (mm) | W (mm) | F (mm) | E (mm) |
|------|--------------------------|-----------------|------------------|---------------------|-----------------|
| 2512 | $3.60 \pm_{0.18}^{0.20}$ | 6.90 ± 0.20 | 12.00 ± 0.20 | 5.50 ± 0.05 | 1.75 ± 0.10 |
| Type | P1 (mm) | P2 (mm) | P0 (mm) | D0/D1 (mm) | T (mm) |
| 2512 | 4.00 ± 0.10 | 2.00 ± 0.05 | 4.00 ± 0.05 | $1.50 \pm_0^{0.10}$ | 1.00 ± 0.15 |



| Type | A (mm) | B (mm) | W (mm) | F (mm) | E (mm) |
|------|-----------------|-----------------|-----------------|---------------------|-----------------|
| 1206 | 2.00 ± 0.15 | 3.60 ± 0.20 | 8.00 ± 0.20 | 3.50 ± 0.05 | 1.75 ± 0.10 |
| Type | P1 (mm) | P2 (mm) | P0 (mm) | D0 (mm) | T (mm) |
| 1206 | 4.00 ± 0.10 | 2.00 ± 0.05 | 4.00 ± 0.10 | $1.50 \pm_0^{0.10}$ | 0.84 ± 0.10 |

2. Reel Dimensions




| Type | ϕA (mm) | ϕB (mm) | ϕC (mm) | F (mm) | W (mm) |
|------|------------------|------------------|------------------|------------|------------|
| 2512 | 178.00±2.00 | 60.00±1.00 | 13.50±0.50 | 15.40±1.00 | 13.00±0.30 |
| 1206 | 178.00±2.00 | 60.00±1.00 | 13.50±0.50 | 11.40±0.10 | 9.00±0.30 |

3. Quantity of Package

| Type | Quantity(pcs) |
|------|---------------|
| 2512 | 4000 |
| 1206 | 5000 |

4. Peeling Test



Storage

- The ambient temperature shall be between 5°C~35°C.
- The relative humidity recommended for storage is between 25%RH~75%RH.
- Sealed plastic bags with desiccant shall be used to reduce the oxidation of the termination and shall only be opened prior to use.
- The products shall not be stored in areas where harmful gases containing sulfur or chlorine are present.