

DATA SHEET

CURRENT SENSOR - LOW TCR AUTOMOTIVE GRADE

PA1206_L series 5%, 1%

RoHS compliant & Halogen free



YAGEO Phicomp



SCOPE

This specification describes PA series current sensor - low TCR with lead-free terminations made by metal substrate.

APPLICATIONS

- · Consumer goods
- Computer
- Telecom / Datacom
- Industrial / Power supply
- Alternative Energy
- · Car electronics

FEATURES

- · AEC-Q200 qualified
- · Halogen-free Epoxy
- · RoHS compliant
- Reduce environmentally hazardous wastes
- High component and equipment reliability
- Non-forbidden materials used in products/production
- Low resistances applied to current sensing

ORDERING INFORMATION - GLOBAL PART NUMBER

Global part numbers are identified by the series, size, tolerance, packing type, temperature coefficient, taping reel and resistance value.

GLOBAL PART NUMBER

PA <u>XXXX</u> <u>X</u> <u>X</u> <u>X</u> <u>X</u> <u>XX</u> <u>XXXX</u> <u>L</u> (6) (7)

(I) SIZE

1206

(2) TOLERANCE

D = $\pm 0.5\%$ (for 5m Ω and up)

 $F = \pm 1\%$

 $| = \pm 5\%$

(3) PACKAGING TYPE

R = Paper taping reel

(4) TEMPERATURE COEFFICIENT OF RESISTANCE

 $F = \pm 100$ ppm/°C

 $M = \pm 75$ ppm/°C

 $E = \pm 50$ ppm/°C

(5) TAPING REEL

07 = 7 inch dia. Reel & standard power (1/4W)

7W = 7 inch dia. Reel & 2 x standard power (1/2W)

47 = 7 inch dia. Reel & $4 \times$ standard power (IW)

67 = 7 inch dia. Reel & $6 \times standard power (1.5W)$

(6) RESISTANCE VALUE

I m Ω to 50 m Ω

(7) DEFAULT CODE

Letter L is the system default code for ordering only. (Note)

number Resistance code rule	Example
0RXXX	0R001 = 1 mΩ
(I to $50\text{m}\Omega$)	$0R015 = 15 \text{ m}\Omega$

Resistance rule of global part

ORDERING EXAMPLE


The ordering code of a PA1206 IW chip resistor, TC100, value 0.003Ω with $\pm1\%$ tolerance, supplied in 7-inch tape reel is: PA1206FRF070R003L

NOTE

I. All our RChip products are RoHS compliant. "LFP" of the internal 2D reel label mentions "Lead-Free Process"

MARKING

PA1206



4 digits

The "R" is used as a decimal point; the other 3 digits are significant PA1206: $Im\Omega$



4 digits

The "R" is used as a decimal point; the other 3 digits are significant PA1206: $2m\Omega$ to $50m\Omega$


CONSTRUCTION

The resistors are constructed using outstanding TCR level material, which makes Yageo PA resistors excellent for current sensing application in battery charger circuit & DC-DC converter.

The composition of the resistive material is adjusted to give the approximate required resistance and is covered with a protective coating. Marking is printed on the top side of the resistor.

Finally, the three external terminations (Cu / Ni / matte Tin) are added, as shown in Fig. 4.

Outlines



DIMENSION

Table I For outlines, please refer to Fig. 4

TYPE	RESISTANCE RANGE	POWER RATING	L (mm)	W (mm)	H (mm)	I _I (mm)	I ₂ (mm)
	Im Ω	I/4W	3.20 ± 0.25	1.60±0.25	0.65±0.25	1.04±0.25	1.04±0.25
PA1206	$2m\Omega \le R \le 5m\Omega$	– 1/2W – IW	3.20 ± 0.25	1.60±0.25	0.65±0.25	0.64±0.25	0.64±0.25
	$6m\Omega \le R \le 50m\Omega$	1.5W (1~5mΩ)	3.20 ± 0.25	1.60±0.25	0.65±0.25	0.51±0.25	0.51±0.25

Note:

- 1. For relevant physical dimensions, please refer to construction outlines.
- 2. Please contact with sales offices, distributors and representatives in your region before ordering.

ELECTRICAL CHARACTERISTICS

Table 2

SERIES	SIZE	POWER RATING	TOLERANCE	RESISTANCE RANGE	TEMPERATURE COEFFICIENT OF RESISTANCE
PA 1206	1206	1/4W 1/2W 1W	±1% ±5%	$Im\Omega \le R \le 2m\Omega$ $3m\Omega \le R \le 50m\Omega$	±75ppm/°C, ±100ppm/°C ±50ppm/°C, ±75ppm/°C, ±100ppm/°C
	1200	1.5W		$Im\Omega \le R \le 2m\Omega$ $3m\Omega \le R \le 5m\Omega$	±75ppm/°C, ±100ppm/°C ±50ppm/°C, ±75ppm/°C, ±100ppm/°C

Note: Please contact with sales offices, distributors and representatives in your region before ordering.

FUNCTIONAL DESCRIPTION

OPERATING TEMPERATURE RANGE

PAI206 Range: -55°C to +170°C

POWER RATING

Standard rated power at 70°C:

For detail power value, please refer to Table 2.

RATED VOLTAGE

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:


$$V = \sqrt{(PxR)}$$

Where

V = Continuous rated DC or AC (rms) working voltage (V)

P = Rated power (W)

 $R = Resistance value (\Omega)$




Chip Resistor Surface Mount | PA1206_L | SERIES |

PACKING STYLE AND PACKAGING QUANTITY

Table 3 Packing style and packaging quantity

PACKING STYLE	REEL DIMENSION	PA1206
Paper Taping Reel (R)	7" (178 mm)	4,000

PAPER TAPE



_____Table 4 Dimensions of paper tape for relevant chip resistors size

SIZE	SYMBOL										Unit: mm
	A_0	B ₀	W	E	F	P_0	Pı	P_2	$ \emptyset D_0 $	$\emptyset D_1$	Т
PA1206	i.90± 0.10	3.50± 0.10	8.00± 0.30	1.75± 0.10	3.50± 0.10	4.00±0.10	4.00±0.10	2.00±0.10	1.55±0.05	1.50±0.10	1.50± 0.10

REEL SPECIFICATION





Table 5 Dimensions of reel specification for relevant chip resistors size

CUTE QUANTITY -		REEL S	SIZE	SYMBOL					Unit: mm
SIZE	PER REEL	8 mm TAPE WIDE	I2 mm TAPE WIDE	Α	N	С	D	Wı	W _{2 MAX.}
PA1206	4000		7" (Ø178 mm)	180.0+0/-3	60.0+1/-0	13.0± 0.2	21.0±0.8	8.4 + 1/-0	12.4

LEADER/TRAILER TAPE SPECIFICATION



FOOTPRINT AND SOLDERING PROFILES

For recommended soldering profiles, please refer to data sheet "Chip resistors mounting".

FOOTPRINT




Table 6 Footprint dimensions

					Unit: mm
SIZE	RESISTANCE RANGE	Α	В	С	D
PA1206	$Im\Omega \le R \le 50m\Omega$	3.90	0.76	1.57	1.78

TESTS AND REQUIREMENTS

Table 8 Test condition, procedure and requirements

TEST	TEST METHOD	PROCEDURE	REQUIREMENT
Short time overload	IEC60115-1 4.13	5 times of rated power for 5 seconds at room temperature	$\pm 0.5\% + 0.0005 \Omega$ No visible damage
High Temperature Exposure	MIL-STD-202-Method 108	I,000 hours at maximum operating temperature depending on specification, unpowered	±1.0%+0.0005 Ω
		No direct impingement of forced air to the parts Tolerances: 170±3°C	
Temperature Cycling	JESD22-A104C	I,000 cycles, -55/+125°C for I cycle per hour	±0.5%+0.0005 Ω
Moisture Resistance	MIL-STD-202-Method 106	Each temperature / humidity cycle is defined at 8 hours method 106F, 3 cycles / 24 hours for 10d with 25°C / 65°C 95% R.H, without steps 7a & 7b, unpowered	±0.5%+0.0005Ω
Biased	MIL-STD-202 Method 103	1,000 hours; 85°C / 85% RH	$\pm 0.5\% + 0.0005 \Omega$
Humidity		10% of operating power	
Operational Life/ Endurance	MIL-STD-202-Method 108	1,000 hours at 125±3°C, de-rated voltage applied for 1.5 hours on, 0.5 hour off, stillair required	±1.0%+0.0005Ω
		1,000 hours at 70±2°C applied RCWV	±1.0%+0.0005 Ω
		1.5 hours on, 0.5 hour off, still air required	
Resistance to Solvents	MIL-STD-202 Method 215	Immerse in isopropyl alcohol for 5 min with ultrasonic at room temperature	No Visible damage
Mechanical Shock	MIL-STD-202 Method 213	Three shocks in each direction shall be applied along the three mutually perpendicular axes of the test specimen.	±0.5%+0.0005Ω
		Peak value: 100 g's	
		Duration: 6 ms	
		Velocity change: 12.3 ft/s	
		Waveform: Half sine	
Vibration	MIL-STD-202 Method 204	5 g's for 20 min., 12 cycles each of 3 orientations	±0.5%+0.0005 Ω
		Test from 10-2000 Hz.	
Resistance to	MIL-STD-202-method 210	Condition B, no pre-heat of samples	±0.5%+0.0005Ω
Soldering Heat		Leadfree solder, 260°C, 10 seconds immersion time	No visible damage
		Procedure 2 for SMD: devices fluxed and cleaned with isopropanol	
Thermal Shock	MIL-STD-202 Method 107	-55/+125°C, Number of cycles is 300.	±0.5%+0.0005 Ω
		Devices mounted.	No visible damage
		Maximum transfer time is 20 seconds.	
		Dwell time is 15 minutes. Air -Air	



9 10

Chip Resistor Surface Mount PA1206_L SERIES

Electrostatic	AEC-Q200-002	Human Body Model, I pos + I neg.	±1.0%+0.0005Ω
Discharge		Discharges 1206=2KV	No visible damage
Solderability - Wetting	J-STD-002B test B	a Method B, aging 4 hours at 155°C dry heat, dipping at 235±3°C for 5±0.5 seconds.	Well tinned (>95% covered) No visible damage
		b Method B, steam aging 8 hours, dipping at $215\pm3^{\circ}$ C for 5 ± 0.5 seconds.	
		c Method D, steam aging 8 hours, dipping at 260 ± 3 °C for 7 ± 0.5 seconds.	
Flammability	UL94	Try to inflame a specimen by a needle flame	No ignition of specimen; V-0
Board Flex / Bending	AEC-Q200-005	Chips mounted on a 90mm glass epoxy resin PCB FR4, Bending for 1206=2 mm	±1.0%+0.0005Ω
		Holding time: Min.60 seconds	
Terminal Strength SMD	AEC-Q200-006	Applied a 17.7N 1.8Kg for 60±1 seconds.	±1.0%+0.0005 Ω No visible damage
Flame Retardance	AEC-Q200-001	Apply voltage from 9V to 32V to increase the surface temp to 350°C	No flame, no explosion
Temperature Coefficient of Resistance T.C.R.	MIL-STD-202 Method 304	At $+25/+150^{\circ}$ C Formula: T.C.R= $\frac{R_2 - R_1}{RI(t_2 - t_1)} \times 10^6 \text{ppm/}^{\circ}$ C Where $t1 = +25^{\circ}$ C or specified room temperature $t2 = +150^{\circ}$ C test temperature R1=resistance at reference temperature in ohms	Refer to table 2
Flower-of-Sulfur FOS	Modified ASTM B809-95	R2=resistance at test temperature in ohms Sulfur 105°C, 750 hours, unpowered.	±1.0%+0.0005Ω

Chip Resistor Surface Mount | PA1206_L | SERIES |

REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 2	Jul. 24, 2017	-	- Add part number coding details for the relationship between taping reel and rated power
Version I	May 05, 2017	-	- Extend resistor value
Version 0	Mar. 31, 2017	-	- New datasheet for automotive grade current sensor –PA1206_L series.

[&]quot;Yageo reserves all the rights for revising the content of this datasheet without further notification, as long as the products itself are unchanged. Any product change will be announced by PCN."