

# FH30150D


## N-Channel Trench Power MOSFET

### Features

- 30V,150A
- $R_{DS(ON)}=1.9\text{m}\Omega$  (Typ.) @  $V_{GS}=10\text{V}$
- $R_{DS(ON)}=2.6\text{m}\Omega$  (Typ.) @  $V_{GS}=4.5\text{V}$
- Advanced Trench Technology
- Provide Excellent  $R_{DS(ON)}$  and Low Gate Charge

### Application


- Load Switch
- PWM Application
- Power management



Schematic diagram



Marking and pin assignment



TO-252 top view

### Absolute Maximum Ratings ( $T_c=25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter		Value	Units
$V_{DSS}$	Drain-Source Voltage		30	V
$V_{GSS}$	Gate-Source Voltage		$\pm 20$	V
$I_D$	Continuous Drain Current	$T_c = 25^\circ\text{C}$	150	A
		$T_c = 100^\circ\text{C}$	105	A
$I_{DM}$	Pulsed Drain Current <sup>note1</sup>		600	A
$E_{AS}$	Single Pulsed Avalanche Energy <sup>note2</sup>		180	mJ
$P_D$	Power Dissipation	$T_c = 25^\circ\text{C}$	130	W
$R_{\theta JC}$	Thermal Resistance, Junction to Case		1.15	$^\circ\text{C}/\text{W}$
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient		62	
$T_J, T_{STG}$	Operating and Storage Temperature Range		-55 to +175	°C

**Electrical Characteristics** ( $T_C=25^\circ\text{C}$  unless otherwise specified)

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Units
<b>Off Characteristic</b>						
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	$V_{GS}=0\text{V}, I_D=250\mu\text{A}$	30	-	-	V
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS}=30\text{V}, V_{GS}=0\text{V}, T_J=25^\circ\text{C}$	-	-	1	$\mu\text{A}$
		$V_{DS}=24\text{V}, V_{GS}=0\text{V}, T_J=125^\circ\text{C}$	-	-	10	
$I_{GSS}$	Gate to Body Leakage Current	$V_{DS}=0\text{V}, V_{GS}=\pm 20\text{V}$	-	-	$\pm 100$	nA
<b>On Characteristics</b>						
$V_{GS(\text{th})}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu\text{A}$	1.0	1.6	2.5	V
$R_{DS(\text{on})}$ note3	Static Drain-Source on-Resistance	$V_{GS}=10\text{V}, I_D=30\text{A}$	-	1.9	2.6	$\text{m}\Omega$
		$V_{GS}=4.5\text{V}, I_D=25\text{A}$	-	2.6	3.4	
$g_{FS}$	Forward Transconductance	$V_{DS}=5\text{V}, I_D=15\text{A}$	-	48	-	S
<b>Dynamic Characteristics</b>						
$C_{iss}$	Input Capacitance	$V_{DS}=25\text{V}, V_{GS}=0\text{V}, f=1.0\text{MHz}$	-	4800	-	pF
$C_{oss}$	Output Capacitance		-	735	-	pF
$C_{rss}$	Reverse Transfer Capacitance		-	420	-	pF
$Q_g$	Total Gate Charge	$V_{DS}=15\text{V}, I_D=24\text{A}, V_{GS}=4.5\text{V}$	-	40	-	nC
$Q_{gs}$	Gate-Source Charge		-	6	-	nC
$Q_{gd}$	Gate-Drain("Miller") Charge		-	19	-	nC
<b>Switching Characteristics</b>						
$t_{d(on)}$	Turn-on Delay Time	$V_{DS}=15\text{V}, I_D=1\text{A}, R_{GEN}=1\Omega, V_{GS}=10\text{V}$	-	20	-	ns
$t_r$	Turn-on Rise Time		-	32	-	ns
$t_{d(off)}$	Turn-off Delay Time		-	75	-	ns
$t_f$	Turn-off Fall Time		-	28	-	ns
<b>Drain-Source Diode Characteristics and Maximum Ratings</b>						
$I_s$	Maximum Continuous Drain to Source Diode Forward Current	-	-	150	-	A
$I_{SM}$	Maximum Pulsed Drain to Source Diode Forward Current	-	-	600	-	A
$V_{SD}$	Drain to Source Diode Forward Voltage	$V_{GS}=0\text{V}, I_s=30\text{A}$	-	-	1.2	V
$trr$	Body Diode Reverse Recovery Time	$I_s=1\text{A}, dI/dt=100\text{A}/\mu\text{s}$	-	49	85	ns
$Qrr$	Body Diode Reverse Recovery Charge		-	18	35	nC

Notes:1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature

2. EAS condition:  $T_J=25^\circ\text{C}, V_{DD}=25\text{V}, V_{GS}=10\text{V}, L=0.1\text{mH}, I_{AS}=60\text{A}, R_G=25\Omega$ 3. Pulse Test: Pulse Width  $\leq 300\mu\text{s}$ , Duty Cycle  $\leq 2\%$

## Typical Performance Characteristics




Figure 1: Gate Charge Test Circuit &amp; Waveform




Figure 2: Resistive Switching Test Circuit &amp; Waveforms







Figure 3: Unclamped Inductive Switching Test Circuit &amp; Waveforms



\*  $V_{GS} = 5V$  for Logic Level Devices

Figure 4:Peak Diode Recovery dv/dt Test Circuit & Waveforms (For N-channel)

## Package Information : TO-252



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	2.200	2.400	0.087	0.094
A1	0.000	0.127	0.000	0.005
b	0.660	0.860	0.026	0.034
c	0.460	0.580	0.018	0.023
D	6.500	6.700	0.256	0.264
D1	5.100	5.460	0.201	0.215
D2	4.830TYP.		0.190 TYP.	
E	6.000	6.200	0.236	0.244
e	2.186	2.386	0.086	0.094
L	9.800	10.400	0.386	0.409
L1	2.900 TYP.		0.114 TYP.	
L2	1.400	1.700	0.055	0.067
L3	1.600 TYP.		0.063 TYP.	
L4	0.600	1.000	0.024	0.039
Φ	1.100	1.300	0.043	0.051
θ	0°	8°	0°	8°
h	0.000	0.300	0.000	0.012
V	5.350 TYP.		0.211 TYP.	