



74LVC1G07Q

SINGLE BUFFER WITH OPEN DRAIN OUTPUT

Description

The 74LVC1G07Q is an automotive-compliant, single buffer with an open-drain output. The device is designed for operation with a power supply range of 1.65V to 5.5V. The inputs are tolerant to 5.5V allowing this device to be used in a mixed voltage environment. The device is fully specified for partial power down applications using IoFF. The IoFF circuitry disables the output preventing damaging current backflow when the device is powered down. The open-drain output can be connected to other open drain outputs to implement active-low wired-OR or active-high wired-AND functions. The maximum sink current is 32mA at 5V.

Pin Assignments

Applications


Voltage Level Shifting

General Purpose Logic

Range

Power Down Signal Isolation

Wide Array of Products such as:



Automotive applications within Grade 1 Temperature

Industrial Computing/Controls/Automation

Industrial/Agricultural Equipment

High Reliability Networking/Communications

Features

- Grade 1 Ambient Temperature Operation: -40°C to +125°C
- Wide Supply Voltage Range from 1.65V to 5.5V
- 24mA Sink Current at 3.3V
- CMOS Low Power Consumption
- IOFF Supports Partial-Power-Down Mode Operation
- Inputs Accept up to 5.5V Regardless of Vcc Level
- ESD Protection Tested per AEC-Q100
- Exceeds 2000V Human Body Model (AEC-Q100-002)
- Exceeds 1000V Charged Device Model (AEC-Q100-011)
- Latch-Up Exceeds 100mA (AEC-Q100-004)
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- The 74LVC1G07Q is suitable for automotive applications requiring specific change control; this part is AEC-Q100 qualified, PPAP capable, and manufactured in IATF 16949 certified facilities.

https://www.diodes.com/quality/product-definitions/

Notes:

- No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
 See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.



Pin Descriptions

Pin Name	Description
NC	No Connection
A	Data Input
GND	Ground
Y	Data Output
Vcc	Supply Voltage

Function Table

Input	Output
Α	Y
Н	Z
L	L


Absolute Maximum Ratings (Notes 4 & 5)

Symbol	Description	Rating	Unit
ESD HBM	Human Body Model ESD Protection	2	kV
ESD CDM	Charged Device Model ESD Protection	1	kV
Vcc	Supply Voltage Range	-0.5 to 6.5	V
VI	Input Voltage Range	-0.5 to 6.5	V
Vo	Voltage Applied to Output in High Impedance or IOFF State	-0.5 to 6.5	V
Vo	Voltage Applied to Output in High or Low State	-0.5 to Vcc +0.5	V
I _{IK}	Input Clamp Current VI < 0	-50	mA
loк	Output Clamp Current	-50	mA
lo	Continuous Output Current	50	mA
Icc, Ignd	Continuous Current Through Vcc or GND	±100	mA
TJ	Operating Junction Temperature	-40 to +150	°C
Tstg	Storage Temperature	-65 to +150	°C

Notes: 4. Stresses beyond the absolute maximum can result in immediate failure or reduced reliability. These are stress values and device operation should be within recommend values.

5. Forcing the maximum allowed voltage could cause a condition exceeding the maximum current or conversely forcing the maximum current could cause a condition exceeding the maximum voltage. The ratings of both current and voltage must be maintained within the controlled range.

Logic Diagram





Recommended Operating Conditions (Note 6)

Symbol		Parameter	Min	Max	Unit
\/	Operating Voltage	Operating	1.65	5.5	V
Vcc	Operating voltage	Data retention only	1.5	—	V
		Vcc = 1.65V to 1.95V	$0.65 \times Vcc$	_	
Maria	High-Level Input Voltage	Vcc = 2.3V to 2.7V	1.7	—	V
Vін	High-Level Input Voltage	$V_{CC} = 3V$ to 3.6V	2	—	v
		V _{CC} = 4.5V to 5.5V	$0.7\times V_{CC}$	—	
	/IL Low-Level Input Voltage	V _{CC} = 1.65V to 1.95V	—	$0.35 \times V_{CC}$	
.,		V _{CC} = 2.3V to 2.7V	—	0.7	V
VIL		V _{CC} = 3V to 3.6V	—	0.8	V
		Vcc = 4.5V to 5.5V	_	$0.3 \times V_{CC}$	
Vı	Input Voltage		0	5.5	V
Vo	Output Voltage		0	5.5	V
		Vcc = 1.65V	_	4	
		Vcc = 2.3V	_	8	
	Low Lovel Output Current	Vcc = 2.7V	—	12	mA
IOL	Low-Level Output Current		_	16	mA
		$V_{CC} = 3V$	—	24	
		$V_{CC} = 4.5V$	—	32	
		$V_{CC} = 1.8V \pm 0.15V, 2.5V \pm 0.2V$	—	20	
Δt/ΔV	Input Transition Rise or Fall Rate	$V_{CC} = 3.3V \pm 0.3V$	—	10	ns/V
		$V_{CC} = 5V \pm 0.5V$	_	5	
TA	Operating Free-Air Temperature	_	-40	+125	°C

Note: 6. Unused inputs should be held at V_{CC} or Ground.



Electrical Characteristics (All typical values are at V_{CC} = 3.3V, T_A = +25°C)

Symphol	Peremeter	Test Ca	nditiono	Vcc	-40°	C to +125°	2°	11:0:4
Symbol	Symbol Parameter		Test Conditions		Min	Тур	Max	Unit
		IoL = 100μA	1.65V to 5.5V	_	—	0.1		
			$I_{OL} = 4mA$	1.65V	_	—	0.45	
	V _{OL} Low Level Output Voltage		IoL = 8mA	2.3V	_	—	0.3	
Vol		VI = VIL	$I_{OL} = 12mA$	2.7V	—	_	0.4	V
			$I_{OL} = 24mA$	3V	_	—	0.55	-
			IoL = 32mA	4.5V	_	—	0.55	
lı	Input Current	VI = 5.5V or GN	ID	0 to 5.5V	_	±0.1	±1	μA
IOFF	Power Down Leakage Current	$V_1 \text{ or } V_0 = 5.5 V$		0V	_	—	±2	μA
loz	Z-State Leakage Current	VI = VIH, VO = 5	.5V	1.65V or 5.5V	_	±0.1	±2	μA
Icc	Supply Current	$V_I = 5.5V$ or GND, $I_O = 0$		5.5V	_	0.1	4	μA
Δlcc	Additional Supply Current	Input at Vcc – 0.6V		3V to 5.5V		—	500	μA
Cı	Input Capacitance	VI = Vcc to GNI)	3.3V		5.0	_	pF

Package Characteristics

Symbol	Parameter	Package	Test Conditions	Min	Тур	Max	Unit
0	Thermal Resistance	SOT25	Note 7	_	184	_	°C M
ALA	θ _{JA} Junction-to-Ambient	SOT353	Note 7	_	385	—	°C/W
0	Thermal Resistance	SOT25	Note 7	_	62	_	80AM
θJC	Junction-to-Case	SOT353	Note 7	_	164	—	°C/W

Note: 7. Device mounted on FR-4 substrate PC board, 2oz copper, with minimum recommended pad layout.

Switching Characteristics

Cincume 4 Truninel Val	$a = a + T_{i}$ $A = a + C = a + c + c + c + c + c + c + c + c + c +$
FIGURE T TVDICALVAI	es at $T_A = +25^{\circ}C$ and nominal voltages 1.8V, 2.5V, 2.7V, 3.3V, and 5.0V.


Parameter	From	То	To $T_A = -40^{\circ}C$				Unit	
Falameter	Input	Output	Vcc	Min	Тур	Max	Onit	
	t _{PD} A		1.8V ± 0.15V	1.0	2.6	8.4		
		Y		2.5V ± 0.2V 0.5	0.5	1.7	7.0	
t _{PD}			2.7V	0.5	2.3	6.0	ns	
		3.3V ± 0.3V	0.5	2.2	5.5			
		5.0V ± 0.5V	0.5	1.6	4.5			

Operating Characteristics

$T_A = +25^{\circ}C$								
Dowow of our		Test	Vcc = 1.8V	Vcc = 2.5V	Vcc = 3.3V	Vcc = 5V	l la li	
	Parameter		Тур	Тур	Тур	Тур	Unit	
Cpd	Power Dissipation Capacitance	f = 10MHz	5	5	6	6	pF	



Measurement Information




TEST	S 1	CLRL
t _{PLZ} /t _{PZL}	V _{LOAD}	Per Table

N.s.s	Inputs		V	Verse	C	D.	MA
Vcc	VI	t _R /t _F	VM	VM VLOAD CL R	RL	VΔ	
1.8V±0.15V	Vcc	≤2ns	Vcc/2	2 × Vcc	30pF	1kΩ	0.15V
2.5V±0.2V	Vcc	≤2ns	Vcc/2	2 × Vcc	30pF	500Ω	0.15V
2.7V	2.7V	≤2.5ns	1.5V	6V	50pF	500Ω	0.3V
3.3V±0.3V	3V	≤2.5ns	1.5V	6V	50pF	500Ω	0.3V
5V±0.5V	Vcc	≤2.5ns	Vcc/2	$2 \times Vcc$	50pF	500Ω	0.3V



Voltage Waveform Pulse Duration



Voltage Waveform Enable and Disable Times Low and High Level Enabling


Figure 1. Load Circuit and Voltage Waveforms

Notes:

- A. Includes test lead and test apparatus capacitance.
- B. All pulses are supplied at pulse repetition rate \leq 10MHz. C. The input is one transition per measurement.
- D. For the open drain device t_{PLZ} and t_{PZL} are the same as t_{PD} .
- E. t_{PZL} is measured at V_M.
- F. t_{PLZ} is measured at V_{OL} +V_{\Delta}.



Ordering Information (Note 8)





Part Number	Package	Package	Package	7" Tape	and Reel
Fart Number	Code	(Notes 9 & 10)	Size	Quantity	Part Number Suffix
74LVC1G07QSE-7	SE	SOT353	2.15mm × 2.1mm × 1.1mm 0.65mm lead pitch	3000/Tape & Reel	-7
74LVC1G07QW5-7	W5	SOT25	3.0mm × 2.8mm × 1.2mm 0.95mm lead pitch	3000/Tape & Reel	-7

Notes:

 For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.
 Pad layout as shown in Diodes Incorporated's package outline PDFs, which can be found on our website at http://www.diodes.com/package-outlines.html. 10. The taping orientation is located on our website at https://www.diodes.com/assets/Packaging-Support-Docs/ap02007.pdf.

Marking Information






Part Number	Package	Identification Code
74LVC1G07QW5-7	SOT25	UNQ
74LVC1G07QSE-7	SOT353	UNQ



Package Outline Dimensions


Please see http://www.diodes.com/package-outlines.html for the latest version.

(1) Package Type: SOT25



SOT25				
Dim	Min	Max	Тур	
Α	0.35	0.50	0.38	
В	1.50	1.70	1.60	
С	2.70	3.00	2.80	
D	-	-	0.95	
н	2.90	3.10	3.00	
J	0.013	0.10	0.05	
К	1.00	1.30	1.10	
L	0.35	0.55	0.40	
м	0.10	0.20	0.15	
Ν	0.70	0.80	0.75	
α	0°	8°	-	
All Dimensions in mm				

(2) Package Type: SOT353




SOT353				
Dim	Min	Max	Тур	
A1	0.00	0.10	0.05	
A2	0.90	1.00	0.95	
b	0.10	0.30	0.25	
Ċ	0.10	0.22	0.11	
D	1.80	2.20	2.15	
ш	2.00	2.20	2.10	
E1	1.15	1.35	1.30	
e	0.650 BSC			
F	0.40	0.45	0.425	
L	0.25	0.40	0.30	
а	0°	8°		
All Dimensions in mm				



Suggested Pad Layout


Please see http://www.diodes.com/package-outlines.html for the latest version.

(1) Package Type: SOT25



Dimensions	Value
Z	3.20
G	1.60
Х	0.55
Y	0.80
C1	2.40
C2	0.95

(2) Package Type: SOT353



Dimensions	Value (in mm)
С	0.650
C1	1.900
G	1.300
Х	0.420
X1	1.720
Y	0.600
Y1	2.500

Mechanical Data

SOT25

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 3
- Weight: 0.0158 grams (Approximate)

SOT353

- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 3
- Weight: 0.0064 grams (Approximate)



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

www.diodes.com