





WITHOUT COVER





WITH COVER

- 1.Contact Resistance:40mOHM Max.;
- 2.Dielectric Withstanding Voltage:100V AC For 1 Minute
- 3.Insulation Resistance:100M OHM Min.;
- 4.Mating And Unmating Force:
Mating Force:5~20N
Unmating Force:8~20N;
- 6~20N AFTER TEST:
- 5.Durability:10000 Cycles;



U263-24XN-4BQC16

- Mating Area plating
- 01: Au 1u"Min.
 - 03: Au 3u"Min.
 - 05: Au 5u"Min.
 - 10: Au 10u"Min.
 - 15: Au 15u"Min.
 - 30: Au 30u"Min.



RECOMMEND P.C.B LAYOUT (COMPONENT SIDE)

TOLERANCE FOR PCB LAYOUT IS ± 0.05
KEEP OUT AREA

Item	Title	Material	Dispose	Q'TY
1	Shell	SUS304	Ni:30u" Min.	1PCS
2	GND Plate	SUS301		2PCS
3	Mid Plate	SUS301		1PCS
4	Contact	C7025	Mating Area:See P/N Solder Tails:Matt Tin	2PCS
5	InsertMolding	LCP E6808	UL 94V-0 Black	1PCS
6	COVER	LCP E6808	UL 94V-0 Black	1PCS

					DSND	DATE	SCALE: N/A	MODEL TYPE: 3.1 TYPE C			
ΔX				ANGULAR		DATE	VIEW:	PART NO.:			
ΔX				L ≤ 4	±5°	DATE	UNIT: mm/in	DWG NO.:			
ΔX				4 < L ≤ 16	±0.2	DATE	SIZE: A4	U263-24XN-4BQC16			
MARK	DESCRIPTION	DATE	REVISED	16 < L ≤ 63	±0.3	DATE					
	REVISIONS			L > 63	±0.4						
				UNSPECIFIED TOLERANCES	±0.5						
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn								KXB INDUSTRIAL PRECISION CO., LIMITED	WEIGHT	SHEET	REVISION
								1.0g	1/1	A0	