

## *Four low power CMOS operational amplifiers*

### DESCRIPTION


The HT4336A is a quad low power CMOS operational amplifiers IC which provides high performance operation at low supply voltages. The basic amplifier can operate at supply voltage as low as 1.4V with very low power consumption and makes it perfect for battery-powered application. The input common-mode voltage extends to the negative rail. The output swings to both rails with light load. The input bias current is inherently low and the input impedance is extremely high. The devices are ideal upgrades for industrial standards operational amplifiers.

### FEATURES

- Low Power Replacement for Standard OP Amps
- Wide supply operating range (1.4V to 7V)
- Input common-mode voltage range includes negative rail
- Output swing to rail
- Low input bias current (typical 1pA)
- High input impedance
- Single supply operation
- Internal compensated
- Output short circuit protection

### APPLICATIONS

- Portable Instruments
- Battery-Powered Systems
- Transducer Interfacing
- Active Filter
- High Impedance Buffer




### ORDERING INFORMATION

HT4336ANZ DIP

HT4336ARZ SOP

TA = -40° to 85°C for all packages.



### PIN ASSIGNMENT

|         |   |    |        |
|---------|---|----|--------|
| OUT 1   | 1 | 14 | OUT 4  |
| IN1(-)  | 2 | 13 | IN4(-) |
| IN1(+)  | 3 | 12 | IN4(+) |
| CC      | 4 | 11 | GND    |
| IN2 (+) | 5 | 10 | IN3(+) |
| IN2 (-) | 6 | 9  | IN3(-) |
| OUT 2   | 7 | 8  | OUT 3  |

**ABSOLUTE MAXIMUM RATINGS**

| Characteristic                   | Symbol                             | Value              | Unit |
|----------------------------------|------------------------------------|--------------------|------|
| Power Supply Voltage             | V <sub>CC</sub>                    | 8                  | V    |
| Input and Output Voltage         | V <sub>IN</sub> , V <sub>OUT</sub> | V+ -0.3 to V- +0.3 | V    |
| Storage Temperature Range        | T <sub>stg</sub>                   | -65 ~ +150         | °C   |
| Ambient Temperature              | T <sub>A</sub>                     | -20 ~ 100          | °C   |
| Duration of output short circuit |                                    | Unlimited          |      |


NOTE: Stresses above those listed may cause permanent damage to the devices.

**ELECTRICAL CHARACTERISTICS** (V<sub>+</sub> = 5V, V<sub>-</sub> = 0V, T<sub>A</sub> = 25 °C, unless otherwise specified)


| Characteristic                  | Symbol               | Test Condition   | Min | Typ  | Max                  | Unit  |
|---------------------------------|----------------------|--|-----|------|----------------------|-------|
| Input Offset Voltage            | V <sub>IO</sub>      |  |     | 2    | 3                    | mV    |
| Input Offset Voltage Drift      | ΔV <sub>IO</sub> /ΔT |  |     | 0.7  |                      | µV/°C |
| Input Offset Current            | I <sub>IO</sub>      |  |     | 1    |                      | pA    |
| Input Bias Current              | I <sub>IB</sub>      | T <sub>A</sub> = 25 °C   |     | 1    |                      | pA    |
| Input Common Mode Voltage Range | V <sub>ICR</sub>     |  | 0   |      | V <sub>CC</sub> -1.3 | V     |
| Supply Current (per amplifier)  | I <sub>CC</sub>      |  |     | 5    | 9                    | µA    |
| Large Signal Voltage Gain       | A <sub>V</sub>       | V <sub>O</sub> =1V to 4V; V <sub>IN</sub> =1.4V; R <sub>L</sub> =1MΩ | 20  | 100  |                      | V/mV  |
| Output Voltage Swing            | V <sub>OH</sub>      | V <sub>IN</sub> =10mV; R <sub>L</sub> =1MΩ (to V-)                   | 4.9 | 4.99 |                      | V     |
|                                 |                      | V <sub>IN</sub> =10mV; R <sub>L</sub> =100KΩ (to V-)                 |     | 4.95 |                      |       |
|                                 |                      | V <sub>IN</sub> =10mV; R <sub>L</sub> =10KΩ (to V-)                  |     | 4.75 |                      |       |
|                                 | V <sub>OL</sub>      | V <sub>IN</sub> =-10mV; R <sub>L</sub> =1MΩ (to V+)                  |     | 0.5  | 0.7                  |       |
|                                 |                      | V <sub>IN</sub> =-10mV; R <sub>L</sub> =100KΩ (to V+)                |     | 0.65 |                      |       |
| Common Mode Rejection Ratio     | CMRR                 | V <sub>O</sub> =1V; V <sub>IN</sub> =0V to 3.5V;                     | 60  | 80   |                      | dB    |
| Power Supply Rejection Ratio    | PSRR                 | V <sub>O</sub> =1V   | 60  | 90   |                      | dB    |



**TYPICAL APPLICATION CIRCUIT**

## • VOLTAGE FOLLOWER





## • INSTRUMENT AMPLIFIER




**SSOP14**



| SYMBOL | MILLIMETER |      |       |
|--------|------------|------|-------|
|        | MIN        | NOM  | MAX   |
| A      | —          | —    | 1.75  |
| A1     | 0.10       | —    | 0.225 |
| A2     | 1.30       | 1.40 | 1.50  |
| A3     | 0.55       | 0.60 | 0.65  |
| b      | 0.23       | —    | 0.31  |
| b1     | 0.22       | 0.25 | 0.28  |
| c      | 0.20       | —    | 0.24  |
| c1     | 0.19       | 0.20 | 0.21  |
| D      | 4.80       | 4.90 | 5.00  |
| E      | 5.80       | 6.00 | 6.20  |
| E1     | 3.80       | 3.90 | 4.00  |
| e      | 0.635BSC   |      |       |
| h      | 0.25       | —    | 0.50  |
| L      | 0.50       | 0.65 | 0.80  |
| L1     | 1.05REF    |      |       |
| theta  | 0          | —    | 8°    |

**TSSOP14**


| SYMBOL | MILLIMETER |      |      |
|--------|------------|------|------|
|        | MIN        | NOM  | MAX  |
| A      | —          | —    | 1.20 |
| A1     | 0.05       | —    | 0.15 |
| A2     | 0.90       | 1.00 | 1.05 |
| A3     | 0.39       | 0.44 | 0.49 |
| b      | 0.20       | —    | 0.28 |
| b1     | 0.19       | 0.22 | 0.25 |
| c      | 0.13       | —    | 0.17 |
| c1     | 0.12       | 0.13 | 0.14 |
| D      | 4.90       | 5.00 | 5.10 |
| E      | 6.20       | 6.40 | 6.60 |
| e      | 0.65BSC    |      |      |
| L      | 0.45       | 0.60 | 0.75 |
| L1     | 1.00BSC    |      |      |
| theta  | 0          | —    | 8°   |

**SOP14**


| SYMBOL   | MILLIMETER |      |       |
|----------|------------|------|-------|
|          | MIN        | NOM  | MAX   |
| A        | —          | —    | 1.75  |
| A1       | 0.05       | —    | 0.225 |
| A2       | 1.30       | 1.40 | 1.50  |
| A3       | 0.60       | 0.65 | 0.70  |
| b        | 0.39       | —    | 0.47  |
| b1       | 0.38       | 0.41 | 0.44  |
| c        | 0.20       | —    | 0.24  |
| c1       | 0.19       | 0.20 | 0.21  |
| D        | 8.55       | 8.65 | 8.75  |
| E        | 5.80       | 6.00 | 6.20  |
| E1       | 3.80       | 3.90 | 4.00  |
| e        | 1.27BSC    |      |       |
| h        | 0.25       | —    | 0.50  |
| L        | 0.50       | —    | 0.80  |
| L1       | 1.05REF    |      |       |
| $\theta$ | 0          | —    | 8°    |

**DIP14**


| SYMBOL | MILLIMETER |       |       |
|--------|------------|-------|-------|
|        | MIN        | NOM   | MAX   |
| A      | 3.60       | 3.80  | 4.00  |
| A1     | 0.51       | —     | —     |
| A2     | 3.20       | 3.30  | 3.40  |
| A3     | 1.47       | 1.52  | 1.57  |
| b      | 0.44       | —     | 0.52  |
| b1     | 0.43       | 0.46  | 0.49  |
| B1     | 1.52REF    |       |       |
| c      | 0.25       | —     | 0.29  |
| c1     | 0.24       | 0.25  | 0.26  |
| D      | 19.00      | 19.10 | 19.20 |
| E1     | 6.25       | 6.35  | 6.45  |
| e      | 2.54BSC    |       |       |
| eA     | 7.62REF    |       |       |
| eB     | 7.62       | —     | 9.30  |
| eC     | 0          | —     | 0.84  |
| L      | 3.00       | —     | —     |