

## Description

Features	Application
<ul style="list-style-type: none"><li>• 30V,120A</li><li>• <math>R_{DS(ON)} &lt; 4.5\text{m}\Omega</math> @ <math>V_{GS} = 10\text{V}</math></li><li>• <math>R_{DS(ON)} &lt; 7.5\text{m}\Omega</math> @ <math>V_{GS} = 4.5\text{V}</math></li><li>• Advanced Trench Technology</li><li>• Provide Excellent <math>R_{DS(ON)}</math> and Low Gate Charge</li><li>• Lead free product is acquired</li></ul>	<ul style="list-style-type: none"><li>• Load Switch</li><li>• PWM Application</li><li>• Power management</li></ul> <p><i>100% UIS TESTED!</i> <i>100% <math>\Delta V_{ds}</math> TESTED!</i></p>

TO-252(DPAK) top view

Marking and pin Assignment

Schematic Diagram

## Absolute Maximum Ratings ( $T_c=25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter		Max.	Units
$V_{DSS}$	Drain-Source Voltage		30	V
$V_{GSS}$	Gate-Source Voltage		$\pm 20$	V
$I_D$	Continuous Drain Current	$T_c = 25^\circ\text{C}$	120	A
		$T_c = 100^\circ\text{C}$	68	A
$I_{DM}$	Pulsed Drain Current <sup>note1</sup>		380	A
$E_{AS}$	Single Pulsed Avalanche Energy <sup>note2</sup>		256	mJ
$P_D$	Power Dissipation	$T_c = 25^\circ\text{C}$	78	W
$R_{\theta JC}$	Thermal Resistance, Junction to Case		1.95	$^\circ\text{C}/\text{W}$
$T_J, T_{STG}$	Operating and Storage Temperature Range		-55 to +175	$^\circ\text{C}$



**Electrical Characteristics** ( $T_J=25^\circ\text{C}$  unless otherwise specified)

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Units
<b>Off Characteristic</b>						
$V_{(\text{BR})\text{DSS}}$	Drain-Source Breakdown Voltage	$V_{\text{GS}}=0\text{V}$ , $I_D=250\mu\text{A}$	30	-	-	V
$I_{\text{DSS}}$	Zero Gate Voltage Drain Current	$V_{\text{DS}}=30\text{V}$ , $V_{\text{GS}}=0\text{V}$ ,	-	-	1.0	$\mu\text{A}$
$I_{\text{GSS}}$	Gate to Body Leakage Current	$V_{\text{DS}}=0\text{V}$ , $V_{\text{GS}}=\pm 20\text{V}$	-	-	$\pm 100$	nA
<b>On Characteristics</b>						
$V_{\text{GS}(\text{th})}$	Gate Threshold Voltage	$V_{\text{DS}}=V_{\text{GS}}$ , $I_D=250\mu\text{A}$	1.0	1.5	2.5	V
$R_{\text{DS}(\text{on})}$ note3	Static Drain-Source on-Resistance	$V_{\text{GS}}=10\text{V}$ , $I_D=30\text{A}$	-	2.8	5.5	$\text{m}\Omega$
		$V_{\text{GS}}=4.5\text{V}$ , $I_D=20\text{A}$	-	5.5	7.5	
<b>Dynamic Characteristics</b>						
$C_{\text{iss}}$	Input Capacitance	$V_{\text{DS}}=15\text{V}$ , $V_{\text{GS}}=0\text{V}$ , $f = 1.0\text{MHz}$	-	2760	-	pF
$C_{\text{oss}}$	Output Capacitance		-	398	-	pF
$C_{\text{rss}}$	Reverse Transfer Capacitance		-	360	-	pF
$Q_g$	Total Gate Charge	$V_{\text{DS}}=15\text{V}$ , $I_D=30\text{A}$ , $V_{\text{GS}}=10\text{V}$	-	32	-	nC
$Q_{\text{gs}}$	Gate-Source Charge		-	7.8	-	nC
$Q_{\text{gd}}$	Gate-Drain("Miller") Charge		-	11.4	-	nC
<b>Switching Characteristics</b>						
$t_{\text{d}(\text{on})}$	Turn-on Delay Time	$V_{\text{DS}}=15\text{V}$ , $I_D=30\text{A}$ , $R_{\text{GEN}}=3\Omega$ , $V_{\text{GS}}=10\text{V}$	-	36	-	ns
$t_r$	Turn-on Rise Time		-	31	-	ns
$t_{\text{d}(\text{off})}$	Turn-off Delay Time		-	82	-	ns
$t_f$	Turn-off Fall Time		-	38	-	ns
<b>Drain-Source Diode Characteristics and Maximum Ratings</b>						
$I_S$	Maximum Continuous Drain to Source Diode Forward Current	-	-	120	A	
$I_{\text{SM}}$	Maximum Pulsed Drain to Source Diode Forward Current	-	-	380	A	
$V_{\text{SD}}$	Drain to Source Diode Forward Voltage	$V_{\text{GS}}=0\text{V}$ , $I_S=30\text{A}$	-	-	1.2	V
$\text{trr}$	Body Diode Reverse Recovery Time	$I_F=20\text{A}$ , $dI/dt=100\text{A}/\mu\text{s}$	-	28	-	ns
$Q_{\text{rr}}$	Body Diode Reverse Recovery Charge		-	21	-	nC


Notes:1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature

2. EAS condition:  $T_J=25^\circ\text{C}$ ,  $V_{\text{DD}}=20\text{V}$ ,  $V_G=10\text{V}$ ,  $R_G=25\Omega$ ,  $L=0.5\text{Mh}$ ,  $I_{\text{AS}}=32\text{A}$


3. Pulse Test: Pulse Width  $\leq 300\mu\text{s}$ , Duty Cycle  $\leq 0.5\%$

## Typical Performance Characteristics


**Figure 1: Output Characteristics**



**Figure 3: On-resistance vs. Drain Current**




**Figure 5: Gate Charge Characteristics**




**Figure 7. Maximum Safe Operating Area**


**Figure 2: Typical Transfer Characteristics**



**Figure 4: Body Diode Characteristics**



**Figure 6: Capacitance Characteristics**



**Figure 8.  $R_{DS(ON)}$  vs Junction Temperature**

### 30H12K/H (文件编号: S&CIC1869)




Figure 9.  $V_{GS(th)}$  vs Junction Temperature






Figure 11. Normalized Maximum Transient Thermal Impedance



### Test Circuit




Figure 1: Gate Charge Test Circuit & Waveform




Figure 2: Resistive Switching Test Circuit & Waveforms







Figure 3: Unclamped Inductive Switching Test Circuit & Waveforms

## TO-252 Package Information



SYMBOL	MILLIMETER		
	MIN	NOM	MAX
A	2.15	2.25	2.35
A1	0.00	0.06	0.12
B	0.96	1.11	1.26
b	0.59	0.69	0.79
b1	0.69	0.81	0.93
c	0.34	0.42	0.50
D	6.45	6.60	6.75
D1	5.23	5.33	5.43
E	5.95	6.10	6.25
e	2.286TYP.		
e1	4.47	4.57	4.67
L	9.90	10.10	10.30
L1	1.40	1.55	1.70
L2	0.60	0.80	1.00
θ	0°	4°	8°