

# FH3090D


## N-Channel Trench Power MOSFET

### Features

- 30V,90A
- $R_{DS(ON)}=3.6m\Omega$  (Typ.) @  $V_{GS}=10V$
- $R_{DS(ON)}=5.0m\Omega$  (Typ.) @  $V_{GS}=4.5V$
- Advanced Trench Technology
- Provide Excellent  $R_{DS(ON)}$  and Low Gate Charge

### Application

- Load Switch
- PWM Application
- Power management




Schematic diagram

### TO-252



Marking and pin assignment



TO-252 top view

### Absolute Maximum Ratings (T<sub>C</sub>=25°C unless otherwise specified)

| Symbol                            | Parameter                                       | Max.                   | Units |
|-----------------------------------|---|------------------------|-------|
| V <sub>DSS</sub>                  | Drain-Source Voltage                            | 30                     | V     |
| V <sub>GSS</sub>                  | Gate-Source Voltage                             | ±20                    | V     |
| I <sub>D</sub>                    | Continuous Drain Current                        | T <sub>C</sub> = 25°C  | 90    |
|                                   |   | T <sub>C</sub> = 100°C | 58    |
| I <sub>DM</sub>                   | Pulsed Drain Current <sup>note1</sup>           | 360                    | A     |
| E <sub>AS</sub>                   | Single Pulsed Avalanche Energy <sup>note2</sup> | 250                    | mJ    |
| P <sub>D</sub>                    | Power Dissipation                               | 90                     | W     |
| R <sub>θJC</sub>                  | Thermal Resistance, Junction to Case            | 1.67                   | °C/W  |
| T <sub>J</sub> , T <sub>STG</sub> | Operating and Storage Temperature Range         | -55 to +175            | °C    |

**Electrical Characteristics** ( $T_C=25^\circ\text{C}$  unless otherwise specified)

| Symbol  | Parameter   | Test Condition  | Min. | Typ. | Max.      | Units      |
|---|---|---|------|------|-----------|------------|
| <b>Off Characteristic</b>                                     |   |   |      |      |           |            |
| $V_{(BR)DSS}$   | Drain-Source Breakdown Voltage                            | $V_{GS}=0V, I_D=250\mu A$   | 30   | -    | -         | V          |
| $I_{DSS}$   | Zero Gate Voltage Drain Current                           | $V_{DS}=30V, V_{GS}=0V,$  | -    | -    | 1.0       | $\mu A$    |
| $I_{GSS}$   | Gate to Body Leakage Current                              | $V_{DS}=0V, V_{GS}=\pm 20V$   | -    | -    | $\pm 100$ | nA         |
| <b>On Characteristics</b>                                     |   |   |      |      |           |            |
| $V_{GS(th)}$  | Gate Threshold Voltage                                    | $V_{DS}=V_{GS}, I_D=250\mu A$                                       | 1.0  | 1.5  | 2.5       | V          |
| $R_{DS(on)}$  | Static Drain-Source on-Resistance<br><small>note3</small> | $V_{GS}=10V, I_D=30A$   | -    | 3.6  | 4.8       | m $\Omega$ |
|   |   | $V_{GS}=4.5V, I_D=20A$  | -    | 5    | 7.3       |            |
| $g_{FS}$  | Forward Transconductance                                  | $V_{DS}=5V, I_D=15A$  | -    | 28   | -         | S          |
| <b>Dynamic Characteristics</b>                                |   |   |      |      |           |            |
| $C_{iss}$   | Input Capacitance   | $V_{DS}=15V, V_{GS}=0V,$<br>$f=1.0\text{MHz}$                       | -    | 1950 | -         | pF         |
| $C_{oss}$   | Output Capacitance  |   | -    | 320  | -         | pF         |
| $C_{rss}$   | Reverse Transfer Capacitance                              |   | -    | 240  | -         | pF         |
| $Q_g$   | Total Gate Charge   | $V_{DS}=25V, I_D=20A,$<br>$V_{GS}=10V$                              | -    | 42   | -         | nC         |
| $Q_{gs}$  | Gate-Source Charge  |   | -    | 4    | -         | nC         |
| $Q_{gd}$  | Gate-Drain("Miller") Charge                               |   | -    | 14   | -         | nC         |
| <b>Switching Characteristics</b>                              |   |   |      |      |           |            |
| $t_{d(on)}$   | Turn-on Delay Time  | $V_{DS}=15V,$<br>$R_I=0.75\Omega, R_{GEN}=3\Omega,$<br>$V_{GS}=10V$ | -    | 13   | -         | ns         |
| $t_r$   | Turn-on Rise Time   |   | -    | 36   | -         | ns         |
| $t_{d(off)}$  | Turn-off Delay Time                                       |   | -    | 43   | -         | ns         |
| $t_f$   | Turn-off Fall Time  |   | -    | 16   | -         | ns         |
| <b>Drain-Source Diode Characteristics and Maximum Ratings</b> |   |   |      |      |           |            |
| $I_S$   | Maximum Continuous Drain to Source Diode Forward Current  |   | -    | -    | 90        | A          |
| $I_{SM}$  | Maximum Pulsed Drain to Source Diode Forward Current      |   | -    | -    | 360       | A          |
| $V_{SD}$  | Drain to Source Diode Forward Voltage                     | $V_{GS}=0V, I_S=30A$  | -    | -    | 1.2       | V          |
| $t_{rr}$  | Body Diode Reverse Recovery Time                          | $I_F=20A, di/dt=100A/\mu s$   | -    | 16   | -         | ns         |
| $Q_{rr}$  | Body Diode Reverse Recovery Charge                        |   | -    | 5    | -         | nC         |

Notes:1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature

2. EAS condition:  $T_J=25^\circ\text{C}, V_{DD}=30V, V_G=10V, L=0.5\text{mH}, R_G=25\Omega$

Typical Performance Characteristics

Figure 1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics







Figure 6: Capacitance Characteristics




**Figure 7:** Normalized Breakdown Voltage vs. Junction Temperature




**Figure 8:** Normalized on Resistance vs. Junction Temperature




**Figure 9:** Maximum Safe Operating Area



**Figure 10:** Maximum Continuous Drain Current vs. Case Temperature



**Figure.11:** Maximum Effective Transient Thermal Impedance, Junction-to-Case (TO-252)






Figure1:Gate Charge Test Circuit & Waveform




Figure 2: Resistive Switching Test Circuit & Waveforms




Figure 3:Unclamped Inductive Switching Test Circuit & Waveforms






Figure 4: Peak Diode Recovery  $dv/dt$  Test Circuit & Waveforms (For N-channel)

## Package Information : TO-252



| Symbol | Dimensions In Millimeters |        | Dimensions In Inches |       |
|--------|---------------------------|--------|----------------------|-------|
|        | Min.                      | Max.   | Min.                 | Max.  |
| A      | 2.200                     | 2.400  | 0.087                | 0.094 |
| A1     | 0.000                     | 0.127  | 0.000                | 0.005 |
| b      | 0.660                     | 0.860  | 0.026                | 0.034 |
| c      | 0.460                     | 0.580  | 0.018                | 0.023 |
| D      | 6.500                     | 6.700  | 0.256                | 0.264 |
| D1     | 5.100                     | 5.460  | 0.201                | 0.215 |
| D2     | 4.830 TYP.                |        | 0.190 TYP.           |       |
| E      | 6.000                     | 6.200  | 0.236                | 0.244 |
| e      | 2.186                     | 2.386  | 0.086                | 0.094 |
| L      | 9.800                     | 10.400 | 0.386                | 0.409 |
| L1     | 2.900 TYP.                |        | 0.114 TYP.           |       |
| L2     | 1.400                     | 1.700  | 0.055                | 0.067 |
| L3     | 1.600 TYP.                |        | 0.063 TYP.           |       |
| L4     | 0.600                     | 1.000  | 0.024                | 0.039 |
| φ      | 1.100                     | 1.300  | 0.043                | 0.051 |
| θ      | 0°                        | 8°     | 0°                   | 8°    |
| h      | 0.000                     | 0.300  | 0.000                | 0.012 |
| V      | 5.350 TYP.                |        | 0.211 TYP.           |       |