

Specification for Approval

Date: 2021/12/27

Customer : 立创

TAI-TECH P/N: HCE1012GH900BP

CUSTOMER P/N: _____

DESCRIPTION: _____

QUANTITY: _____

REMARK:	
Customer Approval Feedback	

西北臺慶科技股份有限公司
TAI-TECH Advanced Electronics Co., Ltd

代理商:
 深圳市天诚科技有限公司
 Shenzhen TsaSun Technology Co., Ltd.
 Room 209, 2/F, Block A, Tengfei Industrial Building, No.6,
 Taohua Road, Futian District, Shenzhen
 TEL: 0755-8335 8885 / 0755-8335 9885
 E-mail: sales@tsasun.com
 www.tsacoil.com

Sales Dep.

APPROVED	CHECKED
夏晓曼	夏晓曼

西北臺慶科技股份有限公司
 TAI-TECH Advanced Electronics Co., Ltd
Headquarter:
 NO.1 YOU 4TH ROAD, YOUTH INDUSTRIAL DISTRICT, YANG-MEI,
 TAO-YUAN HSIEN, TAIWAN, R.O.C.
 TEL: +886-3-4641148 FAX: +886-3-4643565
 http://www.tai-tech.com.tw
 E-mail: sales@tai-tech.com.tw

臺慶精密電子(昆山)有限公司
 TAI-TECH ADVANCED ELECTRONICS(KUNSHAN) CO., LTD
 SHINWHA ROAD, KUNJIA HI-TECH INDUSTRIAL PARK, KUN-SHAN,
 JIANG-SU, CHINA
 TEL: +86-512-57619396 FAX: +86-512-57619688
 E-mail: hui@tai-tech.com.tw

R&D Center

APPROVED	CHECKED	DRAWN
羅宜春	梁周虎	卜文娟

HCE1012GH900 (Chip Common Mode Filter plus ESD function)

Engineering Specification



Features and Application

- Powerful components with composite co-fired material to solve EMI problem for high speed differential signal transmission line as USB, and LVDS, without distortion to high speed signal transmission.
- Common mode filter plus ESD function.
- MIPI, MHL serial interface in mobile device.

1.PRODUCT DETAIL

Part No.	Imp. Com. (Ω)±25% @100MHz	DCR Max. (Ω)	Rated Current Max. (mA)	Rated Voltage (V)	Insulation Resistance Min. (MΩ)	Capacitance @0.5V 1MHz Max(pF)	Leakage Current @5V Max(μA)	Trigger Voltage Typ. (V)	Clamping Voltage Typ. (V)
HCE1012GH 900BP	90	1.5	100	10	100	1.3	1	400	50
•Meet IEC61000-4-2 level 4: Contact Discharge 8KV · Air Discharge 15KV									
Test Instruments	<ul style="list-style-type: none"> • Agilent E4991A RF IMPEDANCE / MATERIAL ANALYZER • HP4338A/B MILLIOHMMETER • Agilent E5071C S-PARAMETER NETWORK ANALYZER • HP6632B SYSTEM DC POWER SUPPLY • Keithley 2410 1100V SOURCE METER 								

2.PART NUMBER CODE


HCE 1012 G □ 90 0 □ P
 1 2 3 4 5 6 7 8

- 1 : Series name
- 2 : Dimensions L*W
- 3 : Material code
- 4 : Product identification number
- 5 : Impedance value (ex : 900=90Ω)
- 6 : Fixed decimal point
- 7 : INPAQ internal code
- 8 : Packaging style
P - Embossed paper tape, 7" reel


3.TYPICAL CHARACTERISTIC

HCE1012GH900


IMPEDANCE vs. FREQUENCY CHARACTERISTICS



INSERTION LOSS vs. FREQUENCY CHARACTERISTICS




Eye pattern USB 2.0 high speed




ESD Wave forms

IEC 8KV_ESD Contact






4. SHAPES AND DIMENSIONS




TYPE	Dimension
L	1.25±0.10
W	1.00±0.10
T	0.60±0.10
P	0.50±0.10
C1	0.30±0.10
C2	0.20±0.15
G1	0.30±0.15
G2	0.20±0.15
Unit : mm	

5. CIRCUIT CONFIGURATION & LAYOUT PAD



6.TAPE AND REEL SPECIFICATIONS/ TAPING DIMENSIONS


Type : Paper Carrier



Unit : mm

Symbol	Size	Symbol	Size
C	8.00±0.10	H	4.00±0.10
D	3.50±0.05	J	Φ1.55±0.05
E	1.75±0.05	T	0.75±0.03
F	4.00±0.10	A	1.20±0.05
G	2.00±0.05	B	1.45±0.05

7. REEL DIMENSIONS



Unit : mm


8. STANDARD QUANTITY FOR PACKAGING

Packaging style : Taping

Reel packaging quantity : 4000 pcs/reel

Inner box : 5 reel/inner box

9.RECOMMENDED SOLDERING CONDITIONS



10.GENERAL TECHNICAL DATA

Operating temperature range : - 40°C ~ +85°C

Storage Condition : Less than 40°C and 70% RH

Storage Time: 6 months Max.

Soldering method: Reflow or Wave Soldering

11.NOTE

All the products in this specification comply with RoHS 1.0 directive.