

US1A THRU US1M

1.0AMP Ultra Fast Recovery Silicon Rectifier

Features

- · Low Power Loss, High Efficiency
- · Ideally Suited for Automatic Assembly
- Guard Ring Die Construction
- Plastic Case Material has UL Flammability Classification Rating 94V- 0

Mechanical Data


. Case: Molded plastic SMA

 Terminals: Plated leads solderable per MIL-STD-750, Method 2026 guaranteed

· Polarity: Color band dentes cathode end

• Mounting Position: Any

· Making: Type Number



Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified Single phase,half wave,60Hz,resistive or inductive load For capacitive load derate current by 20%

Type Number	SYMBOL	US1A	US1B	US1D	US1G	US1J	US1K	US1M	Unit
Maximum Recurrent Peak Reverse Voltage	VRRM	50	100	200	400	600	800	1000	٧
Maximum RMS Voltage	V _{RMS}	35	70	140	280	420	560	700	٧
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	٧
Average Rectified Output Current @TL =100°C	IF(AV)	1.0							Α
Non-Repetitive Peak Forward Surge $@T_{j=25}$ $^{\circ}$ C Current 8.3ms Single half sine-wave $@T_{j=125}$ $^{\circ}$ C Superimposed On Rated Load (JEDEC Method)	Ігѕм	30 24							А
Non-Repetitive Peak Forward Surge @T _{j=25} °C Current 1.0ms Single half sine-wave @T _{j=125} °C Superimposed On Rated Load (JEDEC Method)	IFSM	60 48							А
10000 times of the wave surge current (time width 1ms, time interval 3s)	Ігэм	22.5							А
Rating for fusing (t<8.3ms)	l²t	3.74							A ² s
Forward Voltage @IF=1.0A	V _{FM}		1.0		1.3		1.7		V
Peak Reverse Current @T _A =25 °C At Rated DC Blocking Voltage @T _A =125 °C	lR	5.0 200							uA
Maximum Reverse Recovery Time (Note 1)	Trr	50 75					ns		
Typical Junction Capacitance (Note 2)	CJ	8						pF	
Typical Thermal Resistance (Note 3)	Re jl Re ja	27 70						°C/W	
Operating and Storage Temperature Range	T_J, T_{STG}	-55 to+150						$^{\circ}$ C	

Note: 1.Reverse Recovery Test Conditions:IF=0.5A,IR=1.0A,IRR=0.25A.

- 2. Measured at 1.0 MHz and Applied reverse Voltage of 4.0V D.C
- $3. \ \, \text{Device mounted on FR-4 substrate, 1"*1", 2oz, single-sided, PC boards with 0.1"*0.15" copper pad.}$

version:06 1of3



AVERGE FORWARD RECTIFIED CURRENT, (A) FIG.1MAXIMUM AVERAGE FORWARD CURRENT DERATING





FIG.3MAXIMUM NON-REPEITIVE SURGE CURRENT






FIG.2TYPICAL FORWARD CHARACTERISTICS






FIG.4TYPICAL JUNCTION CAPACITANCE



SMA PAD LAYOUT



version:06 2of3



US1A THRU US1M

1.0AMP Ultra Fast Recovery Silicon Rectifier

Important Notice and Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from XINNUO
- XINNUO reserves the right to make changes to this document and its products and specifications
- XINNUO disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- XINNUO does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the here in document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications.
 - XINNUO makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown here in are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own ris k andagree to fully indemnify XINNUO for any damages resulting from such improper use or sale.
- Since XINNUO uses lot number as the tracking base, please provide the lot number for tracking when complaining.

version:06 3of3