

# UNISONIC TECHNOLOGIES CO., LTD

**MCR100 SCR** 


## SENSITIVE GATE SILICON CONTROLLED RECTIFIERS REVERSE BLOCKING **THYRISTORS**

#### **DESCRIPTION**

PNPN devices designed for high volume, line-powered consumer applications such as relay and lamp drivers, small motor controls, gate drivers for larger thyristors, and sensing and detection circuits.

#### **FEATURES**


- \* Sensitive gate allows triggering by micro controllers and other logic circuits
- \* Blocking voltage to 600V
- \* On-state current rating of 0.8A RMS at 80°C
- \* High surge current capability 10A
- \* Minimum and maximum values of I<sub>GT</sub>, V<sub>GT</sub> and I<sub>H</sub> specified for ease of design
- \* Immunity to dV/dt 20V/µsec minimum at 110°C
- \* Glass-passivated surface for reliability and uniformity



#### **ORDERING INFORMATION**

Ordering Number		Dookogo	Pin assignment			Dooking
Lead Free	Halogen Free	Package	1	2	3	Packing
MCR100L-4-AA3-R	MCR100G-4-AA3-R	SOT-223	K	Α	G	Tape Reel
MCR100L-4-AB3-R	MCR100G-4-AB3-R	SOT-89	G	Α	K	Tape Reel
MCR100L-4-AE3-R	MCR100G-4-AE3-R	SOT-23	K	G	Α	Tape Reel
MCR100L-4-T92-B	MCR100G-4-T92-B	TO-92	K	G	Α	Tape Box
MCR100L-4-T92-K	MCR100G-4-T92-K	TO-92	K	G	Α	Bulk
MCR100L-6-AA3-R	MCR100G-6-AA3-R	SOT-223	K	Α	G	Tape Reel
MCR100L-6-AB3-R	MCR100G-6-AB3-R	SOT-89	G	Α	K	Tape Reel
MCR100L-6-AE3-R	MCR100G-6-AE3-R	SOT-23	K	G	Α	Tape Reel
MCR100L-6-T92-B	MCR100G-6-T92-B	TO-92	K	G	Α	Tape Box
MCR100L-6-T92-K	MCR100G-6-T92-K	TO-92	K	G	Α	Bulk
MCR100L-8-AA3-R	MCR100G-8-AA3-R	SOT-223	K	Α	G	Tape Reel
MCR100L-8-AB3-R	MCR100G-8-AB3-R	SOT-89	G	Α	K	Tape Reel
MCR100L-8-AE3-R	MCR100G-8-AE3-R	SOT-23	K	G	Α	Tape Reel
MCR100L-8-T92-B	MCR100G-8-T92-B	TO-92	K	G	Α	Tape Box
MCR100L-8-T92-K	MCR100G-8-T92-K	TO-92	K	G	Α	Bulk

Note: Pin assignment: K: Cathode A: Anode G: Gate



MCR100

### **■** MARKING

Package	MCR100-4	MCR100-6	MCR100-8		
SOT-223	MCR100 L: Lead Free  G: Halogen Free  Date Code	MCR100 L: Lead Free G: Halogen Free  Date Code	MCR100☐ L: Lead Free  B: Code  Code		
SOT-89	Date Code L: Lead Free G: Halogen Free	Date Code L: Lead Free G: Halogen Free	Date Code L: Lead Free G: Halogen Free		
SOT-23	☐ L: Lead Free → G: Halogen Free	R6☐ L: Lead Free  G: Halogen Free	R8☐ L: Lead Free G: Halogen Free		
TO-92	UTC  MCR100□ L: Lead Free  G: Halogen Free  Date Code	UTC  MCR100□  -6  □□□  C: Lead Free  G: Halogen Free  Date Code	UTC MCR100□ L: Lead Free G: Halogen Free Date Code		

MCR100 scr

#### **■ ABSOLUTE MAXIMUM RATINGS**

PARAMETER	SYMBOL	RATINGS	UNIT	
Peak Repetitive Off-State Voltage(Note 1) MCR100-4			200	V
(T <sub>J</sub> =-40 ~ 110°C, Sine Wave, 50 ~ 60Hz; MCR100-6		$V_{DRM}, V_{RRM}$	400	V
Gate Open)	MCR100-8		600	V
On-Sate RMS Current (Tc=80°C) 180°C Cc	ondition Angles	$I_{T(RMS)}$	0.8	Α
Peak Non-Repetitive Surge Current (1/2 cycle, Sine Wave, 60Hz, T <sub>J</sub> =25°C)		I <sub>TSM</sub>	10	Α
Circuit Fusing Considerations (t=8.3 ms)	l <sup>2</sup> t	0.415	$A^2s$	
Forward Peak Gate Power (T <sub>A</sub> =25°C, Pulse	$P_GM$	0.1	W	
Forward Average Gate Power (T <sub>A</sub> =25°C, t=	$P_{G(AV)}$	0.01	W	
Peak Gate Current - Forward (TA=25°C, Pu	$I_{GM}$	1	Α	
Peak Gate Voltage - Reverse (T <sub>A</sub> =25°C, Pt	$V_{GRM}$	5	V	
Operating Junction Temperature Range (Rated V <sub>RRM</sub> and V <sub>DRM</sub> )	TJ	-40 ~ +110	°C	
Storage Temperature Range	$T_{STG}$	-40 ~ +150	°C	

Note: Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.

#### **■ THERMAL DATA**

PARAMETER		SYMBOL	MAX	UNIT	
		SOT-223		180	°C/W
Junction to Ambient		SOT-23/SOT-89	$\theta_{JA}$	400	°C/W
		TO-92		200	°C/W

#### ■ **ELECTRICAL CHARACTERISTICS** (T<sub>J</sub>=25°C, unless otherwise stated)


PARAMETER		SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
OFF CHARACTERISTICS							
Peak Forward or Reverse Blocking	T <sub>C</sub> =25°C		$V_D$ =Rated $V_{DRM}$ and $V_{RRM}$ ;			10	μA
Current	T <sub>C</sub> =110°C	IDRM, IRRM	$V_D$ =Rated $V_{DRM}$ and $V_{RRM}$ , $R_{GK}$ =1k $\Omega$			100	μΑ
ON CHARACTERISTICS							
Peak Forward On-State Voltage (Note 2)		$V_{TM}$	I <sub>TM</sub> =1A Peak @ T <sub>A</sub> =25°C			1.7	V
Gate Trigger Current (Continuous DO	C) (Note 3)	$I_{GT}$	$V_{AK}$ =7Vdc, $R_L$ =100 $\Omega$ , $T_C$ =25 $^{\circ}$ C	30		100	μΑ
Holding Current	T <sub>C</sub> =25°C	I <sub>H</sub>	V <sub>AK</sub> =7Vdc, initiating		0.5	5	mA
	T <sub>C</sub> =-40°C		current=20mA			10	mA
Latch Current	T <sub>C</sub> =25°C	- IL	V <sub>AK</sub> =7V, Ig=200μA		0.6	10	mA
	T <sub>C</sub> =-40°C					15	mA
Gate Trigger Voltage	T <sub>C</sub> =25°C	\/	V <sub>AK</sub> =7Vdc, R <sub>I</sub> =100Ω		0.62	0.8	V
(continuous dc)	T <sub>C</sub> =-40°C	V <sub>GT</sub>	VAK-7 VUC, RL-10002			1.2	V
DYNAMIC CHARACTERISTICS							
			V <sub>D</sub> =Rated V <sub>DRM</sub> , Exponential				
Critical Rate of Rise of Off-State Volt	age	d <sub>∨</sub> /dt	Waveform, R <sub>GK</sub> =1000Ω,	20	35		V/µs
			T <sub>J</sub> =110°C				
Critical Rate of Rise of On-State Current		di/dt	I <sub>PK</sub> =20A; Pw=10μsec;			50	Λ/us
Childa Rate of Rise of On-State Current		ui/ut	diG/dt=1A/µsec, lgt=20mA			50	A/µs

Notes: 1.  $V_{DRM}$  and  $V_{RRM}$  for all types can be applied on a continuous basis. Ratings apply for zero or negative gate voltage; however, positive gate voltage shall not be applied concurrent with negative potential on the anode. Blocking voltages shall not be tested with a constant current source such that the voltage ratings of the devices are exceeded.


- 2. Indicates Pulse Test Width $\leq$ 1.0ms, duty cycle  $\leq$ 1%.
- 3. Does not include RGK in measurement.


#### ■ VOLTAGE CURRENT CHARACTERISTIC OF SCR


PARAMETER	SYMBOL
Peak Repetitive Off Stat Forward Voltage	V <sub>DRM</sub>
Peak Forward Blocking Current	I <sub>DRM</sub>
Peak Repetitive Off State Reverse Voltage	V <sub>RRM</sub>
Peak Reverse Blocking Current	I <sub>RRM</sub>
Peak On State Voltage	$V_{TM}$
Holding Current	I <sub>H</sub>





#### ■ TYPICAL CHARACTERISTICS














MCR100 scr

UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. UTC reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.