

Hand-Held Instruments

- PCMCIA Cards
- MP3/MP4/MP5 Players
- Portable Information Appliances

FEATURES

- Ultra-low Noise
- Ultra-Fast Response in Line/Load Transient
- <0.1µA Standby Current When Shutdown
- Low Dropout: 230mV@300mA
- Wide Operating Voltage Ranges: 2V to 5.5V
- Low Temperature Coefficient
- Current Limiting Protection
- Thermal Shutdown Protection
- Only 1μF Output Capacitor Required for Stability
- High Power Supply Rejection Ratio
- Fast output discharge
- Available in SOT23-5 Package


APPLICATIONS

- Cellular and Smart Phones
- Cordless Telephones
- Battery-Powered Equipment
- · Laptop, Palmtops, Notebook Computers


DESCRIPTION

The BL9161 is designed for portable applications with demanding performance and space requirements. The BL9161 performance is optimized for battery-powered systems to deliver ultra low noise and low quiescent current. Regulator ground current increases only slightly in dropout, further prolonging the battery life. The BL9161 also works with low-ESR ceramic capacitors, reducing the amount of board space necessary for power applications, critical in hand-held wireless devices. The BL9161 consumes less than 0.1µA in shutdown mode and has fast turn-on time (Typical 50µs). The other features include ultra low dropout voltage, high output accuracy, current limiting protection, and high ripple rejection ratio. Available in SOT23-5 package.

ORDERING INFORMATION



TYPICAL APPLICATION



Application hints:

Output capacitor (C2 > 2.2uF) is recommended in BL9161-1.5V and BL9161-1.8V application to assure the stability of circuit.





Absolute Maximum Rating (Note 1)

Input Supply Voltage (VIN) EN Pin Input Voltage Output Voltages Output Current


-0.3V to +6V -0.3V to VIN -0.3V to VIN+0.3V 300mA Maximum Junction Temperature 150°C

Operating Temperature Range (Note2) -40°C to 85°C

Storage Temperature Range -65°C to 125°C

Lead Temperature (Soldering, 10s) 300°C

Package Information



CKU: Chip ID
X: Output voltage
Y: Data code--Year
W: Data code—Week

Thermal Resistance (Note 3):

Package	Θ_{JA}	θ _{JC}
SOT23-5	250℃/W	130°C/W

X	С	D	G	- 1	K
Output voltage	1.5V	1.8V	2.8V	3.0V	3.3V

Y	4	5	О		U			
Year	2014	2015	2016		2020	2021		
W	Α		Υ	Z	а		у	Z
Week	1		25	26	27		51	52

Note 1: Absolute Maximum Ratings are those values beyond which the life of a device may be impaired.

Note 2: The BL9161 is guaranteed to meet performance specifications from 0°C to 70°C. Specifications over the –40°C to 85°C operating temperature range are assured by design, characterization and correlation withstatistical process controls.


Note 3: Thermal Resistance is specified with approximately 1 square of 1 ozcopper.



Pin Description

PIN	NAME	FUNCTION			
1	VIN	Power Input Voltage.			
2	GND	Ground.			
3	EN	Chip Enable Pin, This pin has an internal pull-down resistor			
4	NC	No Connection.			
5	VOUT	Output Voltage.			

Block Diagram





Electrical Characteristics (Note 4)

(V_{IN}=Vout +1V, EN=V_{IN}, C_{IN}=C_{OUT}=1 μ F, T_A=25 $^{\circ}$ C, unless otherwise noted.)

Pa	rameter	Symbol	Conditions	MIN	TYP	MAX	unit
Input Voltage		V _{IN}		2		5.5	V
Output Voltage Accuracy		ΔV_{OUT}	V _{IN=} Vout+1V, I _{OUT} =1mA	-2		+2	%
Cur	rent Limit	I _{LIM}	R_{LOAD} =1 Ω	360	450		mA
Quieso	cent Current	IQ	V _{EN} >1.2V, I _{OUT} =0mA		70	110	μΑ
Drope	out Voltage	V_{DROP}	I _{OUT} =200mA, V _{OUT} =3.3V		150	200	- mV
Бюрс	out voltage	▼ DROP	I _{OUT} =300mA, V _{OUT} =3.3V		230	300	
Line Reç	gulation ^(Note 5)	ΔV_{LINE}	V _{IN} =Vout+1V to 5.5V I _{OUT} =1mA		0.02	0.17	%/V
Load Re	egulation(Note6)	ΔV_{LOAD}	1mA <i<sub>OUT<300mA</i<sub>		20		mV
Output Voltage(Note 7) Temperature Coefficient		TC _{VOUT}	I _{OUT} =1mA		±60		ppm/℃
Stand	Standby Current		V _{EN} =GND, Shutdown		0.01	1	μА
EN Inpu	t Bias Current	I _{IBSD}	V _{EN} =GND or V _{IN}			2	μΑ
EN Input	Logic Low	V _{IL}	V _{IN} =3V to 5.5V, Shutdown			0.4	V
Threshold	Logic High	V _{IH}	V _{IN} =3V to 5.5V, Start up	1.2			V
Output Noise Voltage		e _{NO}	10Hz to100KHz, I _{OUT} =100mA		150		μV_{RMS}
Power	f=217Hz				-78		
Supply	f=1KHz	PSRR	I _{OUT} =10mA		-71		dB
Rejection Ratio	f=10KHz	1			-53		1
Therma	Thermal Shutdown Temperature		Shutdown, Temp increasing		170		$^{\circ}$
Therm: Hy	al Shutdown	T _{SDHY}	_		30		$^{\circ}$ C

Note 4: Production test at +25°C. Specifications over the temperature range are guaranteed by design and characterization. Note 5: Line regulation is calculated by
$$\Delta V_{LINE} = \left| \left(\frac{V_{OUT_1} - V_{OUT_2}}{\Delta V_{IN} \times V_{OUT_{(normal)}}} \right) \right| \times 100$$

Where V_{OUT1} is the output voltage when V_{IN} =5.5V, and V_{OUT2} is the output voltage when V_{IN} =4.3V,

 ΔV_{IN} =1.2V. V_{OUT} (normal) =3.3V.

Note 6: Load regulation is calculated by V_{load}=Vout1-Vout2

Where V_{OUT1} is the output voltage when I_{OUT}=1mA, and V_{OUT2} is the output voltage when I_{OUT}=300mA.


Note 7: The temperature coefficient is calculated by $TC_{T_{OLT}} = \frac{\Delta V_{OLT}}{\Delta T \times V_{OLT}}$


www.belling.com.cn 4 V1.0




Typical Performance Characteristics

Output Voltage Vs. Temperature







Dropout Voltage Vs. Load Current



PSRR




EN Pin Shutdown Threshold Vs. Temperature









Load Transient Response




Load Transient Response




Line transient Response



Start up



EN Pin Shutdown Response







Applications Information

Like any low-dropout regulator, the external capacitors used with the BL9161 must be carefully selected for regulator stability and performance. Using a capacitor whose value is $> 1\mu F$ on the BL9161 input and the amount of capacitance can be increased without limit. The input capacitor must be located a distance of not more than 0.5 inch from the input pin of the IC and returned to a clean analog ground. Any good quality ceramic or tantalum can be used for this capacitor. The capacitor with larger value and lower ESR (equivalent series resistance) provides better PSRR and line-transient response. The output capacitor must meet both requirements for minimum amount of capacitance and ESR in all LDOs application. The BL9161 is designed specifically to work with low ESR ceramic output capacitor in space-saving and performance consideration. Using a ceramic capacitor whose value is at least 1µF with ESR is > $25m\Omega$ on the BL9161 output ensures stability. The BL9161 still works well with output capacitor of other types due to the wide stable ESR range. Output capacitor of larger capacitance can reduce noise and improve load transient response, stability, and PSRR. The output capacitor should be located not more than 0.5 inch from the Vout pin of the BL9161 and returned to a clean analog ground.

Enable Function

The BL9161 features an LDO regulator enable/disable function. To assure the LDO regulator will switch on; the EN turn on control level must be greater than 1.2 volts. The LDO regulator will go into the shutdown mode when the voltage on the EN pin falls below 0.4 volts. For to protect the system, the BL9161 have a quick discharge function. If the enable function is not needed in a specific application, it may be tied to V_{IN} to keep the LDO regulator in a continuously on state.

Thermal Considerations

Thermal protection limits power dissipation in BL9161. When the operation junction temperature exceeds 170°C, the OTP circuit starts the thermal shutdown function turn the pass element off. The pass element turns on again after the junction temperature cools by 30°C.

For continue operation, do not exceed absolute maximum operation junction temperature 125°C. The power dissipation definition in device is:

$$P_D(MAX) = (T_J(MAX) - T_A)/\theta_{JA}$$

Where T_J(MAX) is the maximum operation junction temperature 125°C, TA is the ambient temperature and the θ_{JA} is the junction to ambient thermal resistance. For recommended operating conditions specification of BL9161, where T_J(MAX) is the maximum junction temperature of the die (125°C) and T_A is the maximum ambient temperature. The junction to ambient thermal resistance (θ_{JA} is layout dependent) for SOT-23-5 package is 250°C/W, on standard JEDEC 51-3 thermal test board. The maximum power dissipation at T_A = can be calculated by following 25°C formula:





 $P_D(MAX) = (125^{\circ}C-25^{\circ}C)/250 = 400$ mW (SOT-23-5)

The maximum power dissipation depends on operating ambient temperature for fixed $T_J(MAX)$ and thermal resistance θ_{JA} . It is also useful to calculate the junction of temperature of the BL9161 under a set of specific conditions. In this example let the Input voltage V_{IN} =3.3V, the output current Io=300mA and the case temperature T_A =40°C measured by a thermal couple during operation. The power dissipation for the V_{OUT} =2.8V version of the BL9161 can be calculated as:

$$P_D = (3.3V-2.8V) \times 300mA + 3.6V \times 100uA$$

=150mW

And the junction temperature, T_J, can be calculated as follows:

$$T_J=T_A+P_D\times\theta_{JA}=40^{\circ}C+0.15W\times250^{\circ}C/W$$

=40°C+37.5°C=77.5°C< $T_J(MAX)=125^{\circ}C$


For this operating condition, T_J is lower than the absolute maximum operating junction temperature,125°C, so it is safe to use the BL9161 in this configuration.

Layout considerations

To improve ac performance such as PSRR, output noise, and transient response, it is recommended that the PCB be designed with separate ground planes for V_{IN} and V_{OUT} , with each ground plane connected only at the GND pin of the device.



Package Descripti



Cumbal	Dimensions In	n Millimeters	Dimensions In Inches		
Symbol	Min	Max	Min	Max	
А	0.889	1.295	0.035	0.051	
A1	0.000	0.152	0.000	0.006	
В	1.397	1.803	0.055	0.071	
b	0.356	0.559	0.014	0.022	
С	2.591	2.997	0.102	0.118	
D	2.692	3.099	0.106	0.122	
е	0.838	1.041	0.033	0.041	
Н	0.080	0.254	0.003	0.010	
L	0.300	0.610	0.012	0.024	

SOT-23-5 Surface Mount Package





