



Shanghai Keter New Materials Co., Ltd.

N0.736 East Zhuanxing Road, Shanghai, China
 TEL: 0086-21-33505870 FAX: 0086-21-33506335
 Web: www.keter.com.cn Email: info@keter.com.cn


Polymer PTC Device

Radial leaded resettable fuse

KT120-1100B

Document: 5TD2
 Revision: A/1
 Page: 1 of 1
 Date:2018.12.04

Physical Dimensions: (mm)




A	B	C	D	E
11.7(Max.)	15.5(Max.)	3.5(Max.)	5.1(Typ.)	30±2

Lead Material: Tinned copper, Φ0.60mm

Encapsulation material: flame-retardant epoxy powder, meets UL94V-0 requirements

Electrical Characteristics:

Part Number	I _{hold} (A)	I _{trip} (A)	V _{max} (V)	I _{max} (A)	T _{trip}		R (Ω)		R _{1max} (Ω)
					current (A)	Time (s)	min	max	
KT120-1100B	0.90	2.30	120	20	5.5	≤8.2	0.15	0.31	0.70



I_{hold} = Hold Current: maximum current at which the device will not trip at 25 °C still air.

I_{trip} = Trip Current: minimum current at which the device will always trip at 25 °C still air.

V_{max} = Maximum voltage device can withstand without damage at rated current.

I_{max} = Maximum fault current device can withstand without damage at rated voltage.

T_{trip} = Maximum time to trip(s) at assigned current.

R_{1max} = Maximum Device resistance at 25 °C, of device one hour after being tripped the first time.



Prepare	Approval	Accept