



Shanghai Keter New Materials Co., Ltd.

N0.736 East Zhuanxing Road, Shanghai, China
 TEL: 0086-21-33505870 FAX: 0086-21-33506335
 Web: www.keter.com.cn Email: info@keter.com.cn


Polymer PTC Device

Radial leaded resettable fuse

KT600-110B

Document: 5TD1
 Revision: A/1
 Page: 1 of 1
 Date:2020.6.11

Physical Dimensions: (mm)




A	B	C	D	F
8.5(Max.)	12.6(Max.)	6.0(Max.)	5.1(TYP.)	4.7±0.4

Lead Material: Tinned copper, $\Phi 0.60\text{mm}$

Encapsulation material: flame-retardant epoxy powder, meets UL94V-0 requirements

Electrical Characteristics:

Part Number	I_{hold} (A)	I_{trip} (A)	V_{max} (V)	I_{max} (A)	T_{trip}		R (Ω)		$R_{1\text{max}}$ (Ω)
					current (A)	Time (s)	min	max	
KT600-110B	0.11	0.22	600	3.0	1.00	≤ 3.0	8.0	16.0	20.0



I_{hold} = Hold Current: maximum current at which the device will not trip at 25 °C still air.

I_{trip} = Trip Current: minimum current at which the device will always trip at 25 °C still air.

V_{max} = Maximum voltage device can withstand without damage at rated current.

I_{max} = Maximum fault current device can withstand without damage at rated voltage.

T_{trip} = Maximum time to trip(s) at assigned current.

$R_{1\text{max}}$ = Maximum Device resistance at 25 °C, of device one hour after being tripped the first time.

Prepare	Approval	Accept

