

GENERAL PURPOSE, LOW VOLTAGE, RAIL-TO-RAIL OUTPUT OPERATIONAL AMPLIFIERS

■ DESCRIPTION

The UTC **LV358** is a dual op amp with low supply current and low voltage (2.7-5.5V). It brings nice performance to low voltage and low power systems. With a 1MHz unity-gain frequency. The UTC **LV358** has a guaranteed 1 V/ μ s slew rate and low supply current. It provides heavy rail-to-rail (R-to-R) output swing loads and the input common-mode voltage range including ground. Besides, it is also capable for comfortably driving large capacitive loads.


The UTC **LV358** has bipolar input and CMOS output for improved noise performance and higher output current drive. It's the most cost effective solution for the applications where low voltage operation, space saving and low price are required.

■ FEATURES




- * 2.7V and 5V Performance Guaranteed
- * No Crossover Distortion
- * 210 μ A Low Supply Current
- * Rail-to-Rail Output Swing
- @10k Ω Load V⁺-10mV
V⁺+65mV
- * V_{CM} From -0.2V to V⁺-0.8V

■ ORDERING INFORMATION


Ordering Number		Package	Packing
Lead Free	Halogen Free		
LV358L-S08-R	LV358G-S08-R	SOP-8	Tape Reel
LV358L-SM1-R	LV358G-SM1-R	MSOP-8	Tape Reel
LV358L-P08-R	LV358G-P08-R	TSSOP-8	Tape Reel
LV358L-K08-2030-R	LV358G-K08-2030-R	DFN2030-8	Tape Reel

 (1) Packing Type (2) Package Type (3) Green Package	(1) R: Tape Reel (2) S08: SOP-8, P08: TSSOP-8, SM1: MSOP-8 K08-2030: DFN2030-8 (3) G: Halogen Free and Lead Free, L: Lead Free
--	---


■ MARKING

PACKAGE	MARKING
SOP-8 / MSOP-8	 <p>UTC LV358 Date Code L: Lead Free G: Halogen Free Lot Code</p>
TSSOP-8	 <p>UTC LV358 Date Code L: Lead Free G: Halogen Free Lot Code</p>
DFN2030-8	 <p>LV 358 Data Code</p>

■ PIN CONFIGURATION




DFN2030-8




SOP-8 / TSSOP-8 / MSOP-8


■ BLOCK DIAGRAM



- INTERNAL SIMPLE CIRCUIT



- TEST CIRCUIT FOR STABILITY VS CAPACITIVE LOAD



■ ABSOLUTE MAXIMUM RATINGS (Note1)

PARAMETER	SYMBOL	RATINGS	UNIT
Supply Voltage	V _{SS}	2.7 ~ 5.5	V
Supply Voltage (V ⁺ - V ⁻)	V _{SS}	5.5	V
Differential Input Voltage	V _{I(DIFF)}	±Supply Voltage	
Output Short Circuit	V ⁺ V ⁻	I _{O(SC)}	(Note 2) (Note 3)
Infrared (15 sec)		215	°C
Junction Temperature	T _J	+150	°C
Operation Temperature	T _{OPR}	-40~+85	°C
Storage Temperature	T _{STG}	-65~+150	°C

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

2. Shorting output to V⁺ will adversely affect reliability
3. Shorting output to V⁻ will adversely affect reliability

■ THERMAL DATA

PARAMETER	SYMBOL	RATINGS	UNIT
Thermal Resistance (Note 1)	SOP-8	190	°C/W
	MSOP-8	235	°C/W
	TSSOP-8	155	°C/W
	DFN2030-8	59	°C/W

Note: All numbers are typical, and apply for packages soldered directly note a PC board is still air.

■ 2.7V ELECTRICAL CHARACTERISTICS

All limits guaranteed for T_J =25°C, V⁺=2.7V, V⁻=0V, V_{CM}=1.0V, V_{OUT} =V⁺/2 and R_L>1MΩ, unless otherwise specified.

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
DC CHARACTERISTICS						
Input Offset Voltage	V _{os}			1.7	7	mV
Input Common Mode Voltage Range	V _{CM}	For CMRR≥50dB	0	-0.2		V
				1.9	1.7	V
Output Swing	V _{OUT}	R _L =10kΩ to 1.35V	V ⁺ -100	V ⁺ -10		mV
				60	180	mV
Input Offset Voltage Average Drift	TCVos			5		µV/°C
Input Bias Current	I _{I(BIAS)}			11	250	nA
Input Offset Current	I _{I(OFF)}			5	50	nA
Common Mode Rejection Ratio	CMRR	0V≤V _{CM} ≤1.7V	50	63		dB
Power Supply Rejection Ratio	PSRR	2.7V≤V ⁺ ≤5V, V _{OUT} =1V	50	60		dB
Supply Current	I _{ss}	Both amplifiers		140	340	µA
AC CHARACTERISTICS						
Gain Bandwidth Product	GBWP	C _L =200pF		1		MHz
Phase Margin	Φ _m			60		Deg
Gain Margin	G _m			10		dB
Input Referred Voltage Noise	eN	F=1KHz		46		$\frac{nV}{\sqrt{Hz}}$
Input Referred Current Noise	i _n	F=1KHz		0.17		$\frac{pA}{\sqrt{Hz}}$

■ 5V ELECTRICAL CHARACTERISTICS







All limits guaranteed for $T_J = 25^\circ\text{C}$, $V^+ = 5\text{V}$, $V^- = 0\text{V}$, $V_{CM} = 2.0\text{V}$, $V_{OUT} = V^+/2$ and $R_L > 1\text{M}\Omega$, unless otherwise specified.

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
DC CHARACTERISTICS						
Input Offset Voltage	V_{OS}			1.7	7	mV
Input Common-Mode Voltage Range	V_{CM}	For CMRR $\geq 50\text{dB}$	0	-0.2		V
				4.2	4	V
Output Swing	V_{OUT}	$R_L = 2\text{K}\Omega$ to 2.5V	V_{OH}	$V^+ - 300$	$V^+ - 40$	mV
			V_{OL}		120	300
		$R_L = 10\text{K}\Omega$ to 2.5V	V_{OH}	$V^+ - 100$	$V^+ - 10$	mV
			V_{OL}		65	180
Input Offset Voltage Average Drift	TCV_{OS}			5		$\mu\text{V}/^\circ\text{C}$
Input Bias Current	$I_{I(BIAS)}$			15	300	nA
Input Offset Current	$I_{I(OFF)}$			5	50	nA
Common Mode Rejection Ratio	CMRR	$0\text{V} \leq V_{CM} \leq 4\text{V}$	50	65		dB
Power Supply Rejection Ratio	PSRR	$2.7\text{V} \leq V^+ \leq 5\text{V}$ $V_{OUT} = 1\text{V}$, $V_{CM} = 1\text{V}$	50	60		dB
Large Signal Voltage Gain(Note 1)	G_V	$R_L = 2\text{K}\Omega$	15	100		V/mV
Output Short Circuit Current	I_{OUT}	Sourcing, $V_{OUT} = 0\text{V}$	5	230		mA
		Sinking, $V_{OUT} = 5\text{V}$	10	160		mA
Supply Current	I_{SS}	Both Amplifiers		210	440	μA
AC CHARACTERISTICS						
Slew Rate	SR	(Note 2)		1		$\text{V}/\mu\text{s}$
Gain Bandwidth Product	GBWP	$C_L = 200\text{pF}$		1		MHz
Phase Margin	Φ_m			60		Deg
Gain Margin	G_m			10		dB
Input Referred Voltage Noise	eN	$f = 1\text{KHz}$		39		$\frac{\text{nV}}{\sqrt{\text{Hz}}}$
Input Referred Current Noise	i_n	$f = 1\text{KHz}$		0.21		$\frac{\text{pA}}{\sqrt{\text{Hz}}}$







Notes: 1. R_L is connected to V^- . The output voltage is $0.5\text{V} \leq V_{OUT} \leq 4.5\text{V}$.

2. Connected as voltage follower with 3V step input. Number specified is these lower of the positive and negative slew rates






■ TYPICAL CHARACTERISTICS









■ TYPICAL CHARACTERISTICS(Cont.)









■ TYPICAL CHARACTERISTICS(Cont.)



■ TYPICAL CHARACTERISTICS(Cont.)



■ TYPICAL CHARACTERISTICS(Cont.)



UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice.



UNISONIC TECHNOLOGIES CO., LTD

www.unisonic.com.tw

12 of 12

QW-R502-316.E