

### **Description**

Gas discharge Tubes (GDT) are classical components for protecting the installations of the telecommunications. It is essential that IT and telecommunications systems -with their high-grade but sensitive electronic circuits - be protected by arresters. They are thus fitted at the input of the power supply system together with varistors and at the connection points to telecommunication lines. They have become equally indispensable for protecting base stations in mobile telephone systems as well as extensive cable television (CATV) networks with their repeaters and distribution systems.

These protective components are also indispensable in other sectors, In AC power transmission systems, they are often used with current-limiting varistors, In customer premises equipment such as DSL modems, WLAN routers, TV sets and cable modems In air-conditioning equipment, the integral black-box concept offers graduated protection by combining arresters with varistors, PTC, diodes and inductor.

#### **Features**

- Non-Radioactive
- RoHS compliant
- ♦ Low insertion loss
- ◆ Excellent response to fast rising transients
- ◆ Ultra low capacitance
- ◆ 5KA surge capability tested with 8/20µs pulse as defined by IEC 61000-4-5

#### **Applications**

- Communication equipment
- CATV equipment
- Test equipment
- Data lines
- Power supplies
- Telecom SLIC protection
- Broadband equipment
- ADSL equipment, including ADSL2+
- ♦ XDSL equipment
- ◆ Satellite and CATV equipment
- Consumer electronics



### **Schematic Symbol**




#### **Product Characteristics**

Materials	Nickel-plated with Tinplated wires
Product Marking	5KA
Glow to Arc Transition Current	< 0.5 Amps
Glow Voltage	~60 Volts
Storage and Operational Temperature	-40 to +90°C
Climatic category (IEC 60068-1)	40/90/21
Weight	~1.0g



# Dimensions (Unit: mm)



### **Electrical Characteristics**

		Maximum Impulse Spark-over Voltage		Minimum Insulation Resistance	Maximum Capacitance	Arc Voltage	Service Life			
Part Number	DC Spark-over Voltage						Nominal Impulse Discharge Current	Max Impulse Discharge Current	Nominal Alternating Discharge Current	Impulse Life
	@100V/S	@100V/µs	@1KV/μs		@1MHz	@1A	@8/20μs ±5 times	@8/20μs 1 time	@50Hz 1 Sec 10 times	@10/1000µs 300 times
K2RL075L-5	75V±20%	<500V	<600V	1 GΩ (at 25V)	<1.0pF	~15V	5KA	10KA	5A	100A
K2RL090L-5	90V±20%	<500V	<600V	1 GΩ (at 50V)	<1.0pF	~15V	5KA	10KA	5A	100A
K2RL150L-5	150V±20%	<500V	<600V	1 GΩ (at 50V)	<1.0pF	~20V	5KA	10KA	5A	100A
K2RL230L-5	230V±20%	<600V	<700V	1 GΩ (at 100V)	<1.0pF	~20V	5KA	10KA	5A	100A
K2RL250L-5	250V±20%	<700V	<800V	1 GΩ (at 100V)	<1.0pF	~20V	5KA	10KA	5A	100A
K2RL300L-5	300V±20%	<800V	<900V	1 GΩ (at 100V)	<1.0pF	~20V	5KA	10KA	5A	100A
K2RL350L-5	350V±20%	<800V	<900V	1 GΩ (at 100V)	<1.0pF	~20V	5KA	10KA	5A	100A
K2RL420L-5	420V±20%	<900V	< 1000V	1 GΩ (at 100V)	<1.0pF	~20V	5KA	10KA	5A	100A
K2RL470L-5	470V±20%	<900V	< 1000V	1 GΩ (at 100V)	<1.0pF	~20V	5KA	10KA	5A	100A
K2RL600L-5	600V±20%	<1100V	< 1200V	1 GΩ (at 100V)	<1.0pF	~20V	5KA	10KA	5A	100A
K2RL800L-5	800V±20%	<1200V	< 1400V	1 GΩ (at 100V)	<1.0pF	~20V	5KA	10KA	5A	100A

### Notes:

<sup>1).</sup> Terms in accordance with ITU-T K.12 and GB/T 9043-2008


<sup>2).</sup> At delivery AQL 0.65 level II, DIN ISO 2859




## **Electrical Rating**

Item	Test Condition / Description	Requirement			
DC Spark-over Voltage	The voltage is measured with a slowly rate of rise dv / dt=100V/s				
Impulse Spark-over Voltage	The maximum impulse spark-over voltage is measured with a rise time of dv / dt=100V//µs or 1KV/µs				
Insulation Resistance	The resistance of gas tube shall be measured each terminal each other terminal, please see above spec.				
Capacitance	The capacitance of gas tube shall be measured each terminal to each other terminal.  Test frequency :1MHz				
Nominal Impulse Discharge Current	The maximum current applying a waveform of 8/20µs that can be applied across the terminals of the gas tube. One hour after the test is completed, re-testing of the DC spark-over voltage does not exceed ±30% of the nominal DC spark-over voltage. Dwell time between pulses is 3 minutes.  1.0  0.5  0.1  0.9  8µsec  20µsec  30% Max  The DC	To meet the specified value			
Nominal Alternating Discharge Current	Rated RMS value of AC current at 50Hz, 1 sec. 10 times. Intervals: 3min. The DC spark-over voltage does not exceed $\pm 30\%$ of the nominal DC spark-over voltage. IR > $10^8$ ohms.				

## **Recommended Soldering Profile**





# **Soldering Parameters - Hand Soldering**

Solder Iron Temperature: 350°C +/-5°C

Heating Time: 5 seconds max.