

Preliminary

Innovative Service Around the Globe **YAGEC**

# DATA SHEET

## WIRELESS COMPONENTS

Band Pass Filter  
BPF1608LM10R5000A

5.0 GHZ  
1608 Series



**YAGEO**  
**Phycomp**

Product Specification – Dec. 6, 2018 V.Pre



FEATURES

- Compact size design
- RoHS compliant

APPLICATIONS

- WLAN, 802.11a/n
- ISM Band

ORDERING INFORMATION

All part numbers are identified by the series, packing type, material, size, antenna type, working frequency and packing quantity.

**PART NUMBER**

**BPF1608 LM 10 R 5000A**

(1) (2) (3) (4) (5) (6)

---

(1) PRODUCT

BPF = Band Pass Filter

---

(2) SIZE

1608 = 1.60 × 0.8 mm

---

(3) MATERIALS

Material Code LM

---

(4) TYPE

10 = Type 10

---

(5) PACKING STYLE

R = Tape and Reel

---

(6) WORKING FREQUENCY

5000 = 5.0 GHz

**SPECIFICATION**

Table 1

DESCRIPTION	Value
Pass Band	4900 ~ 5950MHz
Insertion Loss	1.3 max. at 25°C
Return Loss	10dB (Min.)
Attenuation	38.0 dB @ 30 - 2700 MHz 16.0 dB @ 3453 - 3547 MHz 33.0 dB @ 3667 - 3883 MHz 9.0 dB @ 6900 - 7093 MHz 32.0 dB @ 7333 - 7750 MHz 40.0 dB @ 10600 - 11650 MHz 18.0 dB @ 15540 - 17760 MHz
Operating Temperature	-40 ~ 85°C

**DIMENSIONS**

Table 2 Mechanical Dimension

	DIMENSION
L (mm)	1.60±0.15mm
W (mm)	0.80±0.15mm
T (mm)	0.60±0.15mm
P1 (mm)	0.25±0.10mm
P2 (mm)	0.40±0.10mm
P3(mm)	0.25±0.10mm
D1 (mm)	0.10±0.10mm
D2 (mm)	0.25±0.10mm
D3(mm)	0.10±0.10mm
D4(mm)	0.60±0.10mm

Table 3 Termination configuration

TERMINAL NAME	FUNCTION
P1	I/O port
P2	GND
P3	I/O port

**OUTLINES**





Fig. 1 Filter outlines

**REVISION HISTORY**

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version Pre	Oct. 18, 2019 -		- Preliminary data sheet for Diplexer, 2.4/5.0 GHz application, 1608 series refer to RDV00

# 2.PACKING SPEC



Serial no	Checking note	Index	Spec (mm)	
1	Tape width	W	8.00 ±	0.3 0.1
2	Sprocket hole	D	1.55 ±	0.1
3	Distance sprocket hole to sprocket hole	Po	4.00 ±	0.10
4	Distance pocket to pocket	P1	4.00 ±	0.10
5	Distance sprocket hole to pocket	P2	2.00 ±	0.01
6	Distance sprocket hole to outside	E	1.75 ±	0.10
7	Distance sprocket hole to pocket	F	3.50 ±	0.05
8	Internal diameter of reel	C	13.00 ±	0.50
9	External diameter of reel	A	180.00 ±	1.00



# 3. Reliability Test

---

Test Item	Procedure	Requirements	Remark (Reference)
<b>Vibration</b>	<ol style="list-style-type: none"> <li>5g's for 20 min., 12 cycles each of 3 orientations</li> <li>Note: Use 8"X5" PCB .031" thick 7 secure points on, one long side and 2 secure points at corners of opposite sides.</li> <li>Parts mounted within 2" from any secure point. Test from 10-2000 Hz.</li> </ol>	No Visible Damage.	MIL-STD-202 Method 204
<b>Mechanical Shock</b>	<p>Three shocks in each direction shall be applied along the three mutually perpendicular axes of the test specimen (18 shocks)</p> <p>Peak value: 1,500g's                      Duration: 0.5ms                      Velocity change: 15.4 ft/s                      Waveform: Half-sine</p>	No Visible Damage.	MIL-STD-202 Method 213
<b>Humidity</b>	<ol style="list-style-type: none"> <li>Humidity: 85% R.H., Temperature: 85 ±2 °C.</li> <li>Time: 500±24 hours.</li> <li>Measurement at 24±2hrs after test condition.</li> </ol>	No Visible Damage. Fulfill the electrical specification.	MIL-STD-202 Method 106
<b>Board Flex (For SMD type)</b>	<p>Mounting method:                      IR-Reflow. PCB Size (L:100 × W:40 × T:1.6mm)                      Apply the load in direction of the arrow until bending reaches :                      1 mm for all types.</p>	No Visible Damage.	AEC-Q200 005






V

Test Item	Procedure	Requirements	Remark (Reference)
Electrical Characterization		Fulfill the electrical specification.	User Spec.
Thermal Shock	<ol style="list-style-type: none"> <li>Preconditioning: 150±10°C / 1 hr, then keep for 24±1 hrs at room temp.</li> <li>Initial measure: Spec: refer Initial spec.</li> <li>Rapid change of temperature test: -30°C to +85°C; 100 cycles; 15 Minutes at Lower category temperature; 15 Minutes at Upper category temperature.</li> </ol>	<ol style="list-style-type: none"> <li>No Visible Damage.</li> <li>Fulfill the electrical spec.</li> </ol>	MIL-STD-202 107
Temperature Cycling	Initial measure: Spec: refer Initial spec. Temperature test: Soak Mode=1 (Cycle/hours). 100 Cycles (-30°C to +85°C) Measurement at 24+/-2Hours after test condition.	<ol style="list-style-type: none"> <li>No Visible Damage.</li> <li>Fulfill the electrical spec.</li> </ol>	JESD22 JA104
High Temperature Exposure	<ol style="list-style-type: none"> <li>Initial measure: Spec: refer Initial spec.</li> <li>Unpowered 500 hours @ T=+85 °C</li> <li>Measurement at 24±2 hours after test.</li> </ol>	<ol style="list-style-type: none"> <li>No Visible Damage.</li> <li>Fulfill the electrical spec.</li> </ol>	MIL-STD-202 108
Low Temperature Storage	<ol style="list-style-type: none"> <li>Initial measure: Spec: refer Initial spec.</li> <li>Unpowered 500 hours @ T=-30 °C</li> <li>Measurement at 24±2 hours after test.</li> </ol>	<ol style="list-style-type: none"> <li>No Visible Damage.</li> <li>Fulfill the electrical spec.</li> </ol>	MIL-STD-202 108
Solderability (SMD Bottom Side)	Dipping method: <ol style="list-style-type: none"> <li>Temperature: 235±5°C</li> <li>Dipping time: 3±0.5s.</li> </ol>	The solder coverage: > 95%	IEC 60384-21/22 4.1
Soldering Heat Resistance (RSH)	Preheating temperature: 150±10°C. Preheating time: 1~2 min. Solder temperature: 260±5 °C. Dipping time: 5±0.5s.	No Visible Damage.	IEC 60384-21/22 4.1



Test Item	Procedure	Requirements	Remark (Reference)
<b>Adhesion</b> (For SMD type)	Apply Force for 60 seconds. Size $\geq$ 1608: 5N Size=1005: 2.5N Size<1005: 1N  	No Visible Damage Magnification of 20X or greater may be employed for inspection of the mechanical integrity of the device body terminals and body/terminal junction.	AEC-Q200 006
<b>Physical Dimension</b>	Any applicable method using x10 magnification, micrometers, calipers, gauges, contour projectors, or other measuring equipment, capable of determining the actual specimen dimensions.	In accordance with specification.	JESD22 JB100

# 4.Reflow Profile

---

# Soldering Profile for Lead-free Process

