


## Features

- 4000 Watts Peak Power ( $t_p = 8/20\mu s$ )
- Fast Response time: Typically < 1ns
- Excellent Clamping Capability
- Low Inductance
- Low profile package



## IEC COMPATIBILITY (EN61000-4)

- IEC 61000-4-2 (ESD)  $\pm 30kV$  (air),  $\pm 30kV$  (contact)
- IEC 61000-4-4 (EFT) 40A (5/50ns)
- IEC 61000-4-5 (Lightning) 150A (8/20 $\mu s$ )


## Mechanical Characteristics

- DFN2020-3L package
- Molding compound flammability rating: UL 94V-0
- Marking : Making Code
- Packaging : Tape and Reel per EIA 481
- RoHS Compliant

## Applications

- I/O Interfaces
- Power lines
- Automotive and Telecommunication
- Computer & Consumer Electronics
- Industrial Electronics
- Microcontroller Input Protection

## PIN Configuration




### Absolute Maximum Rating

Rating	Symbol	Value	Units
Lead Soldering Temperature	T <sub>L</sub>	260(10sec)	°C
Operating Temperature	T <sub>J</sub>	-55 to + 125	°C
Storage Temperature	T <sub>STG</sub>	-55 to +150	°C
Peak Pulse Power ( $t_p=8/20\mu s$ )	P <sub>PP</sub>	4000	Watts
Peak Pulse Current ( $t_p=8/20\mu s$ )	I <sub>PP</sub>	150	A

### Electrical Parameters (T=25°C)

Symbol	Parameter
I <sub>PP</sub>	Reverse Peak Pulse Current
V <sub>C</sub>	Clamping Voltage @ I <sub>PP</sub>
V <sub>RWM</sub>	Working Peak Reverse Voltage
I <sub>R</sub>	Reverse Leakage Current @ V <sub>RWM</sub>
V <sub>BR</sub>	Breakdown Voltage @ I <sub>T</sub>
I <sub>T</sub>	Test Current
I <sub>F</sub>	Forward Current
V <sub>F</sub>	Forward Voltage @ I <sub>F</sub>




### Electrical Characteristics


MDFN2020A121S						
Parameter	Symbol	Conditions	Minimum	Typical	Maximum	Units
Reverse Stand-Off Voltage	V <sub>RWM</sub>				12	V
Reverse Breakdown Voltage	V <sub>BR</sub>	I <sub>T</sub> =1mA	13.4	14		V
Reverse Leakage Current	I <sub>R</sub>	V <sub>RWM</sub> =12V, T=25°C			500	nA
Peak Pulse Current	I <sub>PP</sub>	t <sub>p</sub> =8/20μs			150	A
Clamping Voltage <sup>1</sup>	V <sub>C</sub>	I <sub>PP</sub> =40A, t <sub>p</sub> =8/20μs		19	22	V
Clamping Voltage <sup>1</sup>	V <sub>C</sub>	I <sub>PP</sub> =90A, t <sub>p</sub> =8/20μs		23	25	V
Clamping Voltage <sup>1</sup>	V <sub>C</sub>	I <sub>PP</sub> =150A, t <sub>p</sub> =8/20μs		26	27	V
Junction Capacitance	C <sub>j</sub>	V <sub>R</sub> = 0V, f = 1MHz		900	1000	pF

## Typical Characteristics


**Figure 1: Peak Pulse Power vs. Pulse Time**




**Figure 2: Power Derating Curve**




**Figure 3: Clamping Voltage vs. Peak Pulse Current**





**Figure 4: Normalized Junction Capacitance vs. Reverse Voltage**





**Figure 5: 8/20μs Pulse Waveform**



**Outline Drawing –DFN2020-3L**
**PACKAGE OUTLINE**

**DFN2020-3L**

SYMBOL	MILLIMETER		
	MIN	NOM	MAX
A	0.5	0.55	0.60
A1	0.00	0.02	0.05
b	0.25	0.30	0.35
b1	0.20REF		
c	0.152REF		
D	1.90	2.00	2.10
D2	1.40	1.50	1.60
e	1.30BSC		
E	1.90	2.00	2.10
E2	0.95	1.05	1.15
E3	0.20	0.30	0.40
L	0.35	0.40	0.45
L1	0.20	0.25	0.30
h	0.20REF		
K	0.20	0.30	0.40

**Land Pattern**

**Marking Codes**

 M12A=Specific Device Code  
 XXXX=Lot Code

**Package Information**

Qty: 3k/Reel