RLM102 Series

Features

- RoHS compliant.
- Bilateral symmetrical.
- Less decay at on/off state.
- Approximately zero leaking current before clamping voltage
- High capability to withstand repeated lightning strikes.
- Low electrode capacitance(≤1.0pF) and high isolation (≥100MΩ).
- Temperature, humidity and lightness insensitive.
- Working temperature range: : -45℃ ~ +85℃
- Storaging temperature range: -45°C ~ +85°C




Applications

- Power Supplies
- Motor sparks eliminating
- Relay switching spark absorbing
- Data line pulse guarding
- Telephone/Fax/Modem
- High frequency signal transmitters/receivers

- Satellite antenna
- Radio amplifiers
- Alarm systems
- Cathode ray tubes in Monitors/ Television Viewing Systems

Part Number Code



Revised: 2018-07-13







RLM102 Series

Electrical Characteristics

Type Number	DC Spark-Over Voltage	Insul	Min. Insulation Resistance		Surge Current Capacity	Current
	Vs	Test Voltage	I _R	Cj	8/20µs	@8/20µs
	V	V	ΜΩ	pF	Α	
RLM102-141N	140(126~210)	50	100	1	1000	100A 10 times
RLM102-181N	180±30%	50	100	1	1000	100A 10 times
RLM102-201M	200±20%	100	100	1	1000	100A 10 times
RLM102-301M	300±20%	100	100	1	1000	100A 10 times
RLM102-401M	400±20%	250	100	1	1000	100A 10 times
RLM102-501M	500±20%	250	100	1	1000	100A 10 times

Test Methods And Results

Test Item	Test Method	Specification	
DC Spark-over Voltage Vs(V)	Add and measure the DC Voltage gradually Maxto get the discharge threshold voltage. The measuring current is 1mA/1 second max.	It depands on each spec.	
Insulation Resistance	Measure the insulation resistance of two end of leadwire under the specified DC voltage.	100MΩ min.	
Capacitance Cj(pF)	Measure the Electrostatic Capacitance under the test condition of 1KHz,DC 6V(max).	1pF max.	
Life(JSE)	Apply a standard impulse voltage (8X20µsec)of 100A for 5 times with intervals of 30 sec., and then change the polarity of the surge and apply a impulse again. Then measure DC spark-over voltage, IR & Capacitance.	DC spark-over voltage JSE: △ Vs/Vs ≤30%	
Life(JSE)	Apply 10 KV voltage charged in 1500pF condenser and apply the current to the specimen,200 times at 10 seconds of intervals	Insulation Resistance & Capacitance to meet the specified value. Appearance: No cracks or failures.	
Cold Resistance	Measurement after -40 ℃ /1000 HRS & normal temperature/2 HRS.		
Heat Resistance	Measurement after 125°C /1000 HRS & normal temperature/2 HRS.	Features are conformed to rated spec.	
Humidity Resistance	Measurement after humidity 90~95 °C (45 °C) /1000 HRS & normal temperature/2 HRS.		
Temperature Cycle	10 times repetition of cycle -40 °C /30min →normal, temp/2 min →125°C /30min, measurement after normal temp/2 HRS.		
Pull Strength	Apply 0.5kg load for 10sec.		
Flexural Strength	Bend lead wire at the point of 2mm from body under 0.25 load and back to its original point. Repeat 1 time.		

Revised: 2018-07-13






RLM102 Series

Recommended Soldering Conditions

Flow Soldering Conditions



Hand Soldering

Solder iron temperature: $350\pm5^{\circ}$ C Heating time: 3 seconds max.

General attention to soldering

1.High soldering temperatures and long soldering times can cause leaching of the termination, decrease in adherence strength, and the change of characteristic may occur.

2.For soldering, please refer to the soldering curves above. However, please keep exposures to temperatures exceeding 200°C to fewer than 50 seconds.

3.Please use a mild flux (containing less than 0.2wt% CI). Also, if the flux is water soluble, be sure to wash thoroughly to remove any residue from the underside of components that could affect resistance.

- 1) Time shown in the above figures is measured from the point when chip surface reaches temperature.
- 3) After soldering, do not force cool, allow the parts to cool gradually.

Cleaning

When using ultrasonic cleaning, the board may resonate if the output power is too high. Since this vibration can cause cracking or a decrease in the adherence of the termination, we recommend that you use the conditions below.


Revised: 2018-07-13

Frequency: 40kHz max.

Output power: 20W/liter

Cleaning time: 5 minutes max.

Dimensions



DIM	Millimeters	Inches	
Α	5.0±0.5	0.197±0.02	
С	Ф2.6±0.5	0.102±0.02	
D Φ2.7±0.5		0.106±0.02	









RLM102 Series

Taping and Reel Specifications





Symbol	Millimeters	Inches		
w	12.0±0.2	0.472±0.008		
P0	4.0±0.1	0.157±0.004		
P1	4.0±0.1	0.157±0.004		
P2 2.0±0.1		0.079±0.004		
D	Ф1.5±0.1	0.059±0.004		
d	Ф1.5±0.1	0.059±0.004		
E	1.75±0.1	0.069±0.004		
F	5.5±0.05	0.217±0.002		
D1 178.0		7.007		
D0 13.0		0.512		
W1	15.0	0.591		
Quantity:1500PCS / inner box				





Revised: 2018-07-13