



P.C.B LAYOUT

### Specifications:

- 1.Voltage rating:250VAC/DC
- 2.Current rating:1A AC/DC
- 3.Withstanding voltage:300V AC/minute
- 4.Temperature range:-40℃ to +105℃
- 5.Insulation resistance:≥500MΩ Min
- 6.Contanct resistance:≤20MΩ Max
- 7.Material:PA6T 94V-0
- 8.Planting Category:1U"Gold
- 9.Reflow Soldering temperature:260±5℃, 10S

### X1321 F V S -2\*XX-C57-D65

- ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Category:F-Female
- ③ Welding Board Angle:V-Right Angle 90°
- ④ Welding Way:S-SMT
- ⑤ Row No-Pin No:2\*xx-01p-40p
- ⑥ Plastic height:C=5.7mm
- ⑦ Plastic height:D=6.5mm

X1321FVS-2*XX-C57D65	PA6T 94V-0	Brass	1U" Gold	X1321W
PART NO	Material	Material(Terminal)	Finish(Terminal)	Suitable XKB Terminal

					ANGLAR	±5°	DSND		DATE	SCALE: N/A	MODEL TYPE: X1321FVS-2*XX-C57D65
ΔX					L ≤ 4	±0.2	DWN		DATE	VIEW:	PART NO.:
ΔX					4 < L ≤ 16	±0.3	CHKD		DATE	UNIT: mm/in	DWG NO.:
ΔX					16 < L ≤ 63	±0.4	APPD		DATE	SIZE: A4	X1321FVS-2*XX-C57D65
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5					WEIGHT
						UNSPECIFIED TOLERANCES	XKB INDUSTRIAL PRECISION CO., LIMITED				1.0g
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn											SHEET
											1/1
											REVISION
											A0