

系列 SER.NO.: UJ

承 認 書

APPROVAL SHEET

FOR AL. ELECTROLYTIC CAPACITORS

承 認
APPROVED BY:

料号 (Customer)	料号 (CapXon)	规格 Description	Dφ*L	加工形式 (mm)
	UJ681M160M450A	680uF/160V	22X45	
	UJ561M315N500A	560uF/315V	25X50	
	UJ681M315O450A	680uF/315V	30X45	
	UJ331M450P400A	330uF/450V	35X40	
	UJ561M450P500A	560uF/450V	35X50	

簽認後，請送回一份。

PLEASE RETURN US ONE COPY YOUR SIGNED SPECIFICATION AFTER YOU APPROVED OF IT.

核 准
APPROVED BY:



校 對
CHECKED BY:



經 辦
DESIGNED BY:



CapXon

英屬維京群島商凱普松科技股份有限公司
台灣分公司
CAPXON TECHNOLOGY LIMITED TAIWAN BRANCH
新北市汐止區大同路二段 157 號 5 樓
5F, NO. 157, TA TUNG ROAD, SEC. 2,
SHI-CHIH DIST., NEW TAIPEI CITY,
TAIWAN, R.O.C.
TEL : 886-2-86926611
FAX : 886-2-86926477 / 86926481

豐賓電子(深圳)有限公司
CAPXON ELECTRONIC (SHEN ZHEN) CO.,LTD
深圳市光明新區公明鎮塘尾工業區
Tang Wei Section,Tang Wei Village,Gong Ming
Country,GuangMingHsien,ShenZhen,China
TEL:86-755-27177888
FAX:86-755-27177802


CAPXON ELECTRONIC (SHEN ZHEN) CO., LTD FOR APPROVAL

Aluminum Electrolytic Capacitors UJ Type

1. Electric Characteristics

CAPXON P/N	Cap (μF)	Cap Tol (%)	Rate W.V (VDC)	Surge Volt (VDC)	Max.D.F (%)	Ripple Current 120Hz/105°C (mA)	Max.LC (μA)	Oper. Temp. (°C)	Case Size DΦ*L (mm)	Endurance /+105°C (Hrs)	USER P/N
UJ681M160M450A	680	± 20	160	184	15	1640	989	-25~+105	22X45	2000	
UJ561M315N500A	560	± 20	315	362	20	1610	1260	-25~+105	25X50	2000	
UJ681M315O450A	680	± 20	315	362	20	1730	1388	-25~+105	30X45	2000	
UJ331M450P400A	330	± 20	450	495	20	1600	1156	-25~+105	35X41	2000	
UJ561M450P500A	560	± 20	450	495	20	2380	1506	-25~+105	35X50	2000	

2. Diagram of Dimensions (Unit=mm):




3. Remarks:

- 3.1 Leakage Current Test: $I \leq 3 \cdot \sqrt{CV}$ (μA) After 5 minutes whichever is greater measured with rated working voltage applied.
- 3.2 Operating temperature: for -25°C ~ 105°C
- 3.3 Cap and Dissipation factor (D.F) Test: At +20°C, 120Hz.
- 3.4 Shelf Life Test: At +105°C, 1000Hrs.
- 3.5 Such spec. capacitors are just fit for this electric model , if you have some other application, please contact with us in advance.

Part Number System

When placing an order for Aluminum Electrolytic Capacitors, please observe the following Catalog Part Number format that describes.



(1). Series

The series name.

(2). Capacitance

Capacitance is shown in microfarad (μ F)

Capacitance (μ F)	0.1	0.47	1	4.7	10	100	1000	10000
Code	0R1	R47	010	4R7	100	101	102	103

(3). Capacitance tolerance

Tolerance%	± 5	± 10	± 20	± 30	-10to+30	-10to+50	-10to+20	-10to100	0to+20	-30to+0	± 15
Code	H	K	M	N	Q	T	V	W	Z	U	S
Tolerance%	0to+30	0to+40	0to+50	-5to+20	-8to+5	+5to+20	0to-20	-15to+20	-25to+20	-50to+0	-5to+30
Code	Y	X	A	J	E	I	B	P	L	O	C

For tolerance other than these and specified capacitance tolerance, please specify the value on the order sheet.

(4). Voltage (W.V)

Voltage (W.V)	6.3	10	16	25	35	50	63	80	100	160	200	220	250	350	400	420	450	500
Code	6R3	010	016	025	035	050	063	080	100	160	200	220	250	350	400	420	450	500

(5). Case (ϕ D: mm)

Diameter	3	4	5	6.3	7.3	8	10	12	13	16	18	20	22	25	30	35	40	42	45	51	63.5	76.2	89	14.5	12.5
Code	A	B	C	E	7	F	G	H	I	J	K	L	M	N	O	P	Q	U	V	R	S	T	X	Y	Z

(6). Height (L: mm)

Description	5	5.5	7	7.7	8	11	11.5	12	12.5	14	16	20	21	25	25.5	31.5	35	35.5	41	47	52	83	98	118	141	151
Code	050	055	070	077	080	110	115	120	125	140	160	200	210	250	255	315	350	355	410	470	520	830	980	A18	A41	A51

(7). Product type

Type	Without Lead Treatment	With Lead Treatment
Code	A	E

(8). Lead Treatment (Radial type)

Description	Taping (Ammo Package)	Taping (Reel Package)	Lead Cutting	Lead Forming Cutting	Lead Forming only	Lead Crimping & Forming	Lead Cutting & Kink	Kink	Bending & Cutting	Forming & Kink
Code	TA, TB, TC, TD, TE, TF, ETC.	RA, RB, RC, RD, RE, Etc.	CA	CF	FA	KF	CK	KA	CR, CL	EF

Remarks: The product of V- chip sticks a dish to process form is "TR".

(9) Special & appearance requirement (the 17th, 18th, 19th, 20th code)

Code	Special	Code	Special	Code	request characteristic	Code	Special
A	Terminals of Snap-in	H	Height requirement	R	Ripple current	U	Package & label
B	Rubber	I	L.C.	S	countermeasure		
C	Lead wire	K	Vent line	T	Temperature characteristic		
D	D.F.	L	Life	V	Vt, Electrolyte paper		
E	Electrolyte	N	Nude	M	Solder, technics, form, Case with pillar,		
F	Pitch	P	Sleeve, tray, print, PVC sleeve	Y	clip loop		
G	Fill glue	Q	Capacitance, CV, Break	Z	Impedance & ESR		

Remarks:

1. If it's without lead treatment & special requirement, the 15th code is blank.
2. If it's with lead treatment & without require special requirement, the 17th, 18th, 19th, 20th code is blank.
3. If it's without lead treatment, but with special requirement, the 15th, 16th code filled with 0.
4. If it's without lead treatment, but with special requirement, also exceeds 4 kinds, keystone characteristic is 4 codes.
5. If it's with lead treatment, but with 1 special requirement, only remark 17th code, latter three codes is blank.
6. If it's with lead treatment, but with 1 special requirement, and it is different from former data, the 17th is 0, the 18th code is characteristic.

一. 注意事项 Information**1. 最大均方根纹波电流 Maximum RMS ripple current****1.1. 最大均方根纹波电流值是指+105°C 120Hz 测试值。**

Maximum RMS ripples current at +105°C 120Hz.

1.2. 当电容器的使用温度及频率不是+105°C 120Hz 时，该最大均方根纹波电流值必须乘以下表所示的系数进行换算。

When capacitors are operated at temperatures other than +105°C, and frequency other than 120Hz, the maximum RMS ripple currents must be multiplied by the factors shown in below table.

Multiplier for Ripple Current vs. Frequency:

CAP (μF) \ Hz	50(60)	120	400	1K	10K	50K-100K
100<CAP ≤ 1000	0.8	1	1.16	1.25	1.35	1.38
1000<CAP	0.8	1	1.11	1.17	1.25	1.28

1.3 当频率与上面规定条件不同时，纹波电流不能超过允许纹波电流值乘以上表系数所得值。纹波电流验证方法参照 JIS-C-5101-1(2010) No.: 4.23.

When frequency is different from specified condition shown as above, do not exceed the value obtained by multiplying the permissible maximum ripple current by the multiplier above. The ripples current verify methods according to JIS-C-5101-1(2010) No.: 4.23.

☆注意：(1) 纹波电流要对应工作频率 Ripple current corrected with working frequency.

(2) 当电路中纹波电流很难测量时，电容器自身的温升应在 5°C 以内。

Check the generated heat of capacitor when ripple current is hard to measure in the circuit. Promoted temperature by self-generating heat should be within 5°C.

2. 工作电压 Working Voltage (WV)

电容器的应用电压要保证不可过压（也就是高于额定电压）。

Make sure that no excess voltage (that is, higher than the rated voltage) is applied to capacitor. Please pay attention so that the peak voltage, which is DC voltage, overlapped by ripple current, will not exceed the rated voltage.

3. 绝缘性 Insulating

铝电解电容器普通品表面套有乙烯基或类似材料的套管，这种套管一般是用来标示的。如果铝壳需要绝缘，建议采用为绝缘设计的特殊类型的电容器。

General types of aluminum electrolytic capacitors are covered with a vinyl sleeve or the like. And this Sleeve is used for marking. When the internal element or the container is needed to be insulated, capacitors specially designed for insulation requirement are recommended to be used.

4. 焊锡性 Soldering

4.1 在将各种元器件焊接在 PC 板上时，过高的焊接温度或是过长的焊接时间都会引起套管二次收缩，导致破洞，并且必须在 PC 板的反面进行焊锡。

When soldering a PC board with various components, too high soldering temperature or too long dipping time may cause secondary shrinking of the sleeve and then the container unnecessarily exposed. The soldering must be done on the reverse of PC board.

4.2 如果套管与电路板接触，在焊锡时可能熔化或损坏套管，因此建议电容器与电路板保持一定的距离。

Soldering may melt or break the sleeve when the sleeve is contacted with circuit boards. So the capacitors are recommended to be slightly apart from the circuit boards.

5. 防爆 Vent

电容器 (Φ≥10mm) 在铝壳底部设置了一个防爆装置，当误操作时防爆阀会打开以释放内部较高的压力。

The capacitor (Φ≥10mm) is provided with a safety vent on the bottom of the container. The vent would rupture in the event of the unsafe usage or misuse to relieve the internal higher pressure.

6. 高海拔 High Altitude

该电容器可以在 -25°C 到 +105°C 的温度环境和 200,000 英尺的海拔高度运输。

The capacitors can withstand those transportation conditions that temperature may range from -25°C to +105°C and the altitude can reach 200,000 feet.

7. 清洗剂 Cleaning agents:

如果用含卤元素的有机溶剂清洗电容器，溶剂可能会渗入电容内部导致腐蚀。

If the capacitor is cleaned in halogenated agents for organic removing solder flux solvent, the agents may penetrate into the inside of capacitor, and may generate corrosion.

8. 环保方针 Environment-friendly policy

本公司依蒙特利尔协议书之规定，于生产过程中不使用破坏臭氧层之药品。在电容器生产的整个制程中，包括生产、包装、存储和运输，我司始终遵守环保和 ROHS 的相关法律法规。

None of ozone depleting chemicals (ODC) under the Montreal Protocol is used in manufacturing process of CapXon Electronic industrial CO., Ltd. In the entire process of capacitor's production, including manufacture, packaging, storage and transportation, our company always complies with the related Environmental Protection Laws and Regulations of RoHS.

9. 本公司品质量依 JIS-C-5101-1 标准考核，其信性试验方法依 JIS-5101-4(非 SMD 液态)，-18(液态 SMD) 之规范为基准。

CapXon's Products meet or exceed quality standards specified by JIS-C5101-1 Wand with reliability Requirements refer to JIS-C-5102-4(non-SMD liquid capacitor),-18(liquid SMD capacitor).

二. 技术性能 Technical Feature

测试环境 Testing Environment:

环境条件 Condition	方案 Precept	无特别规定及判定无疑问 No special regulation and judgment doubt	无特别规定而判定有疑问 No special regulation but have judgment doubt	在标准室内测试仍有争议 Under the standard room testing but have dispute
温度 Temperature		15~35℃	25±10℃	20±1℃
湿度 Humidity		25~75%RH	40 ~60%RH	63~67%RH
气压 Air pressure		86KPa~106KPa	86KPa~106KPa	86KPa~106KPa

序号 NO.	试验项目 Item	实验条件及判定 Conditions and Criterion							
1	工作温度范围 Range of working temperature	-25℃~+105℃(400V~500V)							
2	电容容量 Capacitance	实验条件 Conditions: 测量温度 Temperature: 20±2℃ 测量频率 Frequency: 120Hz 测量电压 Voltage: 0.5Vrms 判定标准 Criterion: 容量偏差 Tolerance: ±20%							
3	损耗角正切 Dissipation factor (tanδ)	实验条件 Conditions: 测量温度 Temperature: 20±2℃ 测量频率 Frequency: 120Hz 测量电压 Voltage: 0.5Vrms 判定标准 Criterion: <table border="1" style="margin-left: 20px;"> <tr> <td>工作电压 W.V.(V)</td> <td>160~250</td> <td>315~450</td> </tr> <tr> <td>损耗角正切 DF.(%)max.</td> <td>15</td> <td>20</td> </tr> </table>		工作电压 W.V.(V)	160~250	315~450	损耗角正切 DF.(%)max.	15	20
工作电压 W.V.(V)	160~250	315~450							
损耗角正切 DF.(%)max.	15	20							
4	漏电流 Leakage Current	实验条件 Conditions: 将额定电压加在电容和 1000Ω±10% 的保护电阻上充电 5 分钟后测试。 The rated voltage shall be applied across the capacitors and its protective resistor which shall be 1000Ω±10%.The leakage current shall then be measured after an electrification period of 5 min. 判定标准 Criterion: $I \leq 3 \cdot \sqrt{CV} \text{ (}\mu\text{A)}$ I: 漏电流 Leakage Current (μA), C: 容量 Capacitance (μF), V: 额定电压 Rated Voltage (V)							

<p>5</p>	<p>引线强度 Terminal strength</p>	<p>实验条件 Conditions: 引线抗拉强度 Tensile strength of termination: 沿电容器端子引线方向施加固定重力 5N, 10±1S。 A static load of 5N shall be applied to the terminal in the down-lead direction for 10±1S.</p> <table border="1" data-bbox="496 297 1350 488"> <thead> <tr> <th>端子线径 Diameter mm</th> <th>重力 Gravity (±10%)</th> <th>重锤重量 Weight (±10%)</th> </tr> </thead> <tbody> <tr> <td>0.35<d≤0.5</td> <td>5N</td> <td>0.51Kg</td> </tr> <tr> <td>0.5<d≤0.8</td> <td>10N</td> <td>1.02Kg</td> </tr> <tr> <td>0.8<d≤1.25</td> <td>20N</td> <td>2.04Kg</td> </tr> <tr> <td>SNAP-IN 型 端子</td> <td>40N</td> <td>4.08Kg</td> </tr> </tbody> </table> <p>判定标准 Criterion: 端子不得有松动、断裂及接触不良之情形。 The terminal should not be loose, breakage and bad connected.</p>	端子线径 Diameter mm	重力 Gravity (±10%)	重锤重量 Weight (±10%)	0.35<d≤0.5	5N	0.51Kg	0.5<d≤0.8	10N	1.02Kg	0.8<d≤1.25	20N	2.04Kg	SNAP-IN 型 端子	40N	4.08Kg
端子线径 Diameter mm	重力 Gravity (±10%)	重锤重量 Weight (±10%)															
0.35<d≤0.5	5N	0.51Kg															
0.5<d≤0.8	10N	1.02Kg															
0.8<d≤1.25	20N	2.04Kg															
SNAP-IN 型 端子	40N	4.08Kg															
<p>6</p>	<p>温度特性 Temperature characteristic</p>	<p>实验条件 Conditions:</p> <table border="1" data-bbox="496 913 1353 1151"> <thead> <tr> <th>步骤 Step</th> <th>温度 Temperature</th> <th>测量项目 Item</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>20±2℃</td> <td>阻抗 Impedance</td> </tr> <tr> <td>2</td> <td>下限类别温度 Lower Category temperature ±3℃</td> <td>阻抗 Impedance</td> </tr> <tr> <td>3</td> <td>上限类别温度 Upper Category temperature ±2℃</td> <td>漏电 LC</td> </tr> </tbody> </table> <p>要求达到热平衡后测量，并且阻抗在同一频率下测试 Testing when thermal equilibrium and Impedance must be on the same frequency. 判定标准 Criterion: 1.阻抗比不能超出表 1 所示值: Impedance ratio shall not exceed the values shown in Table 1. 2.LC≤800%初始规格值 2. Leakage current Shall not more than 800% of initial specified value.</p>	步骤 Step	温度 Temperature	测量项目 Item	1	20±2℃	阻抗 Impedance	2	下限类别温度 Lower Category temperature ±3℃	阻抗 Impedance	3	上限类别温度 Upper Category temperature ±2℃	漏电 LC			
步骤 Step	温度 Temperature	测量项目 Item															
1	20±2℃	阻抗 Impedance															
2	下限类别温度 Lower Category temperature ±3℃	阻抗 Impedance															
3	上限类别温度 Upper Category temperature ±2℃	漏电 LC															
<p>7</p>	<p>耐久性 Endurance test</p>	<p>实验条件 Conditions: 实验温度 Temperature : 105℃ 施加电压 Applied voltage: 额定电压 Rated voltage 实验时间 Test time : 2000H 测试条件 Test condition : 在标准大气压下保存 16 小时后进行测试 Test after keep on standard atmospheric conditions for 16 hours.</p> <p>判定标准 Criterion: 1.容量的变化: ΔC/C ≤±20%原规格值 Capacitance Change Rate: ΔC/C ≤±20% of initial value 2.损耗角正切: DF ≤2 倍原规格值 Dissipation Factor: DF ≤2 times original Spec value 3.漏电流: LC ≤原规格值 Leakage Current: LC ≤original Spec value 4.外观: 无明显损伤 Appearance: No visible damage.</p>															

<p>8</p>	<p>高温储存 High Temperature Exposure(Storage)</p>	<p>实验条件 Conditions: 实验温度 Temperature: 105℃ 施加电压 Applied voltage: 额定电压 Rated voltage 实验时间 Test time: 1000H 测试条件 Test condition: 在标准大气压下保存 16 小时后进行测试 Test after keep on standard atmospheric conditions for 16 hours.</p> <p>判定标准 Criterion: 1.容量的变化: $\Delta C/C \leq \pm 20\%$ 原规格值 Capacitance Change Rate: $\Delta C/C \leq \pm 20\%$ of initial value 2.损耗角正切: $DF \leq 2$ 倍原规格值 Dissipation Factor: $DF \leq 2$ times original Spec value 3.漏电流: $LC \leq$ 原规格值 Leakage Current: $LC \leq$ original Spec value 4.外观: 无明显损伤 Appearance: No visible damage</p>
<p>9</p>	<p>浪涌试验 Surge Test</p>	<p>实验条件 Conditions: 实验温度 Temperature: 15~35℃ 施加电压 Applied voltage: V 额\leq315V 时, 1.15 倍的额定电压 V 额$>$315V 时, 1.1 倍的额定电压 Rated voltage\leq315V, 1.15 times rated voltage Rated voltage$>$315V, 1.10 times rated voltage 周期 Period: 充电 30 秒, 放电 330 秒为一个周期。 Charge for 30 seconds, discharge for 330 seconds as a cycle 循环次数 Cycles: 1000 测试条件 Test Condition: 在标准大气压下保存 16 小时后进行测试。 Test after keep on standard atmospheric conditions for 16 hours.</p> <p>判定标准 Criterion: 1.容量的变化: $\Delta C/C \leq \pm 15\%$ 原规格值 Capacitance Change Rate: $\Delta C/C \leq \pm 15\%$ of initial value 2.损耗角正切: $DF \leq$ 原规格值 Dissipation Factor: $DF \leq$ Original Spec value 3.漏电流: $LC \leq$ 原规格值 Leakage Current: $LC \leq$ original Spec value 4. 外观: 无明显损伤 Appearance: No visible damage</p>
<p>10</p>	<p>振动 Vibration</p>	<p>实验条件 Conditions: 频率范围 Frequency Scope : 10~55HZ 振幅 Amplitude : 0.75mm 加速度 Acceleration : 98 m/s² (10g) 振动时间 Vibration Time : X、Y、Z 各方向循环各 2 小时、共计 6 小时 X, Y, Z directions each for 2 Hrs, total 6 Hrs. 测试条件 Test Condition : 从振动仪上取下电容后在 30 分钟内测试 Testing within 30 minutes after take it down from vibration machine</p> <p>判定标准 Criterion: 1.容量的变化: $\Delta C/C \leq \pm 5\%$ 原规格值 Capacitance Change Rate: $\Delta C/C \leq \pm 5\%$ of initial value 2.损耗角正切: $DF \leq$ 原规格值 Dissipation Factor: $DF \leq$ Original Spec value 3.漏电流: $LC \leq$ 原规格值 Leakage Current: $LC \leq$ original Spec value 4. 外观: 无明显损伤 Appearance: No visible damage</p>

<p>11</p>	<p>可焊性 Solderability</p>	<p>实验条件 Conditions: 焊锡种类 Kind of solder: Sn: 96.5%, Ag: 3%, Cu: 0.5%或是同等品。 Sn: 96.5%, Ag: 3%, Cu: 0.5% or equal article 锡炉温度 Solder stove temperature: 245±5℃ 浸锡时间 Immerse time: 2.0±0.5S 浸入或移出速度 Speed of immerse or leave: 25±2.5mm/s 浸入深度 Immerse depth: 浸入深度保持在电容本体与焊锡之间距离在 1.5~2.0mm。 1.5~2.0mm between the capacitor body and the solder. 试验次数 times: 1. 测试条件 Test Condition: 从锡炉中取出后 2 小时测试。 Testing after 2 hours for taking it out from the solder stove. 判定标准 Criterion: 1.容量的变化: $\Delta C/C \leq \pm 5\%$原规格值 Capacitance Change Rate: $\Delta C/C \leq \pm 5\%$ of initial value 2.损耗角正切: $DF \leq$原规格值 Dissipation Factor: $DF \leq$ Original Spec value 3.漏电流: $LC \leq$原规格值 Leakage Current: $LC \leq$original Spec value 4.新锡附着度应大于 95%。 Above 95% area of surroundings surface shall be covered by the new soldering.</p>												
<p>12</p>	<p>耐焊接热 Resistance to soldering heat</p>	<p>实验条件 Conditions: 焊锡种类 Kind of solder: Sn: 96.5%, Ag: 3%, Cu: 0.5%或是同等品。 Sn: 96.5%, Ag: 3%, Cu: 0.5% or equal article 锡炉温度 Solder stove temperature: 260 (0~3) °C 浸锡时间 Immerse time: 10±1S 浸入或移出速度 Speed of immerse or leave: 25±2.5mm/s 浸入深度 Immerse depth: 浸入深度保持在电容本体与焊锡之间距离在 1.5~2.0mm。 1.5~2.0mm between the capacitor body and the solder. 试验次数 times: 1. 测试条件 Test Condition: 从锡炉中取出后 2 小时测试。 Testing after 2 hours for taking it out from the solder stove. 判定标准 Criterion: 1.容量的变化: $\Delta C/C \leq \pm 5\%$原规格值 Capacitance Change Rate: $\Delta C/C \leq \pm 5\%$ of initial value 2.损耗角正切: $DF \leq$原规格值 Dissipation Factor: $DF \leq$ Original Spec value 3.漏电流: $LC \leq$原规格值 Leakage Current: $LC \leq$original Spec value</p>												
<p>13</p>	<p>防爆试验 Vent</p>	<p>实验条件 Conditions:</p> <table border="1" data-bbox="496 1417 1425 1686"> <thead> <tr> <th>试验方法 Method</th> <th>电压 Voltage</th> <th>尺寸 Size</th> <th>保持电流 Current</th> </tr> </thead> <tbody> <tr> <td>逆向电压法: 电容两端施加直流反向电压 80V。 Reverse Voltage:80V</td> <td>$0V \leq WV < 160V$</td> <td>$\phi \leq 22.4mm$ $\phi > 22.4mm$</td> <td>1A 10A</td> </tr> <tr> <td>过压法: 两端施加过电压 (工作电压的 1.5 倍) Over Voltage:1.5Rated voltage</td> <td>$WV \geq 160V$</td> <td>所有尺寸 Every Size</td> <td>1A</td> </tr> </tbody> </table> <p>判定标准 Criterion: 当防爆阀打开时, 不能有爆炸、闪火、燃烧等现象。 When the pressure relief vent operated, There shall be no explosion, flash, flame, spark or fire from the capacitor during or after the test. 如果防爆阀 30 分钟未打开, 判定防爆合格,仅适用于过压法。 If the vent does not operate with the voltage applied for 30 minutes, the test is considered to be passed only for the method of over voltage.</p>	试验方法 Method	电压 Voltage	尺寸 Size	保持电流 Current	逆向电压法: 电容两端施加直流反向电压 80V。 Reverse Voltage:80V	$0V \leq WV < 160V$	$\phi \leq 22.4mm$ $\phi > 22.4mm$	1A 10A	过压法: 两端施加过电压 (工作电压的 1.5 倍) Over Voltage:1.5Rated voltage	$WV \geq 160V$	所有尺寸 Every Size	1A
试验方法 Method	电压 Voltage	尺寸 Size	保持电流 Current											
逆向电压法: 电容两端施加直流反向电压 80V。 Reverse Voltage:80V	$0V \leq WV < 160V$	$\phi \leq 22.4mm$ $\phi > 22.4mm$	1A 10A											
过压法: 两端施加过电压 (工作电压的 1.5 倍) Over Voltage:1.5Rated voltage	$WV \geq 160V$	所有尺寸 Every Size	1A											

14	温度循环 Temperature Cycling	<p>实验条件 Conditions:</p> <table border="1" data-bbox="496 248 1377 416"> <thead> <tr> <th>阶段 Step</th> <th>温度 Temp.</th> <th>时间 Time (Min)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>下限类别温度±3℃</td> <td>30±3</td> </tr> <tr> <td>2</td> <td>25±5℃</td> <td>3</td> </tr> <tr> <td>3</td> <td>上限类别温度±2℃</td> <td>30±3</td> </tr> <tr> <td>4</td> <td>25±5℃</td> <td>3</td> </tr> </tbody> </table> <p>参照 JIC-5101-1 (2010) No:4.16, 从 1 到 4 为一个循环, 共需要 10 个循环。 Referring to JIC-5101-1 (2010) No:4.16 (1) to (4) = 1 cycle, total 10 cycles.</p> <p>判定标准 Criterion: 1.容量的变化: $\Delta C/C \leq \pm 5\%$ 原规格值 Capacitance Change Rate: $\Delta C/C \leq \pm 5\%$ of initial value 2.损耗角正切: $DF \leq$ 原规格值 Dissipation Factor: $DF \leq$ Original Spec value 3.漏电流: $LC \leq$ 原规格值 Leakage Current: $LC \leq$ original Spec value 4. 外观: 无明显损伤 Appearance: No visible damage</p>	阶段 Step	温度 Temp.	时间 Time (Min)	1	下限类别温度±3℃	30±3	2	25±5℃	3	3	上限类别温度±2℃	30±3	4	25±5℃	3
阶段 Step	温度 Temp.	时间 Time (Min)															
1	下限类别温度±3℃	30±3															
2	25±5℃	3															
3	上限类别温度±2℃	30±3															
4	25±5℃	3															
15	稳态湿热 High temp and humidity	<p>实验条件 Conditions: 温度 Temperature: 40±2℃ 湿度 Humidity: 90~95%RH 维持时间 Maintained Time: 250H 测试条件 Test Condition: 在标准大气压下保存 16 小时后进行测试 Test after keep on standard atmospheric conditions for 16 hours.</p> <p>判定标准 Criterion: 1.容量的变化: $\Delta C/C \leq \pm 20\%$ 原规格值 Capacitance Change Rate: $\Delta C/C \leq \pm 20\%$ of initial value 2.损耗角正切: $DF \leq 1.2$ 倍原规格值 Dissipation Factor: $DF \leq 1.2$ times of the original Spec. value 3.漏电流: $LC \leq$ 原规格值 Leakage Current: $LC \leq$ original Spec value 4. 外观: 无明显损伤 Appearance: No visible damage</p>															

三. CHARACTERISTICS TABLE

阻抗比值表 (表 1. TABLE 1)

额定电压 Rated Voltage(V)	≤400	450	500
Z-25℃/Z+20℃	8	8	10

四. 标示说明 MARKING:

例:

- (1) **CapXon:** 制造商标 Brand
- (2) **450V:** 电压 Rated Voltage
- (3) **680 μ F :** 容量 Nominal Capacitance
- (4)  : (-)负极指示 Polarity(Cathode Indicate)
- (5) **105℃:** 最高工作温度(Maximum Operating Temp.)
- (6) **UJ:** 系列 Series
- (7) **VENT:** 安全标示 Safety Vent

