









No. of Contacts	DIMENSIONS		
	DIM A	DIM B	DIM C
4	3.75	6.40	8.50
5	5.00	7.65	9.76
6	6.25	8.90	11.00
7	7.50	10.15	12.25
8	8.75	11.40	13.50
9	10.00	12.65	14.75
10	11.25	13.90	16.00
11	12.50	15.15	17.25
12	13.75	16.40	18.50
13	15.00	17.65	19.75
14	16.25	18.90	21.00
15	17.50	20.15	22.25
16	18.75	21.40	23.50
17	20.00	22.65	24.75
18	21.25	23.90	26.00
19	22.50	25.15	27.25
20	23.75	26.40	28.50
21	25.00	27.65	29.75
22	26.25	28.90	31.00
23	27.50	30.15	32.25
24	28.75	31.40	33.50
25	30.00	32.65	34.75
26	31.25	33.90	36.00
27	32.50	35.15	37.25
28	33.75	36.40	38.50
29	35.00	37.65	39.75
30	36.25	38.90	41.00
31	37.50	40.15	42.25
32	38.75	41.40	43.50
33	40.00	42.65	44.75
34	41.25	43.90	46.00
35	42.50	45.15	47.25
36	43.75	46.40	48.50
37	45.00	47.65	49.75
38	46.25	48.90	51.00
39	47.50	50.15	52.25
40	48.75	51.40	53.50



适用扁平电缆
Proper cable



Z: positive needle



F: negative needle

■ 技术参数 (SPECIFICATIONS)

- ◆ 极数: 4~40 Poles: 4~40
- ◆ 额定电压: AC, DC, 50V (50HZ有效值)
Voltage rating: AC, DC, 50V (50HZ)
- ◆ 额定电流: 0.5A, AC, DC
Current rating: 0.5A, AC, DC
- ◆ 耐压性: 500V AC/minute
Withstand voltage: 500V AC/minute
- ◆ 工作温度: -25°C~+85°C
Working Temperature: -25°C~+85°C
- ◆ 绝缘电阻: ≥800MΩ
Insulation resistance: ≥800MΩ
- ◆ 接触电阻: ≤0.02Ω
Contact resistance: ≤0.02Ω
- ◆ 单面接触
Single Contact
- 接触件 (TERMINAL)
 - ◆ 材质: 磷铜
Material: Phosphor Bronze
- 塑胶本体 (HOUSING)
 - ◆ 材质: 热塑性塑料, PA46 UL 94V-0 Black
Material: Thermoplastic, PA46, UL 94-0 Black
- 包装方式 (PACKAGE)
 - ◆ 管装: Pipe Package
 - ◆ 盒装: Box Package

X125 C 725 V XX X
① ② ③ ④ ⑤ ⑥

- ① Series Name: X125=1.25mm
- ② Vertical SMT
- ③ H=7.25mm
- ④ Welding Board Angle: V:180°
- ⑤ Number of terminals: XX=04-40PIN
- ⑥ Z: positive needle
F: negative needle

REVISIONS					UNSPECIFIED TOLERANCES	ANGLAR	±5°	DSND	SCALE: N/A	MODEL TYPE:		
ΔX						L ≤ 4	±0.2	DWN	VIEW:	FPC CONNECTOR		
ΔX						4 < L ≤ 16	±0.3	CHKD	UNIT: mm/in	PART NO.: X125C725VXXX		
ΔX						16 < L ≤ 63	±0.4	APPD	SIZE: A4	DWG NO.: X-X125C725VXXX		
MARK	DESCRIPTION	DATE	REVISED	APPROVED		L > 63	±0.5			WEIGHT	SHEET	REVISION
											1/1	A0

XKLB

XKB INDUSTRIAL PRECISION CO., LIMITED