





SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



P.C.B. LAYOUT

N = Number of poles  
 Dim L = N x 5.0  
 Dim B = (N - 1) x 5.0

	Dim L	Dim B
2-5p	±0.10	±0.10
6-9p	±0.15	±0.15
10-13p	±0.20	±0.20
14-17p	±0.25	±0.25
18-21p	±0.30	±0.30
22-24p	±0.40	±0.40

- Material:
- Item ① Terminal(housing): Thermoplastic (UL94V-0)
  - Item ② Contact pin: Brass
- Electrical: UL / VDE / TUV
- Voltage rating: 300V / 300V / 300V
  - Current rating: 15A / 12A / 15A
  - Withstanding Voltage: 1.6KV / 2.5KV / 2.5KV
  - Operating temperature: -40°C to +115°C (-40°C to +130°C)
  - Soldering temperature: PA66, 260°C ± 5°C / 5 Sec (PA46, 280°C / 10 Sec)
  - Safety Approval:
  - Critical dimension:

**OP xx 00 x x xxxx G**

POLES ————  
 02 pole  
 ... ..  
 24 pole

————— G RoHS compliant (lead<4%)  
 ———— In copper Alloy  
 ———— 0000: Standard  
 Any special item by customer request, please contact sales department.  
 ———— 0 PA 66  
 ———— 1 PA46

0 Tin plated 200u"  
 1 Gold plating 10u"  
 2 Gold flash

<b>ANYTEK</b>				<b>CUSTOMER COPY</b>			
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD							
TITLE		OP 5.0 Series 12.5mm		DWG NO.		80P0085	
PART NO.		OPxx00xxxxxxG		CUST NO.			
APPROVED	CHECKED	DESIGNED	DRAWN	Tolerance			
		Chen Bo 09/24`12	Chen Bo 09/24`12	UNIT: mm SCALE: NONE		X. ±0.50	
						X.X ±0.30	
SHEET: 01/01				REV.: B		X.XX ±0.10	
						X° ±1°	