

## DATASHEET

## ITR1204SR10A/TR

#### Features

- High sensitivity
- Cut-Off visible wavelength
- Compliance Halogen Free(Br < 900ppm, Cl < 900ppm, Br+Cl < 1500ppm)
- Compliance with EU REACH
- This product itself will remain within RoHS compliant version.

### Description

The SMD type ITR1204SR10A/TR consists of an infrared emitting diode and an silicon phototransistor. The phototransistor receives radiation from the IR only. This is the normal situation. But when a reflecting object close to ITR, phototransistor receives the reflecting radiation and the different distance have different light current.

### Applications

- Printer
- Switch Scanner
- Non-contact Switching

### **Device Selection Guide**

Device No.	Chip Material	Lens Color		
IR	GaAs	Black clear		
РТ	Silicon	Black clear		

### **Package Dimensions**



## **Recommended Soldering Pattern**

#### Notes:

- 1. All dimensions are in millimeters
- 2. Tolerances unless dimensions  $\pm 0.2$ mm
- 3. Lead spacing is measured where the lead emerge from the package

## Absolute Maximum Ratings (Ta=25°C)

Parameter		Symbol	Ratings	Unit	
Input	Power Dissipation at(or below) 25°C Free Air Temperature	Pd	75	mW	
	Reverse Voltage	V <sub>R</sub>	6	V	
	Forward Current	$I_{\rm F}$	50	mA	
Output	Collector Power Dissipation	P <sub>C</sub>	75	mW	
	Collector Current	I <sub>C</sub>	20	mA	
	Collector-Emitter Voltage	B V <sub>CEO</sub>	30	V	
	Emitter-Collector Voltage	B V <sub>ECO</sub>	5	V	
Operating Temperature		Topr	-25~+85	°C	
Storage Temperature		Tstg	-40~+100	°C	
Lead Soldering Temperature (*1)		Tsol	260	°C	
(1.1)	a				

 $(*1) t \leq 5$  Sec

## Electro-Optical Characteristics (Ta=25°C)

Parameter		Symbol	Min.	Тур.	Max.	Unit	Condition
Input	Forward Voltage	$V_{\rm F}$	-	1.25	1.5	V	I <sub>F</sub> =4mA
	Reverse Current	I <sub>R</sub>	-	-	10	μΑ	V <sub>R</sub> =6V
	Peak Wavelength	$\lambda_{\mathrm{P}}$	-	940	-	nm	I <sub>F</sub> =20mA
Output	Dark Current	I <sub>CEO</sub>	-	-	0.1	uA	V <sub>CE</sub> =10V
Transfer Characteristics	Collect Current	I <sub>C(ON)</sub>	60		130	μA	$V_{CE}=2V,$ $I_{F}=4mA$
	Operating Dark Current*	I <sub>CEOD</sub>			1	μΑ	$V_{CE}=2V,$ $I_{F}=2mA$
	Rise Time	Tr	-	15	-	μs	$\begin{array}{c} V_{CE} = 2V\\ I_C = 0.1mA\\ R_L = 1000\Omega \end{array}$
	Fall Time	T <sub>f</sub>	-	15	-	μs	

\*Operating dark current may be affected by surrounding situation.

### **Opto Characteristic Curves**







## Package Dimensions



### **Packing Quantity Specification**

- 1.2000PCS/1Bag , 10Bags/1Box
- 2.10Boxes/1Carton

### **Packing Procedure**



### Outer Carton Dimension : 409mm(A)\*245mm(B)\*360mm(C)



### **Recommended Method of Storage**

The following are general recommendations for moisture sensitive level (MSL) 3 storage and use :

- 1. Storage
- 1.1 Do not open moisture proof bag before the products are ready to use.
- 1.2 Before opening the package, the device should be kept at  $30^{\circ}$ C or less and 90%RH or less.
- 1.3 The device should be used within a year.
- 1.4 After opening the package, the device should be kept at 30°C or less and 70%RH or less.
- 1.5 The device should be used within 168 hours (7 days) after opening the package.
- 1.6 If the moisture absorbent material (silica gel) has faded away or the device have exceeded the storage time, baking

treatment should be performed using the following conditions. Baking treatment : 60±5°C for 24 hours.



### Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.

### **Label Form Specification**

## ROHS POEVERLIGHT

CPN:XXXXXXXXX

 QTY:
 HUE:

 QTY:
 HUE:

 CAT:
 REF:

 NUMBER
 NUMBER

 REFERENCE:
 NUMBER



 $\bigcirc$ 

CPN: Customer's Production Number P/N : Production Number QTY: Packing Quantity CAT: Ranks HUE: Peak Wavelength REF: Reference LOT No: Lot Number MADE IN TAIWAN: Production Place

### Disclaimer

- 1.EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
- 2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
- 3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
- 6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.

