Digital Transistors (Built-in Resistors)

Features

Insertion •NPN

•Epoxy meets UL-94 V-0 flammability rating

without connecting external input resistors


• Terminals: Tin plated leads, solderable per

•Surface mount package ideally Suited for Automatic


•Built-in bias resistors enable the configuration of an inverter circuit

• Moisure Sensitivity Level 1

Mechanical Data • Package: SOT-323



■Equivalent circuit



■Maximum Ratings (Ta=25°C Unless otherwise specified)

ITEM	SYMBOL	UNIT	CONDITIONS	VALUE
Supply Voltage	VCC	V		50
Input Voltage	VIN	V		-5to +12
Output Current	Ю	mA		100
Power Dissipation	PD	mW		200
Junction Temperature	Tj	°C		150
Storage Temperature	TSTG	°C		-55 to +150

DTC123YUA


■Electrical Characteristics (Ta=25°C unless otherwise specified)

ITEM	SYMBOL	UNIT	CONDITIONS	MIN	ТҮР	MAX
Input voltage	VI _(off)	V	VCC=5V,Ic=100uA	0.3		
	VI _(on)	V	V0=0.3V,Ic=20mA			3
Output voltage	Vo _(on)	V	lo /li =10mA/0.5 mA			0.3
Output current	I _{O(off)}	uA	VCC=50V, Vi=0			0.5
DC current gain	GI		Vo=5V, lo =10mA	33		
Input resistance	R ₁	kΩ		1.54	2.2	2.86
Resistance ratio	R_2/R_1			3.7	4.7	5.7
Transition frequency	fT	MHz	Vo=10V,IO=5mA,f=100MHz		250	

Ordering Information (Example)

PREFERED P/N	PACKING CODE	UNIT WEIGHT(g)	MINIMUM PACKAGE(pcs)	INNER BOX QUANTITY(pcs)	OUTER CARTON QUANTITY(pcs)	DELIVERY MODE	
DTC123YUA	F2	Approximate 0.008	3000	30000	120000	7" reel	


Characteristics (Typical)



2/4

Ń


DTC123YUA



3/4




SOT-323 Package Outline Dimensions



DIMENSIONS						
	INCHES		м			
DIM	MIN	MAX	MIN	MAX	NOTE	
Α	.071	.087	1.80	2.20		
В	.045	.053	1.15	1.35		
С	.083	.096	2.10	2.45		
D	.026 Nominal		0.65Nominal			
E	.047	.055	1.20	1.40		
F	.012	.016	.30	.40		
G	.000	.004	.000	.100		
Н	.035	.039	.90	1.00		
J	.004	.010	.100	.250		
K	.006	.016	.15	.40		

SOT-323 Suggested Pad Layout



Disclaimer

The information presented in this document is for reference only. Yangzhou Yangjie Electronic Technology Co., Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of with would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), Yangjie or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.

This publication supersedes & replaces all information previously supplied. For additional information, please visit our website http:// www.21yangjie.com , or consult your nearest Yangjie's sales office for further assistance.