Class I Div 2 certified accelerometer 786A-D2

SPECIFICATIONS

Sensitivity, ±5%, 25°C	100 mV/g
Acceleration range	80 g peak
Amplitude nonlinearity	1%
Frequency response: ±5% ±10% ±3 dB	3 - 5,000 Hz 1 - 9,000 Hz 0.5 - 14,000 Hz
Resonance frequency	30 kHz
Transverse sensitivity, max	5% of axial
Temperature response: -55°C +120°C	-20% +10%
Power requirement: Voltage source Current regulating diode	18 - 28 VDC 2 - 10 mA
Electrical noise, equiv. g: Broadband 2.5 Hz to 25 kHz Spectral 10 Hz 100 Hz 1,000 Hz	700 μg 10 μg/√Hz 5 μg/√Hz 5 μg/√Hz
Output impedance, max	100 Ω
Bias output voltage	12 VDC
Grounding	case isolated, internally shielded
Temperature range	–55° to +120°C
Vibration limit	500 g peak
Shock limit	5,000 g peak
Electromagnetic sensitivity, equiv. g, max	70 μg/gauss
Sealing	hermetic
Base strain sensitivity, max	0.0002 g/µstrain
Sensing element design	PZT ceramic / shear
Weight	90 grams
Case material	316L stainless steel
Mounting	1/4-28 UNF tapped hole
Output connector	2 pin, MIL-C-5015 style
Mating connector	R6D2
Recommended cabling	J10 / J9T2A

Accessories supplied: SF6 mounting stud; calibration data (level 2)

Certifications



Class I, Div 2 Groups A, B, C, D Class I, Zone 2 S AEx/Ex nA II T4 Tamb: -50°C to 120°C

Ex nA IIC T4 Gc

Must be installed per 13029. • Ambient temperature range depends on the type cable used during installation. • Cable with FEP jacket, Ta=-50°C to +120°C. • Cable with Santoprene jacket, Ta=-45°C to +115°C.

Note: Due to continuous process improvement, specifications are subject to change without notice. This document is cleared for public release.


Wilcoxon Sensing Technologies An Amphenol Company 98981 Rev.C.3 12/18 8435 Progress Drive Frederick, MD 21701 USA Tel: +1 (301) 330-8811 Fax: +1 (301) 330-8873 info@wilcoxon.com

buy.wilcoxon.com www.wilcoxon.com



Key features

- Class I, Div 2/Zone 2 certified, non-incendive
- API 670 compliant
- MTBF 25 years
- Manufactured in ISO 9001 facility



1/4-28 mounting thread—

