


BAS321

Small-Signal Switching Diodes



Features

- VR 200V
- I_{FAV} 200mA

Typical Applications

- Extreme fast switches

Mechanical Data

- **Package:** SOD323
- **Terminals:** Tin plated leads, solderable per J-STD-002 and JESD22-B102
- **Polarity:** Cathode line denotes the cathode end
- **Marking:** T3

■Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	Conditions	VALUE
Repetitive peak reverse voltage	V _{RRM}	V		250
Reverse Voltage	V _R	V		200
Non-Repetitive Peak Forward Surge Current	I _{FSM}	A	t=8.3ms, Half sine-wave	2
Average forward current	I _{FAV}	mA		200
Power dissipation	P _D	mW		250
Junction temperature	T _j	°C		150
Storage temperature range	T _{stg}	°C		-55 to +150

■Electrical Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	Conditions	Min	Max
Maximum Forward voltage	VF	V	I _F =100mA		1.0
			I _F =200mA		1.25
Maximum Reverse current	IR	nA	VR=200V		100
Minimum Breakdown voltage	V _R	V	I _R =10uA	200	
Maximum Diode capacitance	C _D	pF	V _R =0V, f =1MHz		5
Maximum Reverse recovery time	t _{rr}	ns	IF=IR=30 mA,RL=100Ω,IRR=3mA		50






BAS321

Ordering Information (Example)

PREFERRED P/N	PACKING CODE	UNIT WEIGHT(g)	MINIMUM PACKAGE(pcs)	INNER BOX QUANTITY(pcs)	OUTER CARTON QUANTITY(pcs)	DELIVERY MODE
BAS321	F2	Approximate 0.004	3000	30000	120000	7" reel


Characteristics(Typical)






BAS321

■ SOD-323 Package Outline Dimensions



Symbol	Min. (mm)	Max. (mm)
A		1.000
A1	0.000	0.100
A2	0.800	0.900
b	0.250	0.400
c	0.080	0.150
D	1.200	1.400
E	1.600	1.800
E1	2.500	2.700
L	0.475REF	
L1	0.250	0.400
θ	0°	8°

■ SOD-323 Soldering Footprint



Unit: inches



BAS321

Disclaimer

The information presented in this document is for reference only. Yangzhou Yangjie Electronic Technology Co., Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), Yangjie or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.

This publication supersedes & replaces all information previously supplied. For additional information, please visit our website [http:// www.21yangjie.com](http://www.21yangjie.com) , or consult your nearest Yangjie's sales office for further assistance.