


P-Channel Enhancement Mode Field Effect Transistor



DFN3.3X3.3

Product Summary

- V_{DS} -30V
- I_D -50A
- $R_{DS(ON)}$ (at $V_{GS}=-10V$) <6.2mohm
- $R_{DS(ON)}$ (at $V_{GS}=-4.5V$) <11mohm
- 100% ∇V_{DS} Tested

General Description

- Trench Power LV MOSFET technology
- High Power and current handling capability

Applications

- High current load applications
- Load switching
- Hard switched and high frequency circuits
- Uninterruptible power supply

■ Absolute Maximum Ratings ($T_A=25^\circ C$ unless otherwise noted)

Parameter		Symbol	Limit	Unit
Drain-source Voltage		V_{DS}	-30	V
Gate-source Voltage		V_{GS}	± 25	V
Drain Current	$T_C=25^\circ C$	I_D	-50	A
	$T_C=70^\circ C$		-40	
Pulsed Drain Current ^A		I_{DM}	-200	A
Total Power Dissipation	$T_C=25^\circ C$	P_D	83	W
	$T_A=25^\circ C$		5.2	W
Junction and Storage Temperature Range		T_J, T_{STG}	-55~+150	$^\circ C$

■ Thermal resistance

Parameter		Symbol	Typ	Max	Units
Junction to Ambient @Maximum ^B	$t \leq 10S$	$R_{\theta JA}$	18	24	$^\circ C/W$
Junction to Ambient @Maximum ^{BC}	Steady-State		36	50	
Junction to Case @Maximum	Steady-State	$R_{\theta JC}$	1	1.5	

■ Ordering Information (Example)

PREFERRED P/N	PACKING CODE	Marking	MINIMUM PACKAGE(pcs)	INNER BOX QUANTITY(pcs)	OUTER CARTON QUANTITY(pcs)	DELIVERY MODE
YJQ50P03A	F1	Q50P03A	5000	10000	100000	13" reel



YJQ50P03A

■ Electrical Characteristics (T_J=25°C unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Static Parameter						
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} = 0V, I _D =-250μA	-30			V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =-30V, V _{GS} =0V			-1	μA
Gate-Body Leakage Current	I _{GSS}	V _{GS} = ±25V, V _{DS} =0V			±100	nA
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D =-250μA	-1.2	-1.8	-2.8	V
Static Drain-Source On-Resistance	R _{DS(on)}	V _{GS} = -10V, I _D = -15A		5.0	6.2	mΩ
		V _{GS} = -4.5V, I _D = -10A		6.9	11	
Diode Forward Voltage	V _{SD}	I _S = -15A, V _{GS} =0V			-1.2	V
Dynamic Parameters						
Input Capacitance	C _{iss}	V _{DS} =-15V, V _{GS} =0V, f=1MHZ		6464		pF
Output Capacitance	C _{oss}			779		
Reverse Transfer Capacitance	C _{rss}			477		
Switching Parameters						
Total Gate Charge	Q _g	V _{GS} = -10V, V _{DS} = -15V, I _D = -20A		111.7		nC
Gate-Source Charge	Q _{gs}			21.1		
Gate-Drain Charge	Q _{gd}			22.9		
Reverse Recovery Charge	Q _{rr}	I _F =-20A, di/dt=100A/μs		8.5		ns
Reverse Recovery Time	t _{rr}			24		
Turn-on Delay Time	t _{D(on)}	V _{GS} = -10V, V _{DD} = -15V, R _G =3Ω, R _L = 0.75Ω		15		ns
Turn-on Rise Time	t _r			79		
Turn-off Delay Time	t _{D(off)}			136		
Turn-off fall Time	t _f			80		

A: Pulse Test: Pulse Width ≤ 300μs, Duty cycle ≤ 2%.

B: The value of R_{θJA} is measured with the device mounted on 1 in² FR-4 board with 2oz, Copper, in a still air environment with T_A = 25°C, The Value in any given application depends on the user's specific board design.

C: The R_{θJA} is the sum of the thermal impedance from junction to lead R_{θJC} and lead to ambient.



■ Typical Performance Characteristics




Figure1. Output Characteristics




Figure2. Transfer Characteristics




Figure 3: On-Resistance vs. Drain Current and Gate Voltage




Figure 4: On-Resistance vs. Junction Temperature




Figure5. Capacitance Characteristics




Figure6. Gate Charge



YJQ50P03A




Figure7. Safe Operation Area




Figure8. Maximum Continuous Drain Current vs Case Temperature










Figure9. Normalized Maximum Transient Thermal Impedance





Resistive Switching Test Circuit & Waveforms



Diode Recovery Test Circuit & Waveforms



Gate Charge Test Circuit & Waveform




Unclamped Inductive Switching (UIS) Test Circuit & Waveforms




YJQ50P03A


■ DFN3.3×3.3 Package information



Top View
正面视图




Bottom View
背面视图



Side View
侧面视图

SYMBOL	MILLIMETER		
	MIN	NOM	MAX
D	3.15	3.25	3.35
E	3.15	3.25	3.35
A	0.70	0.80	0.90
A1	0.20 BSC		
A2			0.10
D1	2.20	2.35	2.50
E1	1.80	1.90	2.00
L1	0.35	0.45	0.55
L2	0.35 BSC		
b	0.20	0.30	0.40
e	0.65 BSC		



Suggested Solder Pad Layout
Top View

Note:

1. Controlling dimension: in millimeters.
2. General tolerance: $\pm 0.10\text{mm}$.
3. The pad layout is for reference purposes only.



YJQ50P03A

Disclaimer

The information presented in this document is for reference only. Yangzhou Yangjie Electronic Technology Co., Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), Yangjie or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.

This publication supersedes & replaces all information previously supplied. For additional information, please visit our website [http:// www.21yangjie.com](http://www.21yangjie.com) , or consult your nearest Yangjie's sales office for further assistance.