General purpose triaxial accelerometers 993B series

SPECIFICATIONS


	993B-5	993B-6	993B-7
Sensitivity, ±10%, 25°C	25 mV/g	50 mV/g	100 mV/g
Acceleration range	160 g peak	80 g peak	40 g peak
Amplitude nonlinearity	1%		
Frequency response ¹ : Z axis, ±3 dB X and Y axes, ±3 dB	2 - 10,000 Hz 2 - 7,000 Hz		
Transverse sensitivity, max	7% of axial		
Power requirement: Voltage source Current regulating diode	18 - 30 VDC 2 - 5 mA		
Electrical noise, equiv. g, nominal: Broadband 2.5 Hz to 25 kHz Spectral 10 Hz 100 Hz 1,000 Hz	336 µg 24 µg/√Hz 3.2 µg/√Hz 2.0 µg/√Hz	220 μg 15 μg/√Hz 2.0 μg/√Hz 1.1 μg/√Hz	160 μg 10 μg/√Hz 1.4 μg/√Hz 1.0 μg/√Hz
Output impedance, max	400 Ω		
Bias output voltage	11 VDC		
Grounding	case isolated, internally shielded		
Turn-on time	<1 sec		
Temperature range	–50° to +120°C		
Vibration limit	500 g peak		
Shock limit	5,000 g peak		
Electromagnetic sensitivity, equiv. g	100 μg/gauss		
Sealing	hermetic		
Base strain sensitivity, max	0.0005 g/µstrain		
Hydrostatic pressure, max	100 psi (IP68)		
Weight (excluding cable)	134 grams		
Case material	316L stainless steel		
Cable	integral, 16 ft. Teflon [®] J9T4B, armored		
Cable termination ²	stripped and tinned		
Mounting	10-32 captive screw		


Ministry Constraints

SENSING TECHNOLOGIES

Key features

- Hazardous area certified versions available (models 993B-5-33, 993B-6-33, and 993B-7-33)
- Manufactured in ISO 9001 facility





Notes: ¹ As measured using the mounting screw.

² Optional cable terminations: R11D (11-pin Fischer), R9W (4-pin Bendix), R21 (4-pin Amp), 3xR2 (BNC)

Accessories supplied: 10-32 captive screw; calibration data (level 2)



Connections		
Function	Cable conductor color	
X axis, power/signal	green	
Y axis, power/signal	red	
Z axis, power/signal	white	
common (all channels)	black	
N/C	shield	

Note: Due to continuous process improvement, specifications are subject to change without notice. This document is cleared for public release.

Wilcoxon Sensing Technologies An Amphenol Company 98872 Rev.E.2 09/18 8435 Progress Drive Frederick, MD 21701 USA Tel: +1 (301) 330-8811 Fax: +1 (301) 330-8873 info@wilcoxon.com

buy.wilcoxon.com www.wilcoxon.com