



V_{DS} = -20V**R_{DS(ON)}, V_{GS}@-4.5V, I_{DS}@-4.1A < 52mΩ****R_{DS(ON)}, V_{GS}@-2.5V, I_{DS}@-3.0A < 75mΩ****Features**

Advanced trench process technology

High Density Cell Design For Ultra Low On-Resistance

Package Dimensions

REF.	Millimeter		REF.	Millimeter	
	Min.	Max.		Min.	Max.
A	2.80	3.00	G	1.80	2.00
B	2.30	2.50	H	0.90	1.1
C	1.20	1.40	K	0.10	0.20
D	0.30	0.50	J	0.35	0.70
E	0	0.10	L	0.92	0.98
F	0.45	0.55	M	0°	10°

Maximum Ratings and Thermal Characteristics (TA = 25°C unless otherwise noted)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V _{DS}	-20	V
Gate-Source Voltage	V _{GS}	±12	
Continuous Drain Current	I _D	-4.1	A
Pulsed Drain Current ¹⁾	I _{DM}	-15	
Maximum Power Dissipation ²⁾	P _D	1.25	W
		0.8	
Operating Junction and Storage Temperature Range	T _J , T _{stg}	-55 to 150	°C
Junction-to-Ambient Thermal Resistance (PCB mounted) ²⁾	R _{thJA}	100	°C/W
Junction-to-Ambient Thermal Resistance (PCB mounted) ³⁾		166	

Notes

1) Pulse width limited by maximum junction temperature.







2) Surface Mounted on FR4 Board, t ≤ 5 sec.







3) Surface Mounted on FR4 Board.



ELECTRICAL CHARACTERISTICS

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Static						
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{GS} = 0V, I_D = -250\mu A$	-20			V
Drain-Source On-State Resistance ¹⁾	$R_{DS(on)}$	$V_{GS} = -4.5V, I_D = -4.1A$		46	52	$m\Omega$
		$V_{GS} = -2.5V, I_D = -3.0A$		60	75	
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D = -250\mu A$	0.4		1	V
Zero Gate Voltage Drain Current 0	I_{DSS}	$V_{DS} = -20V, V_{GS} = 0V$			-1	μA
		$V_{DS} = -20V, V_{GS} = 0V, TJ=55^\circ C$			-10	
Gate Body Leakage	I_{GSS}	$V_{GS} = \pm 12V, V_{DS} = 0V$			± 100	nA
Forward Transconductance ¹⁾	g_{fs}	$V_{DS} = -5V, I_D = -3.5A$		6.5	—	S
Dynamic						
Total Gate Charge	Q_g	$V_{DS} = -6V, I_D \equiv -3.5A$ $V_{GS} = -4.5V$		5.8		nC
Gate-Source Charge	Q_{gs}			0.85		
Gate-Drain Charge	Q_{gd}			1.7		
Turn-On Delay Time	$t_{d(on)}$	$V_{DD} = -6V, RL=6\Omega$ $I_D \equiv -1A, V_{GEN} = -4.5V$ $R_G = 6\Omega$		13		ns
Turn-On Rise Time	t_r			36		
Turn-Off Delay Time	$t_{d(off)}$			42		
Turn-Off Fall Time	t_f			34		
Input Capacitance	C_{iss}	$V_{DS} = -6V, V_{GS} = 0V$ $f = 1.0 \text{ MHz}$		415		pF
Output Capacitance	C_{oss}			223		
Reverse Transfer Capacitance	C_{rss}			87		
Source-Drain Diode						
Max. Diode Forward Current	I_s				-1.6	A
Diode Forward Voltage	V_{SD}	$I_s = -1.6A, V_{GS} = 0V$		-0.8	-1.2	V

¹⁾ Pulse test: pulse width <= 300us, duty cycle<= 2%

Typical Electrical and Thermal Characteristics**Figure 1:Switching Test Circuit****Figure 2:Switching Waveforms** T_j -Junction Temperature(°C)**Figure 3 Power Dissipation** T_j -Junction Temperature(°C)**Figure 4 Drain Current****Figure 5 Output Characteristics****Figure 6 Drain-Source On-Resistance**

**Figure 7 Transfer Characteristics****Figure 8 Drain-Source On-Resistance****Figure 9 Rdson vs Vgs****Figure 10 Capacitance vs Vds****Figure 11 Gate Charge****Figure 12 Source-Drain Diode Forward**

**Figure 13 Safe Operation Area****Figure 14 Normalized Maximum Transient Thermal Impedance**