

POWER RELAY 1 POLE - 16A Relay

FTR-K2 Series

■ FEATURES

SPST-NO

• High insulation

Insulation distance: minimum 6mm between coil and contact

Dielectric strength: 4KV Surge strength: 10KV

• TV-5 rating

 Heat resistance, flammability class B (130°C) wire class, flammability 94V-0

• Cadmium free contact for eco-program

Safety standards
 UL, CSA, VDE approved
 UL/CSA TV-5 rating approved

• Flux proof sealing, RTII

RoHS compliant
 Please see page 6 for more information



PARTNUMBER INFORMATION

	FTR-K2	Α	K	012	T	-	OK
[Example]	(a)	(b)	(c)	(d)	(e)		(f)

(a)	Relay type	FTR-K2	: FTR-K2-Series
(b)	Contact configuration	А	: 1 form A (SPST-NO)
(c)	Coil type	K	: Standard type (530mW)
(d)	Coil rated voltage	012	: 548 VDC Coil rating table at page 3
(e)	Contact material / TV type	Т	: Silver-tin oxide / TV-5
(f)	Special type	None TH OK	: Standard (TV-5) : TV-8 rating : 1.0mm contact gap

Actual marking does not carry the type name: "FTR"

E.g.: Ordering code: FTR-K2AK012T Actual marking: K2AK012T

1

■ SPECIFICATION

Item			FTR-K2AK () T		
Contact Data	Configuration		1 form A (SPST-NO)		
	Construction		Single		
	Material		Silver tin oxide (AgSnO ₂)		
	Resistance (initial)		Max. 100mΩ at 1A, 6VDC		
	Contact rating (resistive	2)	250VAC / 30VDC / 16A		
	Max. carrying current		16A		
	Max. switching voltage		400VAC / 300VDC		
	Max. switching power		4,000VA / 480W		
	Min. switching load*		100mA, 5VDC		
Life	Mechanical		Min. 2 x 10 ⁶ operations		
		DC contact rating	Min. 100 x 10 ³ operations		
	Electrical	AC contact rating	Min. 100 x 10 ³ operations		
		Lamp load (TV-5)	Min. 25 x 10 ³ operations		
Coil Data	Rated power (20 °C)		530mW		
	Operate power (20 °C)		260mW		
	Operating temperature range		-40 °C to +70 °C (no frost)		
Timing Data	Operate (at nominal voltage)		Max. 15ms (without bounce)		
	Release (at nominal voltage)		Max. 5ms (without bounce)		
Insulation	Resistance (initial)		Min. 1,000MΩ at 500VDC		
	Dielectric strength	Open contacts	1,000VAC (50/60Hz) 1min		
	Diciectific strength	Contacts to coil	4,000VAC (50/60Hz) 1min		
	Surge strength	Coil to contacts	10,000V / 1.2 x 50µs standard wave		
	Clearance		6mm		
	Creepage		6mm		
	EN61810-1, VDE0435	Voltage	250V		
		Pollution degree	3		
		Material group	III a		
		Category	B / 250V		
Other	Vibration resistance	Misoperation>1us	10 to 55 to 10Hz single amplitude 0.75mm		
	Vibration resistance	Endurance	10 to 55 to 10Hz single amplitude 0.75mm		
	Shock Misoperation> Endurance		200m/s² (11 ± 1ms)		
			1,000m/s² (6 ± 1ms)		
	Weight		Approximately 13g		
	Sealing		Flux proof (RT II)		

^{*} Minimum switching loads mentioned above are reference values. Please perform the confirmation test with actual load before production since reference values may vary according to switching frequencies, environmental conditions and expected reliability levels.

Care shall be taken on the heat generated on PC board when maximum carrying current exceeds 10A. Please perform the confirmation test with actual conditions.

■ COIL RATING

Coil Code	Rated Coil Voltage (VDC)	Coil Resistance +/- 10% (Ohm)	Must Operate Voltage (VDC) *	Must Release- Voltage (VDC) *	Rated Power (mW)	
003	3	17	2.1	0.15		
005	5	47	3.5	0.25		
006	6	68	4.2	0.3		
009	9	155	6.3	0.45	530	
012	12	270	8.4	0.6	330	
018	18	610	12.6	0.9		
024	24	1,110	16.8	1.2		
048	48	4,400	33.6	2.4		

Note: All values in the table are valid for 20°C and zero contact current.

* Specified operate values are valid for pulse wave voltage.

Please use at rated coil voltage. Please refer to characteristic data and set up adequate voltage in case of use at over voltage.


SAFETY STANDARDS


Туре	Compliance	Contact rating
UL	UL 508	Flammability: UL 94-V0 (plastics)
	E63614	16A, 30VDC (resistive) 15A, 140VAC (resistive)
CSA	C22.2 No. 14 LR 40304	10A, 277VAC (resistive) 1/2 HP,125VAC (UL), 1/3 HP 125VAC (CSA) TV-5, 120 VAC, TV-8, 120VAC Pilot duty: A300 (UL), C300 (CSA)
VDE	IEC/EN61810-1 EN60065 clause 14.6.1	16A, 250 VAC (cosφ=1) 8A, 250 VAC cosφ=0.4) 16A, 30 VDC (0ms) 250VAC 5/80A inrush
CQC	GB/T21711-1 GB15092-1 03001008195	<ftr-k2ak()t=""> 16A 250VAC</ftr-k2ak(>


3


■ CHARACTERISTIC DATA


(Characteristic data is not guaranteed value but measured values of samples from production line.)















DIMENSIONS


Dimensions



● Schematics (BOTTOM VIEW) 1 2 COM ○ NO ○

PC board mounting hole layout

Orientation mark



Unit: mm

^{*} Dimensions of the terminals do not include thickness of pre-solder.

^{*} Tolerance of PC board mounting hole layout : ±0.1 unless otherwise specified.

CAUTIONS

- All values mentioned in this datasheet are provided under ideal conditions. Please perform the confirmation test before actual use.
- Reflow soldering is prohibited.
- Do not use relays in the atmosphere with sulfide gas, chloride gas or nitric oxide. Contact resistance may increase.
- Do not use silicon or silicon-containing product or materials near relays. It may cause contact failure.

GENERAL INFORMATION

1. ROHS Compliance

• All relays produced by Fujitsu Components are compliant with RoHS directive 2011/65/EU, including commission delegated directive 2015/863.

2. Recommended lead free solder condition

- Lead free solder plating on relay terminals is Sn-3.0Ag-0.5Cu, unless otherwise specified. This material has been verified to be compatible with PbSn assembly process.
- Recommended solder for assembly: Sn-3.0Aq-0.5Cu.

Flow Solder Condition:

Pre-Heating: maximum 120°C

within 90 sec.

Soldering: dip within 5 sec. at 255°C±5°C solder bath

Relay must be cooled by air immediately after soldering

Solder by Soldering Iron:

Soldering Iron: 30-60W

Temperature: maximum 340-360°C Duration: maximum 3 sec.

We highly recommend that you confirm your actual solder conditions

3. Moisture Sensitivity

• Moisture Sensitivity Level standard is not applicable to electromechanical relays, unless otherwise indicated.

4. Tin Whiskers

• Dipped SnAgCu solder is known as presenting a low risk to tin whisker development. No considerable length whisker was found by our in house test.

Fujitsu Components International Headquarter Offices

Japan

FUJITSU COMPONENT LIMITED Shinagawa Seaside Park Tower 19F,

12-4, Higashi-shinagawa 4-chome, Shinagawa-ku,

Tokyo,140-0002, Japan Tel: (81-3) 3450-1682 Fax: (81-3) 3474-2385

Email: fcl-contact@cs.jp.fujitsu.com Web: www.fujitsu.com/jp/fcl/

North and South America

FUJITSU COMPONENTS AMERICA, INC 1230 E. Arques Ave. M/S 160 Sunnyvale, CA. 94085, USA Tel: (1-408) 745-4900 Fax: (1-408) 745-4970

Email: components@us.fujitsu.com Web: us.fujitsu.com/components

Europe FUJITSU COMPONENTS EUROPE B.V.

Diamantlaan 25 2132 WV Hoofddorp Netherlands Tel: (31-23) 5560910

Fax: (31-23) 5560950 Email: info@fceu.fujitsu.com

Web: www.fujitsu.com/uk/components

Asia Pacific

FUJITSU COMPONENTS ASIA, LTD. 102E Pasir Panjang Road #01-01 Citilink Warehouse Complex

Singapore 118529

Tel: (65) 6375-8560 Fax: (65) 6273-3021 Email: fcal@sg.fujitsu.com

Web: www.fujitsu.com/sg/products/devices/components

China

FUIITSU ELECTRONIC COMPONENTS (SHANGHAI) CO., LTD.

Unit 4306, InterContinental Center 100 Yu Tong Road, Shanghai 200070,

China

Tel: (86-21) 3253 0998 Fax: (86-21) 3253 0997 Email: fcsh@cn.fujitsu.com

Web: www.fujitsu.com/cn/products/devices/components/

Hong Kong FUJITSU COMPONENTS HONG KONG CO., LTD

Unit 506, Inter-Continental Plaza

No.94 Granville Road, Tsim Sha Tsui, Kowloon,

Hong Kong

Tel: (852) 2881-8495 Tex: (852) 2894-9512 Email: fcal@sg.fujitsu.com

Web: www.fujitsu.com/sq/products/devices/components/

Когеа

FUJITSU COMPONENTS KOREA LIMITED Alpha Tower #403, 645 Sampyeong-dong, Bundang-gu, Seongnam-si, Gyeonggi-do,

13524 Korea Tel: (82) 31-708-7108

Fax: (82) 31-709-7108 Email: fcal@sq.fujitsu.com

www.fujitsu.com/sg/products/devices/components/

© 2020 Fujitsu Components Europe B.V. All rights reserved. All trademarks or registered trademarks are the property of their respective owners.

The contents, data and information in this datasheet are provided by Fujitsu Component Ltd. as a service only to its user and only for general information purposes. The use of the contents, data and information provided in this datasheet is at the users' own risk.

Fujitsu has assembled this datasheet with care and will endeavor to keep the contents, data and information correct, accurate, comprehensive complete and up to

Fujitsu Components Europe B.V. and affiliated companies do however not accept any responsibility or liability on their behalf, nor on behalf of its employees, for any loss or damage, direct, indirect or consequential, with respect to this datasheet, its contents, data, and information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof.

Nor do Fujitsu Components Europe B.V. and affiliated companies accept on their behalf, nor on behalf of its employees, any responsibility or liability with respect to these datasheets, its contents, data, information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Rev. September 15, 2020