

## Solid-state contactor - ELR 1-SC-24DC/600AC-20 - 1032919


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Single-phase solid-state contactor, input voltage: 24 V DC, output current: 20 A, zero voltage switch



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 537726
GTIN	4055626537726

### Technical data

#### Dimensions

Width	18 mm
	18 mm
Height	110 mm
	110 mm
Depth	103 mm
	103 mm

#### Ambient conditions

Ambient temperature (operation)	-30 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C

#### Input data

Input name	Control input
Rated actuating voltage $U_c$	24 V DC
Triggering voltage range	4 V DC ... 32 V DC
Rated actuating current $I_c$	approx. 12 mA
Switching threshold	$\leq 1$ V DC ("0" signal)
	$\geq 4$ V DC ("1" signal)

# Solid-state contactor - ELR 1-SC-24DC/600AC-20 - 1032919

## Technical data

### Input data

Transmission frequency	25 Hz
Operating voltage display	Green LED

### Output data load output

Output name	Load output
Operating voltage range	42 V AC ... 660 V AC
Load current range	150 mA ... 20 A (see to derating)
Rated operating current at AC-51	20 A
Rated operating current at AC-53a	5 A (T <sub>A</sub> = 25 °C)
	5 A (T <sub>A</sub> = 40 °C)
Leakage current	< 3 mA (In off state)
Residual voltage	< 1 V
Surge current	325 A (t = 10 ms)
Type of protection	Varistor

### General

Mounting position	Vertical (horizontal DIN rail)
Assembly instructions	Can be aligned with ≥ 22.5 mm spacing

### Connection data

Connection name	Control circuits
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section solid	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section flexible	0.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section AWG	18 ... 12

### Connection data 2

Connection name	Load circuit
Connection method	Screw connection
Stripping length	12 mm
Screw thread	M4
Conductor cross section solid	2.5 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Conductor cross section flexible	1 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross section AWG	14 ... 10

### Standards and Regulations

Designation	Standards/regulations
Standards/regulations	EN 61000-4-2
	EN 61000-4-3
	EN 61000-4-4
	EN 61000-4-5



# Solid-state contactor - ELR 1-SC-24DC/600AC-20 - 1032919

## Technical data

### Standards and Regulations

	EN 55011
--	----------

## Drawings



## Classifications

### eCl@ss

eCl@ss 10.0.1	27371014
eCl@ss 11.0	27371014
eCl@ss 6.0	27371000
eCl@ss 7.0	27371014
eCl@ss 9.0	27371014

### ETIM

ETIM 5.0	EC002055
ETIM 6.0	EC002055
ETIM 7.0	EC002055

## Approvals

### Approvals

#### Approvals

UL Listed / cUL Listed / EAC / cULus Listed


#### Ex Approvals

### Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 323771
-----------	--	---	---------------

## Solid-state contactor - ELR 1-SC-24DC/600AC-20 - 1032919

### Approvals

cUL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 323771
------------	---	---	---------------

EAC		RU C- DE*.B.0080120
-----	---	------------------------

cULus Listed	
--------------	---

Phoenix Contact 2021 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>