

POWER RELAY 1 POLE - 3A/5A Slim Type Relay

FTR-F3 Series

■ FEATURES

High density mounting
 Slim type with 7mm width and 142mm² mounting space
 1C type; height 15mm and 164 mm² mounting space
 right angle type; height 7mm, 330 mm² mounting space

High insulation

Insulation distance:

minimum 6mm (7mm for 1C and right angle type) between coil and contact (conforms to IEC 60065) Dielectric strength: 4KV

Surge strength: 10KV

- Cadmium free contact for eco-program
- Safety standards

UL, CSA, VDE, SEMKO, CQC

- Plastic sealed relay, RTIII
- RoHS compliant

Please see page 7 for more information





■ PARTNUMBER INFORMATION

[Example] $\frac{\text{FTR-F3}}{\text{(a)}} \frac{\text{A}}{\text{(b)}} \frac{\text{A}}{\text{(c)}} \frac{\text{012}}{\text{(d)}} \frac{\text{V}}{\text{(e)}} - \frac{\text{HA}}{\text{(f)}}$

(a)	Relay type	FTR-F3: FTR-F3 Series		
(b)	Contact configuration	A : 1 form A, straight terminals C : 1 form C, straight terminals P : 1 form A, right angle terminals		
(c)	Coil type (power)	A : 200mW, 3A and 5A types, FTR-F3 (A;P) A () E (-HA); (-KS) : 280mW, TV3 and TV5 types, FTR-F3 (A;P) A () (V;T) : 360mW, 1 form C type, FTR-F3 CA () E		
(d)	Coil rated voltage	012 : 524VDC Coil rating table at page 3		
(e)	Contact material	V : AgSnO ₂ TV5 type, 1 form A type only (280mW coil) T : AgSnO ₂ TV3 type, 1 form A type only (280mW coil) E : AgNi 3A and 5A types only (not for TV3 and TV5 types)		
(f)	Contact rating	Nil : 3A type HA : 5A type (for type FTR-F3AA only) KS : Sealing confirmed (3A type FTR-F3AA () E only)		

Actual marking does not carry the type name: "FTR"

E.g.: Ordering code: FTR-F3AA012V Actual marking: F3AA012V

3A 250V~ 3A 30VDC marked on relay

Ordering code: FTR-F3AA012V-HA Actual marking: F3AA012V

5A 250V~ 5Ă 30VDC marked on relay

■ SPECIFICATION

Item			FTR-F3					
			3A type	5A type		TV3 / TV5 type		
Contact Data	Configuration		1 form A	1 form A	1 form C	1 form A		
	Construction		Single					
	Material		Silver nickel (AgNi) Ag alloy (AgSnO ₂)					
	Resistance (initial)		Max. 100mOhm at 1A, 6VDC					
	, ,		5A, 250VAC, 30VDC					
	Contact rating (resistive)		3A, 125VAC, 30VDC	5A, 250VAC, 30VDC		TV3: (120VAC) 3A / 51A / 125VAC 3A / 50A / 250VAC		
						TV5: (120VAC) 5A / 78A / 125VAC 5A / 80A / 250VAC		
	Max. carrying current		5A					
	Max. switching voltage		277VAC, 30VDC	277VAC, 30VDC	277VAC, 150VDC	277VAC, 150VDC		
	Max. switching power		750VA, 90W	1,250VA, 150W				
	Min. switching load *		10 mA, 5VDC					
Life	Mechanical		Min. 5 x 10 ⁶ operations	Min. 5 x 10 ⁶ operations	Min. 5 x 10 ⁶ operations	Min. 5 x 10 ⁶ operations		
	Electrical (at rated load)		Min. 200 x 10 ³ operations	Min. 100 x 10 ³ operations Min. 100 x 10 ³ operations Min. 100 x 10 ³ operation (3A, 250VAC/30VDC) Min. 50 x 10 ³ operation (5A, 250VAC/30VDC)				
Coil Data	Rated power (20 °C)		200mW	200mW	360mW	280mW		
	Operate power		113mW	113mW	200mW	156mW		
	Operating temperature rang	ge	-40 °C to +70 °C (no frost)	-40 °C to +70 °C (no frost)	-40 °C to +85 °C (no frost)	-40 °C to +85 °C (no frost)		
Timing Data	Operate (at nominal voltage	e)	Max. 10ms (without bounce,	Max. 10ms (without bounce, no diode)				
	Release (at nominal voltage	e)	Max. 10ms (without bounce,	Max. 10ms (without bounce, no diode)				
nsulation	Resistance (initial)		Min. 1,000MOhm at 500VDC					
	Dielectric strength	Open contacts	750VAC (50/60Hz) 1min					
	Dielectric strength	Contacts to coil	4,000VAC (50/60Hz) 1min					
	Surge strength Contacts to coil		10,000V / 1.2 x 50μs standard wave					
	Clearance		6mm	6mm	7mm	7mm		
	Creepage		6mm	6mm	7mm	7mm		
	EN61810-1, VDE0435	Voltage	250V					
		Pollution degree	2					
		Material group	III					
		Category	C / 250V					
Other	Vibration resistance Misoperation		10 to 55Hz double amplitude 1.5mm					
	VIDIATION ICSISTANCE	Endurance	10 to 55Hz double amplitude 1.5mm					
	Shock		Min. 100m/s ² (11±1ms)					
	SHOCK	Endurance	Min. 1,000m/s ² (6±1ms)					
	Weight	'	Approximately 4g	Approx. 4g	Approx. 6g	Approximately 6g		
	Sealing		Plastic sealed RTIII	•	•			

^{*} Minimum switching loads mentioned above are reference values. Please perform the confirmation test with actual load before production since reference values may vary according to switching frequencies, environmental contions and expected reliability levels.

■ COIL RATING

200mW type

Coil Code	Rated Coil Voltage (VDC)	Coil Resistance +/- 10% (Ohm)	Must Operate Voltage (VDC) *	Must Release- Voltage (VDC) *	Max. Coil Voltage (VDC)	Rated Power (mW)
005	5	125	3.75	0.5	12	
006	6	180	4.5	0.6	14.4	
009	9	405	6.75	0.9	21.6	200
012	12	720	9	1.2	28.8	200
018	18	1,620	13.5	1.8	43.2	
024	24	2,880	18	2.4	57.6	

280mW type

Coil Code	Rated Coil Voltage (VDC)	Coil Resistance +/- 10% (Ohm)	Must Operate Voltage (VDC) *	Must Release- Voltage (VDC) *	Max. Coil Voltage (VDC)	Rated Power (mW)
005	5	90	3.75	0.5	10	
006	6	130	4.5	0.6	12	
009	9	290	6.75	0.9	19	200
012	12	515	9	1.2	26	280
018	18	1,160	13.5	1.8	39	
024	24	2,060	18	2.4	52	

360mW type


Coil Code	Rated Coil Voltage (VDC)	Coil Resistance +/- 10% (Ohm)	Must Operate Voltage (VDC) *	Must Release- Voltage (VDC) *	Max. Coil Voltage (VDC)	Rated Power (mW)
005	5	69	3.75	0.5	9	
006	6	100	4.5	0.6	11	
009	9	225	6.75	0.9	16	260
012	12	400	9	1.2	21	360
018	18	900	13.5	1.8	32	
024	24	1,600	18	2.4	42	


Note: All values in the tables are valid for 20°C and zero contact current. * Specified operate values are valid for pulse wave voltage.


■ SAFETY STANDARDS


Туре	Compliance	Contact rating
UL	UL 508	Flammability: UL 94-V0 (plastics)
	E63614	3A, 30 VDC/ 277 VAC (resistive) 1/10 HP, 250VAC /125VAC
CSA	C22.2 No. 14 LR 40304	1/8 HP, 277VAC Pilot duty: D300
VDE	0435 40015024	5A, 250 VAC, $\cos \varphi$ 1 = 100 x 10 ³ , 85°C, FTR-F3 AA -E 3A, 250 VAC, $\cos \varphi$ 1 = 200 x 10 ³ , 85°C, FTR-F3 AA -E 5A, 30 VDC, 0 msec = 100 x 10 ³ , 85°C, FTR-F3 AA -E 3A, 30 VDC, 0 msec = 200 x 10 ³ , 85°C, FTR-F3 AA -E 5A, 250 VAC, $\cos \varphi$ 1 = 50 x 10 ³ , 70°C, FTR-F3 CA (CO) 5A, 30 VDC, 0msec = 100 x 10 ³ , 70°C, FTR-F3 CA (CO) 3A, 30 VDC, 0msec = 200 x 10 ³ , 70°C, FTR-F3 CA (CO) 5A, 250 VAC, $\cos \varphi$ 1 = 50 x 10 ³ , 85°C, FTR-F3 (A;P) A - (V;T) 3A, 250 VAC, $\cos \varphi$ 1 = 100 x 10 ³ , 85°C, FTR-F3 (A;P) A - (V;T) 3/51A, 250 VAC = 10 x 10 ³ , 85°C, FTR-F3 (A;P) A - T 5/80A, 250 VAC = 10 x 10 ³ , 85°C, FTR-F3 (A;P) A - V
SEMKO	EN 61058-1: 1992 +A1:1993 EN 61095:1993+A11	5A, 250 VAC 40T70


■ REFERENCE DATA






















DIMENSIONS

Standard type


Dimensions



Schematics (BOTTOM VIEW)



PC board mounting hole layout (BOTTOM VIEW)




PC board mounting

hole layout (BOTTOM VIEW)


Unit: mm

Change-over-contact type

Dimensions




Schematics (BOTTOM VIEW)




Unit: mm

Right angle type


Dimensions



Schematics (BOTTOM VIEW)



PC board mounting hole layout (BOTTOM VIEW)



RoHS Compliance and Lead Free Information

1. General Information

- All signal and power relays produced by Fujitsu Components are compliant with RoHS directive 2002/95EC including amendments.
- Cadmium as used in electrical contacts is exempted from the RoHS directives on October 21st, 2005.
 (Amendment to Directive 2002/95/EC)
- All of our signal and power relays are lead-free. Please refer to Lead-Free Status Info for older date codes at: http://www.fujitsu.com/us/downloads/MICRO/fcai/relays/lead-free-letter.pdf
- Lead free solder plating on relay terminals is Sn-3.0Ag-0.5Cu, unless otherwise specified. This material has been verified to be compatible with PbSn assembly process.

2. Recommended Lead Free Solder Profile

• Recommended solder Sn-3.0Ag-0.5Cu.

Flow Solder condition:

Pre-heating: maximum 120°C dip within 5 sec. at 260°C solder bath

Solder by Soldering Iron:

Soldering Iron

Temperature: maximum 360°C Duration: maximum 3 sec.

We highly recommend that you confirm your actual solder conditions

3. Moisture Sensitivity

• Moisture Sensitivity Level standard is not applicable to electromechanical relays, unless otherwise indicated.

4. Tin Whiskers

• Dipped SnAgCu solder is known as presenting a low risk to tin whisker development. No considerable length whisker was found by our in house test.

Fujitsu Components International Headquarter Offices

Japan

Fujitsu Component Limited Gotanda-Chuo Building 3-5, Higashigotanda 2-chome, Shinagawa-ku Tokyo 141, Japan Tel: (81-3) 5449-7010

Fax: (81-3) 5449-7010

Email: promothq@ft.ed.fujitsu.com

Web: www.fcl.fujitsu.com

North and South America

Fujitsu Components America, Inc. 250 E. Caribbean Drive Sunnyvale, CA 94089 U.S.A.

Tel: (1-408) 745-4900 Fax: (1-408) 745-4970

Email: components@us.fujitsu.com Web: http://us.fujitsu.com/components Europe

Fujitsu Components Europe B.V.

Diamantlaan 25 2132 WV Hoofddorp Netherlands

Tel: (31-23) 5560910 Fax: (31-23) 5560950 Email: info@fceu.fujitsu.com

Asia Pacific

Fujitsu Components Asia Ltd. 102E Pasir Panjang Road #01-01 Citilink Warehouse Complex

Web: emea.fujitsu.com/components/

Singapore 118529 Tel: (65) 6375-8560 Fax: (65) 6273-3021 Email: fcal@fcal.fujitsu.com

Web: http://www.fujitsu.com/sg/services/micro/components/

©2010 Fujitsu Components Europe B.V. All rights reserved. All trademarks or registered trademarks are the property of their respective owners.

The contents, data and information in this datasheet are provided by Fujitsu Component Ltd. as a service only to its user and only for general information purposes.

The use of the contents, data and information provided in this datasheet is at the users' own risk.

Fujitsu has assembled this datasheet with care and will endeavor to keep the contents, data and information correct, accurate, comprehensive, complete and up to date.

Fujitsu Components Europe B.V. and affiliated companies do however not accept any responsibility or liability on their behalf, nor on behalf of its employees, for any loss or damage, direct, indirect or consequential, with respect to this datasheet, its contents, data, and information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Nor do Fujitsu Components Europe B.V. and affiliated companies accept on their behalf, nor on behalf of its employees, any responsibility or liability for any representation or warrant of any kind, express or implied, including warranties of any kind for merchantability or fitness for particular use, with respect to these datasheets, its contents, data, information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Rev. August 12, 2010