

SSCP005GSB

High Frequency High Gain PNP Power BJT

Features

VC	E	VBE	VCESAT Typ.	IC
-40	V	-6V	-150mV	-3A


Description

This device is produced with advanced high carrier density technology, which is especially used to minimize saturation voltage drop. This device particularly suits low voltage applications such as portable equipment, power management and other battery powered circuits, and low in-line power dissipation are needed in a very small outline surface mount package. Excellent thermal and electrical capabilities.

> Applications

- Battery powered circuits
- Low in-line power dissipation circuits
- Power regulator


Pin configuration



SOT23-6L



Bottom view



Marking

> Ordering Information

Device	Package	Shipping	
SSCP005GSB	SOT23-6L	3000/Reel	



> Absolute Maximum Ratings(T_A=25°C unless otherwise specified)

Symbol	Parameter	Ratings	Unit	
V _{CBO}	Collector-Base Voltage	-40	V	
V _{CEO}	Collector-Emitter Voltage	-40	V	
V _{EBO}	Emitter-Base Voltage	-6	V	
	Collector Current@Note1	-3	٨	
Ι _C	Collector Current@Note2	-2	A	
I _{CM}	Pulsed Collector Current@Note3	-6	А	
Р	Power Dissipation@Note1	1.2	10/	
PD	Power Dissipation@Note1 Power Dissipation@Note2		W	
T _A	Operation Temperature Range	-40 to 85	°C	
TL	Lead Temperature	260	°C	
TJ,TSTG	Operation and Storage temperature range	-55 to 150	°C	

> Thermal Resistance Ratings

Symbol	Parameter	Maximum	Unit
P	Junction-to-Ambient Thermal	100	
R _{θJA}	Resistance@Note1	109	°C/W
	Junction-to-Ambient Thermal		
R _{eja}	Resistance@Note2	160	



➢ Electronics Characteristics(T_A=25℃ unless otherwise specified)


Symbol	Parameter	Test Conditions	Min	Тур.	Max	Unit
BVCBO	Collector-Base	IC=-50uA	-40			V
вусво	Breakdown Voltage IE=0	-40			v	
BVCEO	Collector-Emitter	IC=-1mA	-40			V
BVCEO	Breakdown Voltage	IB=0	-40			
BVEBO	Emitter-Base	IE=-1uA	-6		V	V
BVEBU	Breakdown Voltage	IC=0	-0			v
ІСВО	Collector cut off	VCB=-20V			0.4	
ЮВО	current	IE=0			-0.1	uA
IEBO	Emitter cut off	VEB=-4V			0.1	
IEBO	current	IC=0			-0.1	uA
HFE	DC Current	VCE=-2V	100 20	200	350	
	Gain@Note3	IC=-0.5A	100	200	350	
VCESAT	Collector-Emitter	IC=-1.5A			-0.2	V
VCESAI	Saturation Voltage	IB=-80mA			-0.2	V
VBESAT	Base-Emitter	IC=-1.5A			-1.2	V
	Saturation Voltage	IB=-80mA				
f _T	Tropoition froquency	VCE=-5V , IE=-0.1A	50	80		MHz
	Transition frequency	f=10MHz				IVI⊓∠

Notes:

- 1. Surface mounted on FR-4 Board using 1 square inch pad size, 1oz copper.
- 2. Surface mounted on FR-4 Board using minimum pad size, 1oz copper.
- 3. Pulse width=300us, Duty Cycle<2%.



> Typical Performance Characteristics






SSCP005GSB

Package Information

SIDE VIEW



	MILLIMETER				
SYMBOL	MIN	NOM	MAX		
Α	1.06	1.15	1.24		
* A1	0.01	0.05	0.09		
* A2	1.05	1.10	1.15		
A3	0.65	0.70	0.75		
* b	0.30	0.35	0.45		
* с	0.117	0.127	0.157		
* D	2.87	2.92	2.97		
* E	2.72	2.80	2.88		
* E1	1.55	1.60	1.65		
* e	0.90	0.95	1.00		
* L	0.32	0.40	0.48		
* L1	0.55	0.60	0.65		
R	0.10 REF				
R1	0.12 REF				
* 0	0		8°		
θ1	8°	10°	12°		
62	10°	12°	14°		

DISCLAIMER

AFSEMI RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. AFSEMI DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICIENCE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

THE GRAPHS PROVIDED IN THIS DOCUMENT ARE STATISTICAL SUMMARIES BASED ON A LIMITED NUMBER OF SAMPLES AND ARE PROVIDED FOR INFORMATIONAL PURPOSE ONLY. THE PERFORMANCE CHARACTERISTICS LISTED IN THEM ARE NOT TESTED OR GUARANTEED. IN SOME GRAPHS, THE DATA PRESENTED MAY BE OUTSIDE THE SPECIFIED OPERATING RANGE (E.G. OUTSIDE SPECIFIED POWER SUPPLY RANGE) AND THEREFORE OUTSIDE THE WARRANTED RANGE.