

POWER RELAY 1 POLE - 5A Slim Type

NY Series

■ FEATURES

- Slim type with 5 mm thickness
- Suited for high density mounting
- Low power consumption and high sensitivity
 - Nominal coil power: 120 mW
 - Operating power: 54 mW
- UL and CSA recognized
- Conforms to IEC61010, 61131
- High insulation
- Surge voltage: 5,080V
- Dielectric strength: 3,000VAC (coil and contacts)
- SIL pitch terminals
- Plastic sealed type, RTIII
- Compatible with solid state I/O module type SN in size and pin (terminal) arrangement
- Environmentally friendly cadmium free contact type
- RoHS compliant.

Please see page 6 for more information



■ PARTNUMBER INFORMATION

[Example] $\frac{NY}{(a)} \frac{P}{(b)} \frac{-12}{(c)} \frac{W}{(d)} \frac{-K}{(e)} \frac{-IE}{(f)}$

(a)	Relay type	NY	: NY-Series
(b)	Mounting type	Nil P	: PCB board mounting type : Socket mounting type
(c)	Coil rated voltage	12	: 4.524 VDC Coil rating table at page 3
(d)	Contact design	W	: Bifurcated contact
(e)	Enclosure	К	: Plastic sealed type, RTIII
(f)	Insulation	IE	: Complies with IEC standard, IEC61010, 61131

Note: Actual marking omits the hyphen (-) and IE of (*)

1

NY SERIES

■ SPECIFICATION

Item			NY		
Contact Data	Configuration		1 form A (SPST-NO)		
	Construction		Bifurcated		
	Material		Gold overlay silver alloy (AgNi + Au)		
	Resistance (initial)		Max. 30 mΩ at 6 VDC, 1 A		
	Contact rating		5A, 250VAC / 30VDC		
	Max. carrying current		5A		
	Max. switching voltage		270VAC / 150 VDC		
	Max. switching power		750VA / 90W		
	Max. switching current		5A		
	Min. switching load *		1 mA, 5 VDC		
Life	Mechanical		Min. 20 x 10 ⁶ operations		
	Electrical		Min. 100 x 10 ³ operations (at 3A, 250VAC, 30VDC resistive) Min. 50 x 10 ³ operations (at 5A, 250VAC, 30VDC resistive)		
Coil Data	Rated power (at 20 °C)		120 mW		
	Operate power (at 20 °C)		54 mW		
	Operating temperature ra	ange	-40 °C to +90 °C (no frost)		
Timing Data	Operate (at nominal volt	age)	Max. 10 ms (without bounce)		
	Release (at nominal volt	age)	Max. 5 ms (no diode)		
Insulation	Resistance (initial)		Min. 1,000MΩ at 500VDC		
	Dielectric strength	Open contacts	750VAC, 1min		
		Contacts to coil	3,000VAC, 1min		
	Surge strength	Coil to contacts	5,080V / 1.2 x 50µs standard wave		
Other	Vibration resistance	Misoperation	10 to 55Hz double amplitude 1.5 mm		
		Endurance	10 to 55Hz double amplitude 5 mm		
	Charle	Misoperation	Min. 100m/s ² (11 ± 1ms)		
	Shock	Endurance	Min. 1,000m/s² (6 ± 1ms)		
	Weight		Approximately 3.5 g		
	Sealing		Plastic sealed, RTIII		

^{*} Minimum switching loads mentioned above are reference values. Please perform the confirmation test with actual load before production since reference values may vary according to switching frequencies, environmental conditions and expected reliability levels.

■ COIL RATING

Coil Code	Rated Coil Voltage (VDC)	Coil Resistance +/- 10% (Ohm)	Must Operate Voltage (VDC) *	Must Release- Voltage (VDC) *	Rated Power (mW)
4.5	4.5	169	3	0.45	
5	5	208	3.35	0.5	
6	6	300	4	0.6	
9	9	675	6	0.9	120
12	12	1,200	8	1.2	
18	18	2,700	12.1	1.8	
24	24	4,800	16.1	2.4	

Note: All values in the table are valid for 20°C and zero contact current. * Specified operate values are valid for pulse wave voltage.


SAFETY STANDARDS

Туре	Compliance	Contact rating
UL	UL 508, UL 1604	Flammability: UL 94-V0 (plastics)
	E56140, E199193	3A (General use) 5A, 250VAC/30 VDC (resistive)
CSA	C22.2 No. 14 LR 35579	1/8 HP, 250VAC /125VAC Pilot duty: C300

Also complies with IEC 61010, 61131

NY SERIES

CHARACTERISTIC DATA




NY SERIES


DIMENSIONS

NY type


Dimensions



Schematics




 PC board mounting hole layout (BOTTOM VIEW)




NYP type


Dimensions



Schematics




 PC board mounting hole layout (BOTTOM VIEW)




Socket type JL-5N

Dimensions



 PC board mounting hole layout (BOTTOM VIEW)



RoHS Compliance and Lead Free Information

1. General Information

- All relays produced by Fujitsu Components are compliant with RoHS directive 2011/65/EU including amendments.
- Cadmium as used in electrical contacts is exempted from the RoHS directives.
 As per Annex III of directive 2011/65/EU.
- All relays are lead-free. Please refer to Lead-Free Status Info for older date codes at: http://www.fujitsu.com/downloads/MICRO/fcai/relays/lead-free-letter.pdf
- Lead free solder plating on relay terminals is Sn-3.0Ag-0.5Cu, unless otherwise specified.
 This material has been verified to be compatible with PbSn assembly process.

2. Recommended Lead Free Solder Condition

• Recommended solder Sn-3.0Ag-0.5Cu.

Flow Solder Condition:

Pre-heating: maximum 120°C

within 9 sec.

Soldering: dip within 5 sec. at

255°C ± 5°C solder bath

Relay must be cooled by air immediately

after soldering

Solder by Soldering Iron:

Soldering Iron 30-60W

Temperature: maximum 350-360°C Duration: maximum 3 sec.

We highly recommend that you confirm your actual solder conditions

3. Moisture Sensitivity

Moisture Sensitivity Level standard is not applicable to electromechanical relays, unless otherwise indicated.

4. Tin Whiskers

• Dipped SnAgCu solder is known as presenting a low risk to tin whisker development. No considerable length whisker was found by our in house test.

6

Fujitsu Components International Headquarter Offices

Japan

Fujitsu Component Limited Gotanda-Chuo Building 3-5, Higashigotanda 2-chome, Shinagawa-ku Tokyo 141, Japan Tel: (81-3) 5449-7010

Fax: (81-3) 5449-2626

Email: promothq@ft.ed.fujitsu.com

Web: www.fcl.fujitsu.com

North and South America

Fujitsu Components America, Inc. 250 E. Caribbean Drive Sunnyvale, CA 94089 U.S.A. Tel: (1-408) 745-4900 Fax: (1-408) 745-4970

Email: components@us.fujitsu.com

Web: http://us.fujitsu.com/components

Europe

Fujitsu Components Europe B.V.

Diamantlaan 25 2132 WV Hoofddorp Netherlands Tel: (31-23) 5560910

Fax: (31-23) 5560950 Email: info@fceu.fujitsu.com Web: emea.fujitsu.com/components/

Asia Pacific

Fujitsu Components Asia Ltd. 102E Pasir Panjang Road

#01-01 Citilink Warehouse Complex

Singapore 118529 Tel: (65) 6375-8560 Fax: (65) 6273-3021 Email: fcal@fcal.fujitsu.com

Web: http://www.fujitsu.com/sg/services/micro/components/

©2014 Fujitsu Components Europe B.V. All rights reserved. All trademarks or registered trademarks are the property of their respective owners.

The contents, data and information in this datasheet are provided by Fujitsu Component Ltd. as a service only to its user and only for general information purposes.

The use of the contents, data and information provided in this datasheet is at the users' own risk.

Fujitsu has assembled this datasheet with care and will endeavor to keep the contents, data and information correct, accurate, comprehensive,

Fujitsu Components Europe B.V. and affiliated companies do however not accept any responsibility or liability on their behalf, nor on behalf of its employees, for any loss or damage, direct, indirect or consequential, with respect to this datasheet, its contents, data, and information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof.

Nor do Fujitsu Components Europe B.V. and affiliated companies accept on their behalf, nor on behalf of its employees, any responsibility or liability for any representation or warrant of any kind, express or implied, including warranties of any kind for merchantability or fitness for particular use, with respect to these datasheets, its contents, data, information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Rev. January 13, 2014