US1A THRU US1M



US1A THRU US1M 1.0Amp Ultra Fast Surface Mount Rectifiers

General description

1.0Amp Ultra Fast Surface Mount Rectifiers

FEATURES

- For surface mounted applications
- Low reverse leakage
- Built-in strain relief
- Easy pick and place
- Ultrafast recovery times for high efficiency.
- Plastic package has Underwriters Laboratory
- Flammability Classification 94V-0
- Glass passivated Junction chip
- High temperature soldering : 260 9 /10 seconds at terminals


MECHANICAL DATA


Case: SMA

• Terminals: Solderable per MIL-STD-750, Method 2026

Weight: 0.002 ounce, 0.064 grams

SMA/DO-214AC





Unit: inch (mm)

Absolute Maximum Ratings(Ta=25°C unless otherwise specified)

Parameter	Symbols	US1A	US1B	US1D	US1G	US1J	US1K	US1M	Units
Marking Code	Mark	US1A	US1B	US1D	US1G	US1J	US1K	US1M	N/A
Maximum Repetitive Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current	I _{F(AV)}	1							Α
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load	Ifsм	30							А
Maximum Instantaneous Forward Voltage at 1 A	V_{F}	1.0 1.3				1.7			V
Maximum DC Reverse Current $T_a = 25 ^{\circ}\text{C}$ at Rated DC Blocking Voltage $T_a = 100 ^{\circ}\text{C}$	I _R	5 500							μА
Maximum Reverse Recovery Time(Note 1) TJ=25°C	Trr	50 75						nS	
Typical Junction Capacitance (Note 2)	Cj	17							pF
Maximum Thermal Resistance(Note 3) RθJA	Reja	30							°C/W
Operating and Storage Temperature Range	Tj, Tstg	-55 ~ + 150							°C

NOTES: 1. Reverse Recovery Test Conditions: IF=0.5A, IR=1.0A, Irr=0.25A

2. Measured at 1 MHz and applied Vr = 4.0 volts.

US1A THRU US1M



Ratings And Characteristic Curves




Fig.1 FORWARD CURRENT DERATING CURVE




Fig.2 PEAK FORWARD SURGE CURRENT




Fig.3 FORWARD CHARACTERISTICS




Fig.4 TYPICAL REVERSE CHARACTERISTICS




Fig.5 TYPICAL JUNCTION CAPACITANCE

www.doeshare.net

US1A THRU US1M



Important Notice and Disclaimer

DOESHARE has used reasonable care in preparing the information included in this document, but DOESHARE does not warrant that such information is error free. DOESHARE assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.

DOESHARE no warranty, representation or guarantee regarding the documents, circuits and products specification, DOESHARE reservation rights to make changes for any documents, products, circuits and specifications at any time without notice.

Purchasers are solely responsible for the choice, selection and use of the DOESHARE products and services described herein, and DOESHARE assumes no liability whatsoever relating to the choice, selection or use of the products and services described herein.

No license, express or implied, by implication or otherwise under any intellectual property rights of DOESHARE.

Resale of DOESHARE products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by DOESHARE for the DOESHARE product or service described herein and shall not create or extend in any manner whatsoever, any liability of DOESHARE.