

# **DATASHEET**

# 5mm Infrared LED HIR333-A



#### **Features**

- · High reliability
- High radiant intensity
- Peak wavelength λp=850nm
- 2.54mm Lead spacing
- Low forward voltage
- Pb Free
- This product itself will remain within RoHS compliant version.
- Compliance with EU REACH
- Compliance Halogen Free(Br < 900ppm, Cl < 900ppm, Br+Cl < 1500ppm)

## **Description**

- EVERLIGHT's Infrared Emitting Diode (HIR333-A) is a high intensity diode, molded in a yellow plastic package.
- The device is spectrally matched with phototransistor, photodiode and infrared receiver module.

## **Applications**

- Free air transmission system
- Infrared remote control units with high power requirement
- Smoke detector
- Infrared applied system



## **Device Selection Guide**

Chip Materials	Lens Color
GaAlAs	Yellow

# Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit
Continuous Forward Current	I <sub>F</sub>	100	mA
Peak Forward Current(*1)	I <sub>FP</sub>	1.0	A
Reverse Voltage	$V_R$	5	V
Operating Temperature	T <sub>opr</sub>	-40 ~ +85	$^{\circ}$ C
Storage Temperature	$T_{stg}$	-40 ~ +85	$^{\circ}$ C
Soldering Temperature(*2)	T <sub>sol</sub>	260	$^{\circ}$ C
Power Dissipation at (or below)	$P_d$	150	mW
25°C Free Air Temperature	ı u		

Notes: \*1:I<sub>FP</sub> Conditions--Pulse Width  $\leq$  100 $\mu$ s and Duty  $\leq$  1%. \*2:Soldering time  $\leq$  5 seconds.



# Electro-Optical Characteristics (Ta=25℃)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
		7.8	15	67		IF=20mA
Radiant Intensity	l <sub>e</sub>		80		mW/sr	I <sub>F</sub> =100mA Pulse Width≦100μs and Duty≦1%
			800			I <sub>F</sub> =1A Pulse Width≦100μs and Duty≦1%
Peak Wavelength	λр		850		nm	I <sub>F</sub> =20mA
Spectral Bandwidth	Δλ		45		nm	I <sub>F</sub> =20mA
Forward Voltage	VF		1.45	1.65	<b>V</b>	I <sub>F</sub> =20mA
			1.80	2.40		I <sub>F</sub> =100mA Pulse Width≦100µs and Duty≦1%
			4.10	5.25		I <sub>F</sub> =1A Pulse Width≦100μs and Duty≦1%
Reverse Current	I <sub>R</sub>			10	uA	V <sub>R</sub> =5V
View Angle	201/2		17		deg	I <sub>F</sub> =20mA

## Rank

Condition:I<sub>F</sub>=20mA Unit: mW/sr

Bin Number	М	N	Р	Q	R	S
Min	7.8	11.0	15.0	21.0	30.0	42.0
Max	12.5	17.6	24.0	34.0	48.0	67.0

#### Note:


<sup>\*</sup>Measurement Uncertainty of Forward Voltage: ±0.1V


<sup>\*</sup>Measurement Uncertainty of Luminous Intensity: ±10%


<sup>\*</sup>Measurement Uncertainty of Dominant Wavelength ±1.0nm




## **Typical Electro-Optical Characteristics Curves**










Relative Radiant Intensity vs. Angular Displacement




# **Package Dimension**



Note: Tolerances unless dimensions ±0.25mm





## **Label Form Specification**



- · CPN: Customer's Product Number
- P/N: Product Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- · HUE: Dom. Wavelength Rank
- REF: Forward Voltage Rank
- · LOT No: Lot Number
- · X: Month
- · Reference: Identify Label Number

## **Packing Specification**





- Packing Quantity
- 1.200~ 500 PCS/1 Bag, 5 Bags/1 Inner Carton
- 2. 10 Inner Cartons/1 Outside Carton

## **Notes**

- Lead Forming
  - During lead formation, the leads should be bent at a point at least 3mm from the base of the epoxy bulb.
  - Lead forming should be done before soldering.
  - Avoid stressing the LED package during leads forming. The stress to the base may damage the LED's characteristics or it may break the LEDs.
  - Cut the LED lead frames at room temperature. Cutting the lead frames at high temperatures may cause failure of the LEDs.
  - When mounting the LEDs onto a PCB, the PCB holes must be aligned exactly with the lead position of the LED. If the LEDs are mounted with stress at the leads, it causes deterioration of the epoxy resin and this will degrade the LEDs.



#### 2. Storage


- The LEDs should be stored at 30°C or less and 70%RH or less after being shipped from Everlight and the storage life limits are 3 months. If the LEDs are stored for 3 months or more, they can be stored for a year in a sealed container with a nitrogen atmosphere and moisture absorbent material.
- Please avoid rapid transitions in ambient temperature, especially, in high humidity environments where condensation can occur.

### 3. Soldering

- Careful attention should be paid during soldering. When soldering, leave more then 3mm from solder joint to epoxy bulb, and soldering beyond the base of the tie bar is recommended.
- Recommended soldering conditions:

Hand Soldering		DIP Soldering		
Temp. at tip of iron	300°C Max. (30W Max.)	Preheat temp.	100°C Max. (60 sec Max.)	
Soldering time	3 sec Max.	Bath temp. & time	260 Max., 5 sec Max	
Distance	3mm Min.(From solder	Distance	3mm Min. (From solder	
	joint to epoxy bulb)		joint to epoxy bulb)	

Recommended soldering profile



- Avoiding applying any stress to the lead frame while the LEDs are at high temperature particularly when soldering.
- Dip and hand soldering should not be done more than one time
- After soldering the LEDs, the epoxy bulb should be protected from mechanical shock or vibration until the LEDs return to room temperature.
- A rapid-rate process is not recommended for cooling the LEDs down from the peak temperature.
  Although the recommended soldering conditions are specified in the above table, dip or hand soldering at the lowest possible temperature is desirable for the LEDs.
- Wave soldering parameter must be set and maintain according to recommended temperature and dwell time in the solder wave.



#### Cleaning

- When necessary, cleaning should occur only with isopropyl alcohol at room temperature for a duration of no more than one minute. Dry at room temperature before use.
- Do not clean the LEDs by the ultrasonic. When it is absolutely necessary, the influence of ultrasonic cleaning on the LEDs depends on factors such as ultrasonic power and the assembled condition. Ultrasonic cleaning shall be pre-qualified to ensure this will not cause damage to the LED

#### 5. Heat Management

- Heat management of LEDs must be taken into consideration during the design stage of LED application. The current should be de-rated appropriately by referring to the de-rating curve found in each product specification.
- The temperature surrounding the LED in the application should be controlled. Please refer to the data sheet de-rating curve.

#### 6. ESD (Electrostatic Discharge)

- Electrostatic discharge (ESD) or surge current (EOS) can damage LEDs.
- An ESD wrist strap, ESD shoe strap or antistatic gloves must be worn whenever handling LEDs.
- All devices, equipment and machinery must be properly grounded.
- Use ion blower to neutralize the static charge which might have built up on surface of the LEDs plastic lens as a result of friction between LEDs during storage and handing.

## **DISCLAIMER**

- 1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
- 2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
- 3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
- 6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.