

## Bi-directional Ultra Low Capacitance TVS Array

#### **DESCRIPTION**

The BV05C are ultra low capacitance transient voltage suppressor arrays, designed to protect applications such as portable electronics and SMART phones. This series is available in both unidirectional and bidirectional configurations and is rated at 350 Watts for an 8/20µs wave shape.

The BV05C meets IEC 61000-4-2 (ESD) and IEC 61000-4-4 (EFT) requirements. At higher operating frequencies or faster edge rates, insertion loss and signal integrity are a major concern. This series offers a ultra low capacitance and low leakage current in a miniature SOD-323 package.

#### **FEATURES**

♦ Transient protection for high-speed data lines IEC 61000-4-2 (ESD) ±8kV (Contact) ±15kV (Air)

IEC 61000-4-4 (EFT) 40A (5/50 ns)

- ♦Protects one I/O line (bidirectional)
- ♦Low clamping voltage
- ♦Low leakage current
- ♦ Response time is < 1 ns

### **MACHANICAL DATA**

- ♦SOD-323 package
- ♦Flammability Rating: UL 94V-0
- ♦ Packaging: Tape and Reel
- ♦High temperature soldering guaranteed: 260°C/10s
- ♦Reel size: 7 inch
- ♦MSL1

# **ORDERING INFORMATION**


→ Package: SOD-323→ Material: Halogen free→ Packing: Tape & Reel

♦ Quantity per reel: 3,000pcs

#### **APPLICATIONS**

- ♦ Cell Phone Handsets and Accessories
- ♦ Microprocessor based equipment
- ♦ Personal Digital Assistants (PDA's)
- ♦Notebooks, Desktops, and Servers
- ♦Portable Instrumentation
- ♦ Peripherals
- ♦USB Interface

#### PIN CONFIGURATION



#### PACKAGE OUTLINE








# BV05C Bi-directional Ultra Low Capacitance TVS Array


ABSOLUTE M	UTE MAXIMUM RATING						
Symbol	Parameter	Value	Units				
V <sub>ESD</sub>	ESD per IEC 61000-4-2 (Air)	±15	kV				
- 235	ESD per IEC 61000-4-2 (Contact)	±8					
P <sub>PP</sub>	Peak Pulse Power (8/20μs)	350	W				
T <sub>OPT</sub>	Operating Temperature	-55/+150	°C				
T <sub>STG</sub>	Storage Temperature	-55/+150	°C				
TL	Lead Soldering Temperature	260	°C				

ELECTRICAL CHARA	ECTRICAL CHARACTERISTICS (Tamb=25°C)								
	$V_{RWM}$	V <sub>B</sub> @1mA	V <sub>C</sub> @1A	V <sub>c</sub> @	Jpp	V <sub>C</sub> @	plpp	I <sub>R</sub>	$C_T$
PART	(V)	(V)	(V)	(\	/)	(\	/)	(µA)	(pF)
NUMBER	Max	Min	Max	Max	lpp (A)	Max	Ipp (A)	Max	Тур.
BV05C	5.0	6.0	9.8	18.3	8	20.0	18	1	0.8




# **ELECTRICAL CHARACTERISTICS CURVE**






#### **Pulse Waveform**








**Power Derating Curve** 


Junction Capacitance vs. Reverse Voltage







# **SOD-323 PACKAGE OUTLINE DIMENSIONS**







Cumbal	Dimensions In Millimeters			
Symbol	Min	Max		
А		1.00		
A1	0.000	0.100		
A2	0.800	0.900		
b	0.250	0.350		
С	0.080	0.150		
D	1.200	1.400		
Е	1.600	1.800		
E1	2.500 2			
е	1.800	2.040		
L	0.475 REF			
L1	0.250	0.400		
θ	0°	8°		



**Recommended Pad outline**