

Features

- Single-Supply Operation from +1.8V ~ +5.5V
- Rail-to-Rail Input / Output
- Gain-Bandwidth Product: 4.5MHz (Typ@25°C)
- Low Input Bias Current: 20pA (Typ@25°C)
- Low Offset Voltage: 30µV (Max @25°C)
- Quiescent Current: 550µA per Amplifier (Typ)
- Operating Temperature: -45°C ~ +125°C
- Zero Drift: 0.01µV/°C (Typ)

- Embedded RF Anti-EMI Filter
- Small Package:

HGA376 Available in SOT23-5 and SOP-8 Packages
HGA2376 Available in MSOP-8 and SOP-8 Packages
HGA4376 Available in SOP-14 and TSSOP-14 Packages

General Description

The HGAx376 amplifier is single/dual/quad supply, micro-power, zero-drift CMOS operational amplifiers, the amplifiers offer bandwidth of 4.5MHz, rail-to-rail inputs and outputs, and single-supply operation from 1.8V to 5.5V. HGAx376 uses chopper stabilized technique to provide very low offset voltage (less than 30µV maximum) and near zero drift over temperature. Low quiescent supply current of 550µA per amplifier and very low input bias current of 20pA make the devices an ideal choice for low offset, low power consumption and high impedance applications. The HGAx376 offers excellent CMRR without the crossover associated with traditional complementary input stages. This design results in superior performance for driving analog-to-digital converters (ADCs) without degradation of differential linearity.

The HGA376 is available in SOT23-5 and SOP-8 packages. And the HGA2376 is available in MSOP-8 and SOP-8 packages. The HGA4376 Quad is available in Green SOP-14 and TSSOP-14 packages. The extended temperature range of -45°C to +125°C over all supply voltages offers additional design flexibility.

Applications

- Transducer Application
- Temperature Measurements
- Electronics Scales

- Handheld Test Equipment
- Battery-Powered Instrumentation

Pin Configuration




Figure 1. Pin Assignment Diagram



Absolute Maximum Ratings

Condition	Min	Max		
Power Supply Voltage (V _{DD} to Vss)	-0.5V	+7.5V		
Analog Input Voltage (IN+ or IN-)	Vss-0.5V	V _{DD} +0.5V		
PDB Input Voltage	Vss-0.5V	+7V		
Operating Temperature Range	-45°C	+125°C		
Junction Temperature	+16	0°C		
Storage Temperature Range	-55°C	+150°C		
Lead Temperature (soldering, 10sec)	+26	0°C		
Package Thermal Resistance (T _A =+25℃)				
SOP-8, θ _{JA}	125°	C/W		
MSOP-8, θ _{JA}	216°	216°C/W		
SOT23-5, θ _{JA}	190°	190°C/W		
ESD Susceptibility				
НВМ	6KV			
MM	400V			

Note: Stress greater than those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions outside those indicated in the operational sections of this specification are not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.

Ordering Information

DEVICE	Package Type	MARKING	Packing	Packing Qty
HGA376M5/TR	SOT23-5	A376	REEL	3000pcs/reel
HGA376M/TR	SOP8L	HGA376	REEL	2500pcs/reel
HGA2376M/TR	SOP8L	HGA2376	REEL	2500pcs/reel
HGA2376MM/TR	MSOP8L	A2376	REEL	3000pcs/reel
HGA4376M/TR	SOP14L	HGA4376	REEL	2500pcs/reel
HGA4376MT/TR	TSSOP14L	HGA4376	REEL	2500pcs/reel




Electrical Characteristics

(V_S = +5V, V_{CM} = +2.5V, V_O = +2.5V, T_A = +25 $^{\circ}$ C, unless otherwise noted.)

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
INPUT CHARACTERISTICS		•			1
Input Offset Voltage (Vos)			1	30	μV
Input Bias Current (I _B)			20		pA
Input Offset Current (I _{OS})			10		pA
Common-Mode Rejection Ratio (CMRR)	V _{CM} = 0V to 5V		110		dB
Large Signal Voltage Gain (A _{VO})	$R_L = 10k\Omega$, $V_O = 0.3V$ to 4.7V		145		dB
Input Offset Voltage Drift (ΔV _{OS} /Δ _T)			10	50	nV/℃
OUTPUT CHARACTERISTICS		•	•	•	•
Output Valta and High (V.)	$R_L = 100k\Omega$ to - V_S		4.998		V
Output Voltage High (V _{OH})	$R_L = 10k\Omega$ to - V_S		4.994		V
Output Valtage Levy (V)	$R_L = 100k\Omega$ to + V_S		2		mV
Output Voltage Low (V _{OL})	$R_L = 10k\Omega$ to + V_S		5		mV
Short Circuit Limit (I _{SC})	R_L =10 Ω to - V_S		43		mA
Output Current (I _O)			30		mA
POWER SUPPLY		•			
Power Supply Rejection Ratio (PSRR)	V _S = 2.5V to 5.5V		115		dB
Quiescent Current (IQ)	$V_O = 0V$, $R_L = 0\Omega$		550		μA
DYNAMIC PERFORMANCE		•			
Gain-Bandwidth Product (GBP)	G = +100		4.5		MHz
Slew Rate (SR)	$R_L = 10k\Omega$		2.5		V/µs
Overload Recovery Time			0.10		ms
NOISE PERFORMANCE		•	•	•	•
Voltage Noise (e _n p-p)	0Hz to 10Hz		0.2		μV _{P-P}
Voltage Noise Density (e _n)	f = 1kHz		30		nV/\sqrt{Hz}




Typical Performance characteristics





Typical Performance characteristics





Application Note

Size

HGAx376 series op amps are unity-gain stable and suitable for a wide range of general-purpose applications. The small footprints of the HGAx376 series packages save space on printed circuit boards and enable the design of smaller electronic products.

Power Supply Bypassing and Board Layout

HGAx376 series operates from a single 1.8V to 5.5V supply or dual ± 0.9 V to ± 2.75 V supplies. For best performance, a 0.1μ F ceramic capacitor should be placed close to the V_{DD} pin in single supply operation. For dual supply operation, both V_{DD} and V_{SS} supplies should be bypassed to ground with separate 0.1μ F ceramic capacitors.

Low Supply Current

The low supply current (typical 550µA per channel) of HGAx376 series will help to maximize battery life They are ideal for battery powered systems.

Operating Voltage

HGAx376 series operate under wide input supply voltage (1.8V to 5.5V). In addition, all temperature specifications apply from -40 °C to +125 °C. Most behavior remains unchanged throughout the full operating voltage range. These guarantees ensure operation throughout the single Li-Ion battery lifetime.

Rail-to-Rail Input

The input common-mode range of HGAx376 series extends 100mV beyond the supply rails (V_{SS} -0.1V to V_{DD} +0.1V). This is achieved by using complementary input stage. For normal operation, inputs should be limited to this range.

Rail-to-Rail Output

Rail-to-Rail output swing provides maximum possible dynamic range at the output. This is particularly important when operating in low supply voltages. The output voltage of HGAx376 series can typically swing to less than 5mV from supply rail in light resistive loads (>100k Ω), and 60mV of supply rail in moderate resistive loads (10k Ω).

Capacitive Load Tolerance

The HGAx376 family is optimized for bandwidth and speed, not for driving capacitive loads. Output capacitance will create a pole in the amplifier's feedback path, leading to excessive peaking and potential oscillation. If dealing with load capacitance is a requirement of the application, the two strategies to consider are (1) using a small resistor in series with the amplifier's output and the load capacitance and (2) reducing the bandwidth of the amplifier's feedback loop by increasing the overall noise gain. Figure 2. shows a unity gain follower using the series resistor strategy. The resistor isolates the output from the capacitance and, more importantly, creates a zero in the feedback path that compensates for the pole created by the output capacitance.




Figure 2. Indirectly Driving a Capacitive Load Using Isolation Resistor



The bigger the R_{ISO} resistor value, the more stable V_{OUT} will be. However, if there is a resistive load R_L in parallel with the capacitive load, a voltage divider (proportional to R_{ISO}/R_L) is formed, this will result in a gain error.

The circuit in Figure 3 is an improvement to the one in Figure 2. R_F provides the DC accuracy by feed-forward the V_{IN} to R_L . C_F and R_{ISO} serve to counteract the loss of phase margin by feeding the high frequency component of the output signal back to the amplifier's inverting input, thereby preserving the phase margin in the overall feedback loop. Capacitive drive can be increased by increasing the value of C_F . This in turn will slow down the pulse response.




Figure 3. Indirectly Driving a Capacitive Load with DC Accuracy



Typical Application Circuits

Differential amplifier

The differential amplifier allows the subtraction of two input voltages or cancellation of a signal common the two inputs. It is useful as a computational amplifier in making a differential to single-end conversion or in rejecting a common mode signal. Figure 4. shown the differential amplifier using HGAx376.




Figure 4. Differential Amplifier

$$V_{\text{OUT}} = (\frac{R_1 + R_2}{R_2 + R_4}) \frac{R_4}{R_1} V_{\text{IN}} - \frac{R_2}{R_1} V_{\text{IP}} + (\frac{R_1 + R_2}{R_2 + R_4}) \frac{R_2}{R_1} V_{\text{REF}}$$

If the resistor ratios are equal (i.e. R₁=R₃ and R₂=R₄), then

$$V_{\text{OUT}} = \frac{R_2}{R_1} (V_{\text{IP}} - V_{\text{IN}}) + V_{\text{REF}}$$

Low Pass Active Filter

The low pass active filter is shown in Figure 5. The DC gain is defined by $-R_2/R_1$. The filter has a -20dB/decade roll-off after its corner frequency $f_C=1/(2\pi R_3C_1)$.




Figure 5. Low Pass Active Filter



Instrumentation Amplifier

The triple HGAx376 can be used to build a three-op-amp instrumentation amplifier as shown in Figure 6. The amplifier in Figure 6 is a high input impedance differential amplifier with gain of R_2/R_1 . The two differential voltage followers assure the high input impedance of the amplifier.






Figure 6. Instrument Amplifier



PACKAGE










Dimensions In Millimeters						
Symbol:	Min:	Max:	Symbol:	Min:	Max:	
Α	1.225	1.570	D	0.400	0.950	
A1	0.100	0.250	Q	0°	8°	
В	4.800	5.100	а	0.420 TYP		
С	5.800	6.250	b	1.270 TYP		
C1	3.800	4.000				

MSOP8








Dimensions In Millimeters						
Symbol:	Min:	Max:	Symbol:	Min:	Max:	
Α	0.800	1.200	E1	4.700	5.100	
A1	0	0.200	L	0.410	0.650	
A2	0.760	0.970	θ	0°	6°	
D	2.900	3.100	b	0.300 TYP		
E	2.900	3.100	е	0.650 TYP		


10




PACKAGE



TSSOP14




D



Dimensions In Millimeters						
Symbol:	Min:	Max:	Symbol :	Min:	Max:	
Α	0.950	1.200	E1	4.300	4.500	
A1	0.050	0.150	L	0.450	0.750	
A2	0.900	1.050	θ	0°	8°	
В	0.200	0.280	е	0.650 BSC		
С	0.100	0.190	L1	1.000 REF		
D	4.860	5.060	L2	1.250 BSC		
E	6.200	6.600				



PACKAGE





Important statement:

Huaguan Semiconductor Co,Ltd. reserves the right to change the products and services provided without notice. Customers should obtain the latest relevant information before ordering, and verify the timeliness and accuracy of this information.

Customers are responsible for complying with safety standards and taking safety measures when using our products for system design and machine manufacturing to avoid potential risks that may result in personal injury or property damage.

Our products are not licensed for applications in life support, military, aerospace, etc., so we do not bear the consequences of the application of these products in these fields.

Our documentation is only permitted to be copied without any tampering with the content, so we do not accept any responsibility or liability for the altered documents.