

## ESD05V32D-LC

## Bi-directional Ultra Low Capacitance TVS Array

#### DESCRIPTION

The ESD05V32D-LC are ultra low capacitance transient voltage suppressor arrays, designed to protect applications such as portable electronics and SMART phones. This series is available in both unidirectional and bidirectional configurations and is rated at 350 Watts for an 8/20µs wave shape.

The ESD05V32D-LC meets IEC 61000-4-2 (ESD) and IEC 61000-4-4 (EFT) requirements. At higher operating frequencies or faster edge rates, insertion loss and signal integrity are a major concern. This series offers a ultra low capacitance and low leakage current in a miniature SOD-323 package.

#### **ORDERING INFORMATION**

- ♦Package: SOD-323
- ♦Material: Halogen free
- ♦Packing: Tape & Reel
- ♦Quantity per reel: 3,000pcs

#### **FEATURES**

±15kV (Air)

- IEC 61000-4-4 (EFT) 40A (5/50 ns)
- ♦Protects one I/O line (bidirectional)
- ♦Low clamping voltage
- ♦Low leakage current
- $\diamond$  Response time is < 1 ns

#### **MACHANICAL DATA**

- $\diamond$  SOD-323 package
- ♦ Flammability Rating: UL 94V-0
- ♦Packaging: Tape and Reel
- ♦ High temperature soldering guaranteed: 260 °C/10s
- ♦Reel size: 7 inch
- ♦MSL1


#### APPLICATIONS

- ♦ Cell Phone Handsets and Accessories
- Microprocessor based equipment
- ♦ Personal Digital Assistants (PDA's)
- Notebooks, Desktops, and Servers
- ♦Portable Instrumentation
- ♦Peripherals
- ♦USB Interface

#### PACKAGE OUTLINE



#### **PIN CONFIGURATION**





# ESD05V32D-LC Bi-directional Ultra Low Capacitance TVS Array


Symbol	Parameter	Value	Units
$\mathbf{V}_{\text{ESD}}$	ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	±15 ±8	kV
P <sub>PP</sub>	Peak Pulse Power (8/20µs)	350	W
T <sub>OPT</sub>	Operating Temperature	-55/+150	°C
T <sub>STG</sub>	Storage Temperature	-55/+150	°C
TL	Lead Soldering Temperature	260	°C


ELECTRICAL CHARA	CTERIST	ICS (Tamb	o=25°C)						
	V <sub>RWM</sub>	V <sub>B</sub> @1mA	V <sub>c</sub> @1A	V <sub>c</sub> @	)lpp	V <sub>c</sub> @	)]pp	I <sub>R</sub>	CT
PART	(V)	(V)	(V)	(\	/)	(\	/)	(µA)	(pF)
NUMBER	Max	Min	Max	Max	lpp (A)	Max	lpp (A)	Max	Тур.
ESD05V32D-LC	5.0	6.0	9.8	18.3	8	20.0	18	1	0.8



### ESD05V32D-LC Bi-directional Ultra Low Capacitance TVS Array


#### **ELECTRICAL CHARACTERISTICS CURVE**





Pulse Waveform


Non-Repetitive Peak Pulse Power vs. Pulse Time







ESD05V32D-LC Bi-directional Ultra Low Capacitance TVS Array

## SOD-323 PACKAGE OUTLINE DIMENSIONS







Sumbol	Dimensions In Millimeters			
Symbol –	Min	Max		
A		1.00		
A1	0.000	0.100		
A2	0.800	0.900		
b	0.250	0.350		
с	0.080	0.150		
D	1.200	1.400		
E	1.600	1.800		
E1	2.500	2.700		
e	1.800	2.040		
L	0.475 REF			
L1	0.250	0.400		
θ	0°	8°		

