

High Power Precision Shunt Resistor, Up to 500W

FEATURES AND BENEFITS

- **Temperature coefficient of resistance (TCR)**
+25°C to +60°C, 25°C ref.: 0 ±1 ppm/°C
-25°C to +125°C, 25°C ref.: 0 ±5 ppm/°C
- Utilizing Ni-Cr Bulk Metal® Foil Technology for realizing low TCR
- Low thermal resistance with Copper plate
 - Improved to 0.1°C/W from 0.3°C/W (conventional model)
 - Maximum rated power up to 500W on heat sink
- Extended max. ambient temperature to 125°C (85°C with conventional model)
- Built-in Pt100 sensor monitor temperature of resistive element
 - Easily define size of suitable heat sink
 - As safety function for continuous operation



Available
RoHS
COMPLIANT



APPLICATIONS


- Output reference of precision power supply
- Reference of charge-discharge test for high capacity batteries

CONSTRUCTION OF MATERIALS

- Base plate: Nickel-plated Copper
- Current terminal: Nickel-plated Copper (T = 1.0 mm)
- Voltage and Pt terminals: Nickel-plated Copper (T = 0.5 mm)
- Package: PPS Injection-molded case

COMPOSITION OF MODEL NUMBER

Example:



* R is a dual-purpose letter that designates both the value range (R for ohmic) and the location of decimal point.

TCR – RESISTANCE VS. TOLERANCE


Tolerance of Built-in Pt100 Sensor:
±[0.8 + 0.008(t)]°C

TCR (ppm/°C)	Resistance Range (Ω)	Tolerance (%)	Rated Power (W)
0 ±1 (Z) 0 ±2.5 (Y) (+25°C to 60°C)	0.001 to 1**	±0.05 (A)	500 (on heat sink*)
0 ±5 (X) (-25°C to 125°C)		±0.1 (B)	
		±0.5 (D) ±1.0 (F)	

* Keep temperature of element surface less than 125°C.

** Please contact us for higher resistance value

CONFIGURATION – Dimensions in millimeters









TABLE 2 – PERFORMANCE	
PARAMETERS	SPECIFICATION
Maximum Rated Operating Temperature	25°C ($R \leq 10 \text{ m}\Omega$) 75°C ($R > 10 \text{ m}\Omega$)
Working Temperature Range	-55°C to +125°C
Maximum Working Current	320 A
Single Pulse Power Load	50 J (tp < 10 msec)
Dielectric Withstanding Voltage	AC 500 V
Inductance	< 10 nH
Internal Thermal Resistance (element/base plate)	$R_{\theta} < 0.1^{\circ}\text{C}/\text{W}$ ($R > 10 \text{ m}\Omega$) $R_{\theta} < 0.2^{\circ}\text{C}/\text{W}$ ($R \leq 10 \text{ m}\Omega$)
Life (200 W, Element Temperature 100°C)	±0.2% (2000 h)
High Temperature Exposure (125°C)	±0.2% (2000 h)





Disclaimer

ALL PRODUCTS, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE.

Vishay Precision Group, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "VPG"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

The product specifications do not expand or otherwise modify VPG's terms and conditions of purchase, including but not limited to, the warranty expressed therein.

VPG makes no warranty, representation or guarantee other than as set forth in the terms and conditions of purchase. **To the maximum extent permitted by applicable law, VPG disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.**

Information provided in datasheets and/or specifications may vary from actual results in different applications and performance may vary over time. Statements regarding the suitability of products for certain types of applications are based on VPG's knowledge of typical requirements that are often placed on VPG products. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. You should ensure you have the current version of the relevant information by contacting VPG prior to performing installation or use of the product, such as on our website at vpgsensors.com.

No license, express, implied, or otherwise, to any intellectual property rights is granted by this document, or by any conduct of VPG.

The products shown herein are not designed for use in life-saving or life-sustaining applications unless otherwise expressly indicated. Customers using or selling VPG products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify VPG for any damages arising or resulting from such use or sale. Please contact authorized VPG personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Copyright Vishay Precision Group, Inc., 2014. All rights reserved.