



#### **FEATURES**

- Flexibility Every unit offers linear position up to 400" (10m) providing flexibility to work across a wide range of aerial applications. These series offer a wide selection of industry standard output signals (4-20mA, 0-10Vdc, CANOpen and J1939 CANbus).
- Ease of use A compact design, a stainless-steel mounting bracket for multiple installation options and an easily-adjustable measuring cable orientation make this sensor easy to install and manage.
- Superior engineering TE provides engineering partnership to customize for specific applications. There is also an option to have two sensors elements in the same package with no additional space requirement. This provides fail-safe security for aerial applications.

#### **APPLICATIONS**

Accurate measurement in customized applications industrial and commercial transportation like:

- Fork lifts
- Telescopic arms
- Boom lifts
- Scissor lifts

# SK6

## Cable Actuated Encoder Reel

The SK6 is easily customizable to any rotary encoder into a 400-inch (10m), the linear position sensor is a perfect solution for applications ranging from mobile construction equipment to hydraulic lift tables and anything else in between.

This model offers ease-of-use, compact design and user flexibility. Designed for popular 2½ inch square flange and 58mm diameter synchro-mount flange encoder styles, the SK6 comes with everything you need to attach your own encoder. Also included is a stainless steel mounting bracket which lets the user easily change measuring cable orientation to one of the 4 different directions.

Converts Rotary Encoder to Linear Position Sensor Use with Popular Square Flange & Servo Mount Style User Adjustable Measuring Cable Orientation

### **Specifications**

Stroke Range 400 inches (10.2 m)

Rotary to Linear 1

1 turn = 15.020 inches

**Conversion Ratio** 

Accuracy 0.04% FS.

Measuring Cable 0.031-inch dia. bare stainless steel

Maximum Cable

60 inches per second

Velocity

Maximum Cable Acceleration

5 g

Measuring Cable

23 oz. (6,4 N) ±40%

Tension

Operating Temperature -40° to 185° F (-40° to 85° C)





2.5-inch Square Flange Style




Ø58 mm Synchro-Mount Style


### **Outline Drawing**









DIMENSIONS ARE IN INCHES [MM] tolerances are 0.04 IN. [1,0 MM] unless otherwise noted.



\* tolerance = +.005 -.001 [+0,1 -0,0] \*\* tolerance = +.005 -.005 [+0,1 -0,1]

## **Mounting Options**






## **Ordering Information**

### **Order Number**

## **Encoder Mounting Style**

stroke range


SK6-400-F01



F01 2½-inch Sq. Flange with 3/8-inch shaft

400 inches (10,2 m)


SK6-400-S02




**\$02**Synchro-Mount (Face Mount) with 10mm shaft / M4 screws

400 inches (10,2 m)

## 2.5-inch Square Flange Encoder Installation



### Synchro-Mount Encoder Installation



#### **NORTH AMERICA**

Measurement Specialties, Inc., a TE Connectivity Company Phone: +1-800-522-6752

Email: customercare.hmpt@te.com

#### **EUROPE**

MEAS Deutschland GmbH (Europe) a TE Connectivity Company Phone: +31 73 624 6999

Email: customercare.dtmd@te.com

#### ASIA

Measurement Specialties (China), Ltd., a TE Connectivity Company Phone: +86-400-820-6015 Email: <a href="mailto:customercare.shzn@te.com">customercare.shzn@te.com</a>

#### TE.com/sensors

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2019 TE Connectivity Ltd. family of companies All Rights Reserved.