



GE Sensing

A COMMITMENT TO EXCELLENCE

GE Sensing, Crown Industrial Estate, Priorswood Road, Taunton, Somerset, TA2 8QY, UK
Tel +44 (0) 1823 335200 Fax +44 (0) 1823 332637

TEST SPECIFICATION	PART No. YQS6000	ISSUE: A
CUSTOMER: Various	DATE: 12th August, 2010	QUANTITY:
Customer P/N:	ORIGINATOR: M.J.Roberts	PAGE 1 OF 1


DESCRIPTION: PTC THERMISTOR INTENDED FOR USE AS A CURRENT LIMITING PROTECTION DEVICE

MECHANICAL SPECIFICATION

CONSTRUCTION: ORGANIC RESIN COATED CERAMIC DISC WITH UNINSULATED LEADWIRES. THICK FILM SILVER ELECTRODES

TERMINATIONS: TIN COATED COPPER WIRE, STRAIGHT

DIMENSIONS in mm. NTS: SEE DRAWING BELOW.



ELECTRICAL SPECIFICATION:

RESISTANCE AT 25°C, R ₂₅ :	10Ω +/-20%	(1)
SWITCHING TEMPERATURE, T _b for ref at 2 x R min:	120°C +/- 7°C	(2)
MAXIMUM OPERATING VOLTAGE, V _{max} :	120Vdc	
BREAKDOWN VOLTAGE, V _{BD} :	>180Vdc	

NOTES

- (1) Measuring current: 10mA max.
- (2) Resistance = 2 × Resistance minimum

CHANGES SINCE LAST ISSUE: Δ							
Issue :	A						
Date :	12/08/10						

The copyright in this Specification/Drawing/Document is the property of Thermometrics and the Specification/Drawing/Document is issued on the condition that it is not copied, reprinted, stored in an electronic retrieval system or reproduced, nor its contents disclosed either wholly or in part to any Third Party without either the consent in writing of or in accordance with the conditions of a contract with Thermometrics@GE THERMOMETRICS.